



PM2H25-M0







- Push mounts require no adhesive backing or additional mounting hardware. They are inserted into pre-drilled holes. Can be used where only one side of the panel is accessible. This push mount does not have tensioning wings.

▪ Part Number	PM2H25-M0
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Push Barb Cable Tie Mount
▪ Product Type	Cable Tie Mounts - Push Mount
▪ Material	Weather Resistant Nylon 6.6
▪ Color	Black
▪ UL Recognized	E136577
▪ Height (In.)	.18
▪ Height (mm)	4.6
▪ Width (In.)	.38
▪ Width (mm)	9.6
▪ CE Compliant	CT-ACC4 / 10.96
▪ Environment	Outdoors
▪ Flammability Rating	UL94 V-2
▪ Max. Bundle Diameter (mm)	4.8
▪ Max. Panel Thickness (In.)	.125
▪ Max. Panel Thickness (mm)	3.2
▪ Mounting Method	Push barb
▪ Panel Hole Diameter (In.)	.250
▪ Panel Hole Diameter (mm)	6.4
▪ Pricing Description	Cable Tie Mount, Push Mount, WRBL
▪ Thickness (In.)	.30
▪ Thickness (mm)	7.6
▪ Used With Cable Ties	M, I, S
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1000
▪ BOM Qty. (# of Pkgs.)	

PANDUIT PART NO.	USE WITH THESE CABLE TIE CROSS-SECTIONS	DIMENSIONS				WEIGHT g/100pcs
		A	B	C	D	
PM2H25	MINIATURE INTERMEDIATE STANDARD	.62 (15.8)	.18 (4.6) REF	.30 (7.6)	.38 (9.6)	.10 (.45)

NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, AND COLOR.
- (*) DIMENSIONAL VARIANCE IS POSSIBLE DUE TO MOLDING PROCESS RELATED SINK MARKS.
- APPLICATION SPECIFICATION:
HOLE DIAMETER: .245 (6.3) - .255 (6.5)
PANEL THICKNESS: .125 (3.2) (MAX)



DIMENSIONS IN BRACKETS ARE METRIC [mm]

CAD FILENAME/LAYERS

G002391J_PB_PM2H25_03

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

PUSH MOUNT
PM2H25

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)
(.XX) ±0.02 (0.5) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE
PROJECTION.

DRAWN BY

MAT'L:

SCALE

5:2

DATE

01-20-02

NYLON 6/6

DRAWING NO.

GB02391J

DWG

A

SIZE

CHK'D

3	5/27/08	DJSM		CORRECTED FILE NAME	GB02391J	3			
2	5/22/08	DJSM		TABULARIZED DIMENSIONS, REMOVED WINDOW DIMENSIONS	GB02391J	2			
1	02/05/03	MSAD		.070 +/- .015 WAS .070 +/- .010 (1.8 +/- 0.38) (1.8 +/- 0.25)	GB02391J	1			
R	01/10/02	LGG		INITIAL RELEASE	GB02391J	R			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	