

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F


E

D

C


B

A




NOTES.

1. 適合ハウジング : 504051-****
APPLICABLE HOUSING : 504051-****
2. 材質 : 銅合金
MATERIAL : COPPER ALLOY
3. メッキ仕様 : 金メッキ、ニッケル下地
PLATING : GOLD PLATING
NICKEL UNDER PLATING
4. 圧着後、CS-504052-002の内容を満たす事
FULFILL THE CONTENTS OF
CS-504052-002 AFTER CRIMP



SECTION A-A



SECTION B-B

φ0.54 - 0.8	AWG #30 - #32	5040520298	CHAIN
INS. RANGE	WIRE RANGE	ORDER No.	FORM

REVISED EC NO: J2014-1702 DRAWN:YNAKE CHK'D:KASAKAWA APPR:NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 20:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION			
		10 UNDER	± 0.2	DRAWN BY THANYU	DATE 2012/09/04	TITLE 1.5 WIRE TO BOARD CONN. REC CRIMP TERMINAL (AWG #30 - 32)					
		10 OVER 30 UNDER	± 0.25	CHECKED BY KASAKAWA	DATE 2012/09/04						
		30 OVER	± 0.3	APPROVED BY YOITO	DATE 2012/09/04				molex		
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.					SHEET NO.
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		SD-504052-002					1 OF 1
				SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

9 8 7 6 5 4 3 2