









TYPE 102
SAME AS TYPE 101
EXCEPT AS SHOWN



OPTIONAL CONSTRUCTION
TYPE 102


SYMBOL DEFINITION			MISSING NUMBERS	
A DIMENSION WITHOUT AN INSPECTION REPORT SYMBOL  DOES NOT REQUIRE INSPECTION. IT MAY BE CONTROLLED ON AN INDIVIDUAL COMPONENT DRAWING.	TOTAL NO. OF SYMBOLS ON DRAWING	11		
	LAST NO. USED	19		

DATE		STG	REV	N/P	CHG	ZONE	REVISION HISTORY		AUTH	DR	APVD	APVD
15MY02	R	01	-	-	-	-	CLEARED REV COL 1 ALL PARTS - ADDED LOGO NOTE & RECYCLING CODE NOTES & ADDED NOTE AND REVISED MAT'L SPEC		225437	006	RH	ET
28JUN02	R	02	-	-	-	-	ALL PARTS - REVISED MATERIAL SPEC FROM PA6 TO PA66		226918	JGR	EOV	RC
30JUN03	R	03	-	-	-	-	ADDED OPTIONAL CONSTRUCTION FOR TYPE 102		242896	JYD	JYD	RC
22JUL03	R	04	-	-	-	-	ALL PARTS - REVISED TOLERANCES (2 PLCS)		243744	EOV	EOV	RC







OPTIONAL CONSTRUCTION

18
SMALL PINHOLES (INFO'S)
ACCEPTABLE IN THIS
AREA, DUE TO THIN
SECTIONS CAUSED BY PART
GEOMETRY & TOOL DRAFT




TYPE 101



NOTES


- UNLESS OTHERWISE SPECIFIED AND/OR INDICATED: DIMENSIONS ARE TO FACE OF VIEW SHOWN AND AUTOMATICALLY ROUNDED BY COMPUTER FOR INSPECTION CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. FOR ALL OTHER DIMENSIONS NOT SHOWN BUT REQUIRED FOR TOOL BUILD, SEE MATH MODEL FOR PRECISE TOOL PATH DATA.
- MATERIAL RECYCLING CODE >PA66< PER SAE J1344. (1.2)X(0.1) RAISED CHARACTERS AS SHOWN TO BE LOCATED ON ANY EXTERIOR SURFACE. OPTIONAL CONSTRUCTION TO BE NO MATERIAL RECYCLING CODE.
- THIS PART IS NOT CONTROLLED FOR AUTOMATIC FEEDING.
- MATING COMPONENTS OR EQUIVALENT: CONNECTOR 15300008
- (1.2)X(0.1) RAISED DELPHI CORPORATE BRAND TO BE LOCATED ON ANY EXTERIOR SURFACE, PREFERABLY VISIBLE AT FINAL ASSEMBLY. OPTIONAL CONSTRUCTION TO BE "PED" OR NO LOGO.

** 15300014	06	AB		M3592008 PA66 1M HS BLU	101-102	0.848
12191070	02	AA		M3592001 PA66 1M HS BLK	101	0.848
12186995	02	AA		M3592025 PA66 1M HS GRA MD	101	0.848
* 12162363	02	AB		M3592025 PA66 1M HS GRA MD	102	1.122
PART NO	REV N/P	STATUS		MATERIAL SPECIFICATION AND COLOR	TYPE	VOLUME CM ³



DIMENSIONAL RANGE (MM)		CHART	
FROM	TO	1	2
> 0	> 20	> 30	> 70
> 20	> 30	> 70	> 100
> 30	> 70	> 100	> 150
> 70	> 100	> 150	> 200
> 100	> 150	> 200	> 250
> 150	> 200	> 250	> 300
> 200	> 250	> 300	> 400
TOLERANCE UNLESS OTHERWISE SPECIFIED		ANGULAR TOLERANCE 12°	
1±0.15	±0.2	±0.3	±0.4
±0.4	±0.5	±0.6	±0.8
±1	±1	±1.2	±1.2

THIRD ANGLE PROJECTION	DO NOT SCALE	USE MATH DATA
------------------------	--------------	---------------



DELPHI

DELPHI PACKARD ELECTRIC SYSTEMS
WARREN, OH

DR	DATE
APVD1 E. O. VAZQUEZ	13MY00
APVD2 C. MIRANDA	15MY00
APVD3 J. ALVAREZ	15MY00
APVD4	
APVD5	

SUBSTANCES OF CONCERN AND RECYCLED CONTENT PER DELPHI 10949001

MATERIAL SEE CHART

DRAWING NAME TAXI LOCK TPA M/P 280

DRAWING NUMBER 12162505

SIZE A0	SCALE 5:1	FRAME NO 1	SHEET NO 1	STG REV 1	N/P 04
---------	-----------	------------	------------	-----------	--------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Delphi Connection Systems:](#)

[15300014-B](#)