







LOC		DIST		REVISIONS						
AD	00	P	LTR	DESCRIPTION			DATE	DWN	APVD	
			B	REVISED PER ECO-11-025276			05JAN2012	KH	DY	



- 1 MATERIAL:
HOUSING: LCP, GLASS FILLED, UL94V-0.
TERMINALS: HIGH PERFORMANCE COPPER ALLOY.
- 2 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN
ON PCB TAILS, NICKEL OVERALL.
- 3 FINISH:
30µ" MIN GOLD IN CONTACT AREA. SELECTIVE TIN-LEAD
ON PCB TAILS, NICKEL OVERALL.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 31JAN2011	 TE Connectivity	
		CHK J. EABY 31JAN2011		
DIMENSIONS:		APVD J. EABY 31JAN2011	NAME	
mm		PRODUCT SPEC	IMPACT, 2 PAIR, 16 COLUMN, HEADER	
		APPLICATION SPEC	UNGUIDED, LEFT END WALL	
			SIGNAL MODULE, 0.39 PTH	
MATERIAL		WEIGHT	SIZE	RESTRICTED TO
			A100779C=2057749	
SEE TABLE		CUSTOMER DRAWING	SCALE 6:1	SHEET 1 OF 2 REV B

LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		-		SEE SHEET 1	-	-	-

	5.5	2057749-6
	4.9	2057749-5
	4.5	2057749-4
	5.5	2057749-3
	4.9	2057749-2
	4.5	2057749-1
FINISH	DIM M	PART NUMBER

REFER TO WWW.TE.COM
FOR PRODUCT AVAILABILITY

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. K. SHOBER 31 JAN 2011	TE Connectivity			
DIMENSIONS:		CHK J. EABY 31 JAN 2011				
mm		APVD J. EABY 31 JAN 2011	NAME IMPACT, 2 PAIR, 16 COLUMN, HEADER UNGUIDED, LEFT END WALL SIGNAL MODULE, 0.39 PTH			
		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		
		9 PLC ± 1 PLC ±0.25 2 PLC ±0.13 3 PLC ± 4 PLC ± ANGLES ±		APPLICATION SPEC		
MATERIAL		FINISH		WEIGHT		RESTRICTED TO
-		SEE TABLE		-		-
-		CUSTOMER DRAWING		SCALE 5:1		SHEET 2 OF 2 REV B