



**Tripp Lite**  
1111 West 35th Street  
Chicago, IL 60609 USA  
Telephone: +(773) 869 1234  
E-mail: [saleshelp@tripplite.com](mailto:saleshelp@tripplite.com)

## Model #: INTERNET350U

### Internet Office 350VA Ultra-compact Standby 120V UPS with USB port



#### Highlights

- 350VA ultra-compact 120V standby UPS
- Maintains AC output during power failures
- 3 UPS battery supported outlets, 3 surge-only outlets
- USB port, TEL/DSL protection, Wall mountable, 99% efficient
- NEMA 5-15P input plug and 6 NEMA 5-15R outlets

#### Description

Tripp Lite's INTERNET350U standby UPS system offers complete protection from blackouts, brownouts and transient surges on both AC and dialup modem lines. Provides seamless battery support during brownouts and power failures with enough runtime to save and shutdown connected equipment without data loss. Offers complete power protection in an ultra-compact, flat-pack housing with an appearance closer to a power strip than other bulky UPS designs. Includes 3 battery supported outlets for computer, monitor and one vital system peripheral, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support. USB port enables optional unattended system shutdown without data loss in the case of extended power failure. PowerAlert software available via free download from [www.tripplite.com](http://www.tripplite.com), includes bundled USB cable. Built-in single line RJ11 phone suppression jacks with line splitter protects up to two directly connected modems, fax machines, cordless phones or other peripherals with a standard dialup phone connection. Built-in audible alarm and front panel LEDs offer continuous status information regarding line and battery power operation. 350VA/180 watt power handling ability supports entry-level PC systems for up to 15 minutes during power fail conditions. \$100,000 [connected equipment insurance](#) (USA, Puerto Rico, & Canada Only).

#### Package Includes

- INTERNET350U UPS System
- USB cable
- Instruction manual

#### Features

- INTERNET350U standby UPS offers complete protection from blackouts, brownouts and surges on both AC and TEL/DSL line connections
- 6 widely spaced outlets accommodate large transformer plugs without blocking outlets
- 3 battery supported outlets protect computer, monitor and vital system peripherals, plus 3 additional surge suppression-only outlets for printers and other system accessories not requiring battery support
- Provides battery derived AC output during blackouts and brownouts
- 350VA/180 watt power handling ability supports a variety of PCs, workstations and other sensitive electronics
- Supports entry-level PC systems up to 12 minutes during blackout conditions
- Built-in single line TEL/DSL line surge suppression protects modems, fax machines or cordless phones on a single phone line connection
- USB port, free PowerAlert software (available via web download) and cabling offer safe unattended shutdown without data loss during extended outages
- HID-compliant USB interface enables integration with built-in power management and auto-shutdown features of Windows and Mac OS X.

- Supports Tripp Lite's Watchdog system service to restore operation to locked equipment through soft reboot of application/OS or hard power off/on reboot of connected equipment - ideal for unattended kiosk applications
- Space saving, ultra-compact housing fits almost anywhere

## Specifications

OUTPUT	
Output Volt Amp Capacity (VA)	350
Output Watt Capacity (watts)	180
Nominal Output Voltage(s) Supported	115V; 120V
Frequency compatibility	60 Hz
Output voltage regulation (Battery mode)	115V (+/- 5%)
Built-in UPS output receptacles	6 5-15R outlet(s)
Surge suppression only outlets	3 UPS outlets, 3 surge-only outlets
Output AC waveform (AC mode)	Sine wave
Output AC waveform (battery mode)	PWM sine wave
INPUT	
Rated input current (at maximum load)	10A
Nominal Input Voltage(s) Supported	120V AC
UPS input connection type	5-15P
UPS Input cord length (ft.)	6
UPS Input cord length (m)	1.8
Recommended Electrical Service	15A 120V
BATTERY	
Full load runtime (minutes)	3.1 minutes (180w)
Half load runtime (minutes)	11.3 minutes (90w)
DC system voltage (VDC)	12
LEDS ALARMS & SWITCHES	
LED Indicators	2 LEDs indicate power status and overload/check battery status
Alarms	Audible alarm indicates power-failure and overload status
Switches	Combination switch controls on/off power status and self-test operation
SURGE / NOISE SUPPRESSION	
UPS AC suppression joule rating	380 joules

UPS Dateline suppression	1 line TEL/DSL (1 in / 1 out)
EMI / RFI AC noise suppression	Yes
<b>PHYSICAL</b>	
Installation form factors supported with included accessories	Tower; Ultra-compact desktop; Wallmount (using keyhole mounting tabs)
Primary form factor	Desktop
UPS / Power Module dimensions in primary form factor (height x width x depth / inches)	3 x 8 x 6.4
UPS / Power Module dimensions in primary form factor (height x width x depth / cm)	7.5 x 20.4 x 16.1
UPS / Power Module weight (lbs)	5
UPS / Power Module weight (kg)	2.3
UPS Shipping dimensions (height x width x depth / inches)	4.1 x 11.3 x 7.7
UPS Shipping dimensions (height x width x depth / cm)	10.5 x 28.7 x 19.5
Shipping weight (lbs)	5.8
Shipping weight (kg)	2.6
UPS housing material	ABS
<b>ENVIRONMENTAL</b>	
Operating Temperature Range	+32 to +104 degrees Fahrenheit / 0 to +40 degrees Celsius
Storage Temperature Range	+5 to +122 degrees Fahrenheit / -15 to +50 degrees Celsius
Relative Humidity	0 to 95%, non-condensing
AC mode BTU / hr. (full load)	6
Battery mode BTU / hr. (full load)	134.3
<b>COMMUNICATIONS</b>	
Communications interface	USB (HID enabled)
PowerAlert software	Free download from <a href="http://www.tripplite.com">www.tripplite.com</a>
Communications cable	USB interface cable included
WatchDog compatibility	Supports Watchdog application, OS and hard-reboot restart options for remote applications
<b>LINE / BATTERY TRANSFER</b>	
Transfer time	4 milliseconds (AC to battery mode) / 2 milliseconds (Battery to AC mode)
Low voltage transfer to battery power (setpoint)	99

High voltage transfer to battery power (setpoint)	139
<b>SPECIAL FEATURES</b>	
Cold Start (startup in battery mode during a power failure)	Cold-start operation supported
Green & high efficiency features	Greater than 95% efficiency - GREEN UPS
<b>CERTIFICATIONS</b>	
UPS Certifications	Tested to UL1778 (USA); Tested to CSA (Canada); Tested to NOM (Mexico); Meets FCC Part 15 Category B (EMI)
<b>WARRANTY</b>	
Product Warranty Period (U.S. & Canada)	3-year limited warranty
Product Warranty Period (International)	2-year limited warranty
Product Warranty Period (Mexico)	3-year limited warranty
Product Warranty Period (Puerto Rico)	3-year limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$100,000 <a href="#">Ultimate Lifetime Insurance</a>

## Related Items

### Optional Products

Related Model	Description	Qty.
<a href="#">CT120</a>	Instant-Read- AC Outlet Circuit Tester	1
<a href="#">DCATV</a>	Network Surge Suppressor - Essential protection for TV/VCR coaxial lines	1
<a href="#">DNET1</a>	Network Surge Suppressor - Essential protection for data and communication lines	1
<a href="#">DTEL2</a>	Network Surge Suppressor - Essential protection for data and communication lines	1
<a href="#">U005-10I</a>	10-inch USB A/A Gold Extension Cable (USB-A Right Angle Male to USB-A Female)	1
<a href="#">U222-004-R</a>	4-Port USB2.0 Ultra-Mini Hub	1
<a href="#">WATCHDOGSW</a>	WatchDog Service Monitoring / Reboot Software	1
<a href="#">WEXT5-INTERNET</a>	5-Year Extended Warranty - For Internet Office, AVR and ECO Series UPS Systems	1

More information, including related products, owner's manuals, and additional technical specifications, can be found online at [www.tripplite.com/en/products/model.cfm?txtModelID=2663](http://www.tripplite.com/en/products/model.cfm?txtModelID=2663).

Copyright © 2013 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.