




| LOC | DIST | REVISIONS |     |                           |         |     |      |
|-----|------|-----------|-----|---------------------------|---------|-----|------|
|     |      | P         | LTR | DESCRIPTION               | DATE    | DWN | APVD |
| AD  | 39   |           | K2  | REVISED PER ECO-11-004820 | 11MAR11 | RK  | HMR  |

D


C

B

A



KEY LOCATIONS (REF ONLY)



- 1 TOLERANCE NON CUMULATIVE
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

|   |          |                         |       |       |     |     |            |            |
|---|----------|-------------------------|-------|-------|-----|-----|------------|------------|
| 2 | OBSOLETE | A,C,E,H,K,M,Q,S,U,W,Y   | 3.900 | 3.744 | 24  | 1 1 | 25         | -2=87159-4 |
|   | OBSOLETE | A,C,E,G,J,L,N,Q,S,U,W,Y | 3.744 | 3.588 | 23  | 12  | 24         | 2- -3      |
|   | OBSOLETE | A,D,G,K,N,R,U,X         | 3.588 | 3.432 | 22  | 8   | 23         | 2- -2      |
|   | OBSOLETE | A,C,E,G,J,L,N,Q,S,U,W   | 3.432 | 3.276 | 21  | 1 1 | 22         | 2- -1      |
|   | OBSOLETE | A,D,G,K,N,R,U           | 3.276 | 3.120 | 20  | 7   | 21         | 2- -0      |
| 2 | OBSOLETE | A,C,E,G,J,L,N,Q,S,U     | 3.120 | 2.964 | 19  | 10  | 20         | 1- -9      |
|   |          | B,D,F,J,L,N,Q,S         | 2.964 | 2.808 | 18  | 8   | 19         | 1- -8      |
|   |          | A,D,F,J,P,S             | 2.808 | 2.652 | 17  | 6   | 18         | 1- -7      |
|   |          | A,D,G,K,N,R             | 2.652 | 2.496 | 16  | 6   | 17         | 1- -6      |
|   |          | A,C,E,G,J,L,N,Q         | 2.496 | 2.340 | 15  | 8   | 16         | 1- -5      |
|   |          | A,D,G,K,N               | 2.340 | 2.184 | 14  | 5   | 15         | 1- -4      |
|   |          | A,C,E,G,J,L,N           | 2.184 | 2.028 | 13  | 7   | 14         | 1- -3      |
| 2 | OBSOLETE | A,C,E,G,J,L             | 1.872 | 1.716 | 1 1 | 6   | 12         | 1- -2      |
|   |          | A,D,G,K                 | 1.716 | 1.560 | 10  | 4   | 1 1        | 1- -1      |
| 2 | OBSOLETE | A,C,E,G,J               | 1.560 | 1.404 | 9   | 5   | 10         | 1- -0      |
|   |          | A,D,G                   | 1.404 | 1.248 | 8   | 3   | 9          | - -9       |
| 2 | OBSOLETE | A,C,E,G                 | 1.248 | 1.092 | 7   | 4   | 8          | - -8       |
|   |          | A,C,E                   | 1.092 | .936  | 6   | 3   | 7          | - -7       |
|   |          | A,C,E                   | .936  | .780  | 5   | 3   | 6          | - -6       |
|   |          | A,C                     | .624  | .468  | 3   | 2   | 4          | - -5       |
|   |          | A                       | .468  | .312  | 2   | 1   | 3          | - -4       |
|   |          | A                       | .312  | .156  | 1   | 1   | 2          | - -3       |
|   |          | A,D,J,M,                | 2.028 | 1.872 | 12  | 4   | 13         | - -2       |
|   |          | A,D                     | .780  | .624  | 4   | 2   | 5          | 87159-1    |
|   |          | KEY LOCATIONS           |       | L     | B   | A   | NO OF KEYS | NO OF POS  |