


# TS

D-Sub connectors - Stamped and Formed Contacts

## STRAIGHT PCB TERMINATION ONE METAL SHELL CONNECTORS



### Specifications

- Connectors according to MIL C24308
- UL File: E149426

#### Materials and Platings

|                  |                                      |
|------------------|--------------------------------------|
| <b>Shells</b>    | Steel, tin over nickel plating       |
| <b>Insulator</b> | Glass-filled thermoplastic, UL 94V-0 |
| <b>Contacts</b>  | Brass, with selective gold plating   |
| <b>Boardlock</b> | Brass with nickel plating            |
| <b>Screwlock</b> | Brass with nickel plating            |

#### Electrical Data

|                              |                                  |
|------------------------------|----------------------------------|
| <b>Current rating</b>        | 5A                               |
| <b>Voltage rating</b>        | 600V AC/rms 50Hz                 |
| <b>Withstanding voltage</b>  | 1000V AC/rms 50Hz for one minute |
| <b>Insulation resistance</b> | 5000MΩ                           |
| <b>Contact resistance</b>    | 10mΩ max                         |

#### Climatic Data

|                              |                 |
|------------------------------|-----------------|
| <b>Operating temperature</b> | -55°C to +125°C |
|------------------------------|-----------------|

#### Mechanical Data

##### Mating and unmating force

Unit: kg (lb)

| No. of Cts | Mate (max)    | Unmate (min) |
|------------|---------------|--------------|
| 9          | 3.05 (6.74)   | 0.36 (0.79)  |
| 15         | 5.09 (11.24)  | 0.46 (1.01)  |
| 25         | 8.44 (18.66)  | 0.81 (1.8)   |
| 37         | 12.51 (27.65) | 1.1 (2.47)   |

- Standard plating thicknesses**
- gold flash
  - 0.4μm (15μ") gold
  - 0.76 μm (30μ") gold

The one shell D-sub Amphenol series features, stamped and formed contacts.

This series gives you Amphenol's high standards of quality and reliability to meet all of your commercial requirements

Economical  
straight PCB,  
one shell  
connectors


- Industrial
- Telecom
- Any industry standard I / O connections



**Amphenol**


TS / E10

## Shell Size Dimensions




\*see chart "how to order"

### RECOMMENDED P.C.B. LAYOUT




| Nb OF CONTACTS | DIMENSIONS mm (inch) |              |              |              |              |      |
|----------------|----------------------|--------------|--------------|--------------|--------------|------|
|                | A                    | B            | C            | D            | E            | X    |
| 9              | 30.84 (1.21)         | 24.99 (.984) | 16.92 (.666) | 16.26 (.640) | 11.08 (.436) | 2.77 |
| 15             | 39.24 (1.54)         | 33.32 (1.31) | 25.25 (.994) | 24.56 (.967) | 19.39 (.763) | 2.77 |
| 25             | 53.04 (2.09)         | 47.04 (1.85) | 38.96 (1.53) | 38.30 (1.51) | 33.24 (1.31) | 2.77 |
| 37             | 69.34 (2.73)         | 63.50 (2.50) | 55.42 (2.18) | 54.76 (2.16) | 49.86 (1.96) | 2.77 |


# Panel mounting option




Boardlock with Threaded Insert  
**RM5**



Boardlock with Front Screwlock  
**RM8**



Clear Hole  
**Blank**



Rear Insert Threaded  
**H or G**

## How to order

|                                                                                                                                                                                              |                                                                          |                                                                                                                                                   |  |
|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------|--|
| RoHS Compliant                                                                                                                                                                               |                                                                          | L ... TS ... ... ... C309                                                                                                                         |  |
| gold flash                                                                                                                                                                                   | 77: tinned shell for receptable<br>717: tinned shell + dimples for plug  | <p><b>plating option valid only for 0.76µm (30µ")</b></p> <p>part numbers to be written as follow:</p> <p>77.....C309<br/>or<br/>717.....C309</p> |  |
| 0.4µm (15µ")                                                                                                                                                                                 | 177: tinned shell for receptable<br>777: tinned shell + dimples for plug |                                                                                                                                                   |  |
| shell size<br>E, A, B, C                                                                                                                                                                     |                                                                          | <p><b>board mounting options</b></p> <p><b>Blank</b> = Clear Hole<br/><b>RM5</b> = boardlock<br/><b>RM8</b> = boardlock +front screwlock</p>      |  |
| <p><b>mounting options</b></p> <p><b>Blank</b> = Clear Hole<br/><b>G</b> = M3<br/><b>H</b> = 4-40<br/><b>H,G</b> must also be used to specify the threading of RM5 or RM8 grounding tabs</p> |                                                                          |                                                                                                                                                   |  |
| configuration<br>09, 15, 25, 37                                                                                                                                                              |                                                                          | <p><b>termination</b></p> <p><b>OL2</b> : L = 6.02mm (.237")<br/><b>OL2C</b> : L = 11.48mm (.452")</p>                                            |  |
|                                                                                                                                                                                              |                                                                          | <p><b>contact type</b></p> <p><b>P</b> = pin<br/><b>S</b> = socket</p>                                                                            |  |

Example: L77 TS E H 09 S OL2 RM5  
L717 TS E H 09 P OL2 RM8 C309

For special request, please consult factory

## Memo

Do not hesitate to contact us for further information

# Amphenol

## Amphenol IT & Communication Products

Block A3/A4, The 4th Industrial District of  
Industrial Headquarters, Dong Keng Road  
Gong Ming Town, Shen Zhen China  
Fax: +86(0)755 2754 9955

### Technical Support

Tel: +86(0)755 2717 7945  
Info-dsub@amphenol.com.cn  
<http://www.dsubconnector.com>