


FEATURES:

- CW light source with integrated wavelength locker
- Output Power: 13dBm (min.)
- Tunable over 8 ITU-T 50 GHz spaced channels (2.8nm)
- Available at L-band ITU-T grid wavelengths between 1570.416 to 1607.035nm
- Wavelength stability better than $\pm 25\text{pm}$ drift over 20 years operation and (0 to 70°C) case temperature variation
- Built-in optical isolator, Thermistor, TEC, Wavelength Monitor PIN-PD, Power Monitor PIN-PD
- Polarization maintaining (PANDA) fiber



APPLICATIONS:

Long haul DWDM transmission system
Metropolitan DWDM transmission system
Optical Test Equipment

DESCRIPTION:

The Eudyna Tunable LD module with Wavelength Locker (FLD5F15CA-S) is a high power CW laser (13dBm) with polarization maintaining fiber. It is intended for use with an external modulator. The oscillation wavelength can be tuned across a 2.8nm range (8 ITU-T 50GHz spaced channels) via adjustment of the chip temperature with the built-in TEC. The tuned wavelength can be locked onto the desired ITU-T grid channel via use of the built-in Wavelength Monitor. This laser is available at any of the 88 ITU-T wavelengths in the L-band (1570.416 to 1607.035nm). The device comes in a standard 14-pin butterfly package, and operates between 0 to 70°C.

ABSOLUTE MAXIMUM RATINGS ($T_c=25^\circ\text{C}$, unless otherwise specified)

Parameter	Symbol	Condition	Ratings		Unit
			Min.	Max.	
Storage Temperature	T_{stg}	-	-40	+85	$^\circ\text{C}$
Operating Case Temperature	T_{op}	-	0	+70	$^\circ\text{C}$
Optical Output Power	P_f	CW	-	30	mW
LD Forward Current	I_f	CW	-	300	mA
LD Reverse Voltage	V_R	-	-	2	V
PD Reverse Voltage	V_{DR}	-	-	20	V
PD Forward Current	I_{PF}	-	-	10	mA
Cooler Voltage	V_c	Cooling	-	+5.00	V
		Heating	-2.50	-	
Cooler Current	I_c	Cooling	-	+1.85	A
		Heating	-0.60	-	
Thermistor Temperature	T_{th}	ATC Operation	0	+70	$^\circ\text{C}$
Lead Soldering Time	-	260°C	-	10	sec

OPTICAL AND ELECTRICAL CHARACTERISTICS ($T_L=T_{set}$, (CH.1 to CH.8) $T_c=25^\circ\text{C}$, BOL, unless otherwise specified)

Parameter	Symbol	Test Conditions	Limits			Unit
			Min.	Typ.	Max.	
Laser Set Temperature (BOL)	T_{set}	-	11	-	47	$^\circ\text{C}$
Laser Set Temperature (EOL)	T_{set}	-	10	-	48	$^\circ\text{C}$
Optical Output Power	P_f	-	20	-	-	mW
Threshold Current	I_{th}	-	3	-	45	mA
Forward Voltage	V_F	-	-	-	2.2	V
Slope Efficiency	η	-	-	0.14	-	mW/mA
Operating Forward Current	I_{op}	-	-	-	250	mA
Peak Wavelength	λ_p	CH.1 to CH.8, ORL>40dB	Note (4)			nm
Wavelength Stability with Case Temperature and Aging	-	$I_{m1}, I_{m2}=\text{constant}$, $T_c=0$ to 70°C , 20 years	-25	-	+25	pm
Wavelength Stability with LD Current Change	-	$TLD=T_{set}$	-	-	25	pm/mA
Spectral Width (-3dB)	$\Delta\lambda$	ORL>40dB	-	3	10	MHz
Side Mode Suppression	S_r		33	-	-	dB
Power Monitor Current	I_{m1}	$P_f=20\text{mW}$	0.1	-	1.8	mA
Power Monitor Dark Current	I_{dm1}	$V_{pd}=5\text{V}$	-	-	100	nA
Power Monitor Capacitance	C_{t1}	$V_{pd}=5\text{V}$, $f=1\text{MHz}$	-	-	10	pF
Wavelength Monitor Current	I_{m2}	$P_f=20\text{mW}$, WL Locked	0.1	-	1.8	mA
Wavelength Monitor Dark Current	I_{dm2}	$V_{pd}=5\text{V}$	-	-	100	nA
Wavelength Monitor Capacitance	C_{t2}	$V_{pd}=5\text{V}$, $f=1\text{MHz}$	-	-	10	pF
Wavelength difference between lock point and $I_{m2\text{peak}}$ (Note 2)	$\Delta\lambda$ locked		17.0	-	33.0	GHz
I_{m2} peak/bottom Ratio	$I_{m2\text{peak}}/I_{m2\text{bottom}}$		1.0	-	4.5	dB
Tracking Error (Note 3)	TE	$I_{m1}, I_{m2}=\text{constant}$, $T_c=0$ to $+70^\circ\text{C}$	-0.5	-	+0.5	dB
Optical Isolation	I_S	$T_c=0$ to $+70^\circ\text{C}$	22	-	-	dB
Polarization Extinction Ratio	PER		20	-	-	dB
Relative Intensity Noise	RIN	CW, ORL>40dB average of $f=\text{DC}$ to 7.5GHz	-	-	-140	dB/Hz
Cooler Current	I_c	$T_L=T_{set}$, $T_c=+70^\circ\text{C}$	-	-	1.05	A
Cooler Voltage	V_c		-	-	3.80	V
Cooler Power	P_c		-	-	4.00	W
Thermistor Resistance	R_{th}	$T_L=25^\circ\text{C}$, $T_c=+25^\circ\text{C}$	9.5	10.0	10.5	$\text{k}\Omega$
Thermistor B Constant (Note 4)	B		3,270	3,450	3,630	K

Note 1. $TE=10\log[P_f(T_c)/P_f(25)]$

Note 2. Relation between resistance and temperature ($^\circ\text{K}$) is: $R_{th}(T) = R_{th}(25^\circ\text{C}) \cdot \exp[B(1/T - 1/298)]$

Note 3. At the shortest wavelength of each sub-band, wavelength at lock point is longer than I_{m2} peak. (Increasing wavelength shall give a decrease in wavelength monitor current) The value is written in frequency: $f=c/\lambda_p$, $c=2.99792458 \times 10^8\text{m/s}$

Note 4. Reference Table 1 for Wavelength Table

Fig. 1 Forward Current vs Output Power




Fig. 2 Temperature Dependence of Wavelength(ACC Operation)




Fig. 3 Cooler Voltage -Current




Fig.4 Spectrum




Fig. 5 Filter Curve





Table 1 Wavelength Table

Part Number	Wavelength (nm) (TL=Tset) (in vacuum)	Tolerance (nm)	Locking Curve Slope	Part Number	Wavelength (nm) (TL=Tset) (in vacuum)	Tolerance (nm)	Locking Curve Slope
FLD5F15CA-S9090	1570.416	±0.01	Negative	FLD5F15CA-S8850	1590.411	±0.01	Negative
	1570.828	±0.01	Positive		1590.833	±0.01	Positive
	1571.239	±0.01	Negative		1591.255	±0.01	Negative
	1571.651	±0.01	Positive		1591.678	±0.01	Positive
	1572.063	±0.01	Negative		1592.100	±0.01	Negative
	1572.476	±0.01	Positive		1592.523	±0.01	Positive
	1572.888	±0.01	Negative		1592.946	±0.01	Negative
FLD5F15CA-S9050	1573.301	±0.01	Positive		1593.369	±0.01	Positive
	1573.714	±0.01	Negative	FLD5F15CA-S8810	1593.793	±0.01	Negative
	1574.127	±0.01	Positive		1594.217	±0.01	Positive
	1574.540	±0.01	Negative		1594.641	±0.01	Negative
	1574.954	±0.01	Positive		1595.065	±0.01	Positive
	1575.368	±0.01	Negative		1595.489	±0.01	Negative
	1575.782	±0.01	Positive		1595.914	±0.01	Positive
FLD5F15CA-S9010	1576.196	±0.01	Negative		1596.339	±0.01	Negative
	1576.610	±0.01	Positive		1596.764	±0.01	Positive
	1577.025	±0.01	Negative	FLD5F15CA-S8770	1597.189	±0.01	Negative
	1577.440	±0.01	Positive		1597.615	±0.01	Positive
	1577.855	±0.01	Negative		1598.041	±0.01	Negative
	1578.270	±0.01	Positive		1598.467	±0.01	Positive
	1578.686	±0.01	Negative		1598.893	±0.01	Negative
	1579.102	±0.01	Positive		1599.320	±0.01	Positive
	1579.518	±0.01	Negative		1599.746	±0.01	Negative
FLD5F15CA-S8970	1579.934	±0.01	Positive		1600.173	±0.01	Positive
	1580.350	±0.01	Negative	FLD5F15CA-S8730	1600.600	±0.01	Negative
	1580.767	±0.01	Positive		1601.028	±0.01	Positive
	1581.184	±0.01	Negative		1601.455	±0.01	Negative
	1581.601	±0.01	Positive		1601.883	±0.01	Positive
	1582.018	±0.01	Negative		1602.311	±0.01	Negative
	1582.436	±0.01	Positive		1602.740	±0.01	Positive
FLD5F15CA-S8930	1582.854	±0.01	Negative		1603.168	±0.01	Negative
	1583.271	±0.01	Positive		1603.597	±0.01	Positive
	1583.690	±0.01	Negative	FLD5F15CA-S8690	1604.026	±0.01	Negative
	1584.108	±0.01	Positive		1604.455	±0.01	Positive
	1584.527	±0.01	Negative		1604.885	±0.01	Negative
	1584.946	±0.01	Positive		1605.314	±0.01	Positive
	1585.365	±0.01	Negative		1605.744	±0.01	Negative
	1585.784	±0.01	Positive		1606.174	±0.01	Positive
FLD5F15CA-S8890	1586.203	±0.01	Negative		1606.605	±0.01	Negative
	1586.623	±0.01	Positive		1607.035	±0.01	Positive
	1587.043	±0.01	Negative				
	1587.463	±0.01	Positive				
	1587.884	±0.01	Negative				
	1588.304	±0.01	Positive				
	1588.725	±0.01	Negative				
	1589.146	±0.01	Positive				
	1589.568	±0.01	Negative				
	1589.989	±0.01	Positive				

NOTE

Negative slope: Increasing wavelength shall give a decrease in wavelength monitor current.

Positive slope: Increasing wavelength shall give an increase in wavelength monitor current.



For further information please contact:

Eudyna Devices USA Inc.

2355 Zanker Rd.
San Jose, CA 95131-1138, U.S.A.
TEL: (408) 232-9500
FAX: (408) 428-9111
www.us.eudyna.com

Eudyna Devices Europe Ltd.

Network House
Norreys Drive
Maidenhead, Berkshire SL6 4FJ
United Kingdom
TEL: +44 (0) 1628 504800
FAX: +44 (0) 1628 504888

Eudyna Devices Asia Pte Ltd.

Hong Kong Branch
Rm. 1101, Ocean Centre, 5 Canton Rd.
Tsim Sha Tsui, Kowloon, Hong Kong
TEL: +852-2377-0227
FAX: +852-2377-3921

Eudyna Devices Inc.

Sales Division
1, Kanai-cho, Sakae-ku
Yokohama, 244-0845, Japan
TEL: +81-45-853-8156
FAX: +81-45-853-8170

CAUTION

Eudyna Devices Inc. products contain **gallium arsenide (GaAs)** which can be hazardous to the human body and the environment. For safety, observe the following procedures:

- Do not put this product into the mouth.
- Do not alter the form of this product into a gas, powder, or liquid through burning, crushing, or chemical processing as these by-products are dangerous to the human body if inhaled, ingested, or swallowed.
- Observe government laws and company regulations when discarding this product. This product must be discarded in accordance with methods specified by applicable hazardous waste procedures.

Eudyna Devices Inc. reserves the right to change products and specifications without notice. The information does not convey any license under rights of Eudyna Devices Inc. or others.

© 2004 Eudyna Devices USA Inc.
Printed in U.S.A.