

Features

- RoHS compliant* (see How to Order "Termination" option)
- Standard E.I.A. package compatible with automatic placement equipment
- Tape and reel packaging standard
- Custom circuits are available
- AEC-Q200 qualified
- Compliant leads to reduce solder joint fatiguing
- Standard electrical schematics: isolated, bussed, dual terminator
- **Now available with improved tolerance to ±0.5 %**

4800P Series - Thick Film Surface Mount Medium Body

Product Characteristics

Resistance Range ..... 10 ohms to 2.2 megohms
Maximum Operating Voltage .....50 V
Temperature Coefficient of Resistance
50 Ω and above.....±100 ppm/°C
below 50 Ω.....±250 ppm/°C
TCR Tracking
(for equal values within a package)
.....50 ppm/°C max. for values > 50 Ω;
.....100 ppm/°C for values ≤ 50 Ω
Operating Temperature
.....-55 °C to +125 °C
Insulation Resistance
..... 10,000 megohms min.
Dielectric Withstanding Voltage
.....200 VRMS
Lead Solderability.....Meet requirements of MIL-STD-202 Method 208

Environmental Characteristics

TESTS PER MIL-STD-202..... ΔR MAX.
Short Time Overload.....±0.25 %
Load Life.....±1.00 %
Moisture Resistance.....±0.50 %
Resistance to Soldering Heat....±0.25 %
Thermal Shock .....±0.25 %

Physical Characteristics

Flammability ..... Conforms to UL94V-0
Lead Frame Material
.....Copper, solder coated
Body Material..... Thermoplastic

How To Order

48 16 P - 1 - 103 __ __

Model
(48 = SOM Pkg.)

Number of Pins

Electrical Configuration
- 1 or 4 = Isolated*
- 2 = Bussed*
- 3 = Dual Terminator*

Resistance Code
- First 2 digits are significant
- Third digit represents the number of zeros to follow.

Resistance Tolerance
- Blank = ±2 % (see "Resistance Tolerance" on next page for resistance range)
- F = ±1 % (100 ohms - 1 megohm)
- D = ±0.5 % (100 ohms - 1 megohm)

Terminations
- All electrical configurations EXCEPT T03: LF = RoHS compliant
- ONLY electrical configuration T03: L = RoHS compliant
- Blank = Tin/Lead-plated

*For tube packaging, use T01, T02, T03 or T04.
Consult factory for other available options.

Package Power Temp. Derating Curve



Package Power Rating at 70 °C

4814P .....1.12 watts
4816P .....1.28 watts
4818P .....1.44 watts
4820P .....1.60 watts

Typical Part Marking

Represents total content. Layout may vary.



Recommended Land Pattern



NOTE: Land pattern dimensions are based on design rules established by the Institute for Interconnecting and Packaging Electronic Circuits in IPC-SM-782.

For Standard Values Used in Capacitors, Inductors, and Resistors, click here.

Product Dimensions



Lead coplanarity .102mm (.004 inch) max. at mounting surface.

Governing dimensions are in metric. Dimensions in parentheses are inches and are approximate.

*Terminal centerline to centerline measurements made at point of emergence of the lead from the body.

*RoHS Directive 2002/95/EC Jan. 27, 2003 including annex and RoHS Recast 2011/65/EU June 8, 2011.
Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.

For information on specific applications, download Bourns' application notes:

- DRAM Applications
- Dual Terminator Resistor Networks
- R/2R Ladder Networks
- SCSI Applications

4800P Series - Thick Film Surface Mount Medium Body

BOURNS®

Isolated Resistors (1 and 4 Circuits)

Model 4814P-1
Model 4816P-1 (Shown)
Model 4818P-1
Model 4820P-1



Model 4816P-4 (Shown)
Model 4820P-4



Resistance Tolerance
10 ohms to 49 ohms..... ±1 ohm
50 ohms to 2.2 megohms..... ±2 %*

Power Rating per Resistor
1 Circuit at 70 °C ..... 0.160 watt
4 Circuit at 70 °C ..... 0.160 watt

Resistor Power Temp. Derating Curve



Bussed Resistors (2 Circuit)

Model 4814P-2
Model 4816P-2 (Shown)
Model 4818P-2
Model 4820P-2



Resistance Tolerance
10 ohms to 49 ohms..... ±1 ohm
50 ohms to 2.2 megohms..... ±2 %*

Power Rating per Resistor
2 Circuit at 70 °C ..... 0.080 watt

Resistor Power Temp. Derating Curve



Dual Terminator (3 Circuit)

Model 4814P-3
Model 4816P-3 (Shown)
Model 4818P-3
Model 4820P-3



Resistance Tolerance
Below 100 ohms ..... ±2 ohms
100 ohms to 2.2 megohms..... ±2 %*

Power Rating per Resistor
3 Circuit at 70 °C ..... 0.080 watt

Resistor Power Temp. Derating Curve



Popular Resistance Values (1, 4 and 2 Circuits)**

Ohms	Code	Ohms	Code	Ohms	Code	Ohms	Code	Ohms	Code
10	100	180	181	1,800	182	15,000	153	120,000	124
22	220	220	221	2,000	202	18,000	183	150,000	154
27	270	270	271	2,200	222	20,000	203	180,000	184
33	330	330	331	2,700	272	22,000	223	220,000	224
39	390	390	391	3,300	332	27,000	273	270,000	274
47	470	470	471	3,900	392	33,000	333	330,000	334
56	560	560	561	4,700	472	39,000	393	390,000	394
68	680	680	681	5,600	562	47,000	473	470,000	474
82	820	820	821	6,800	682	56,000	563	560,000	564
100	101	1,000	102	8,200	822	68,000	683	680,000	684
120	121	1,200	122	10,000	103	82,000	823	820,000	824
150	151	1,500	152	12,000	123	100,000	104	1,000,000	105

* Add "F" after resistance code for ±1 % tolerance available from 100 Ω through 1M Ω, or add "D" after resistance code for ±0.5 % tolerance available from 100 Ω through 1M Ω.
Part number suffix examples: -103 = 10K Ω, ±2 %; -103F = 10K Ω, ±1 %; -103D = 10K Ω, ±0.5 %
** Non-standard values available, within resistance range.

Popular Resistance Values (3 Circuit)**

Resistance			
Ohms		Code	
R_1	R_2	R_1	R_2
160	240	161	241
180	390	181	391
220	270	221	271
220	330	221	331
330	390	331	391
330	470	331	471
3,000	6,200	302	622

REV. 04/15

Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.

Surface Mount Ordering Guide

BOURNS®

Electrical Configuration	*Circuit Codes		Examples
	Tape & Reel	Tubes	
Isolated	1	T01	4816P-1-101 Isolated Circuit in Tape & Reel Package
Bussed	2	T02	
Dual Terminated	3	T03	4816P-T01-101 Isolated Circuit in Slide Tube Package
Adj. Isolated	4	T04	

*4816P-X-RC: To specify package type, replace "X" with appropriate "Circuit Code".



NOTE: DIMENSIONS NOT SPECIFIED ARE PER EIA RS-481-2.

DIMENSIONS: MM / (IN)



Model	Standard Quantity per Reel	Carrier Tape Width (W)	Cover Tape Width (W)	Reel Width (T)	Pocket Center (F)
4814P	2,000	24.0 ± .30 / (.945 ± .012)	21.0 / (.827) NOM.	30.4 / (1.197) MAX.	11.5 ± .10 / (.453 ± .004)
4816P					
4818P					
4820P					

Leader Length = 500 min.
Trailer Length = 500 mm min.
} Empty Component Pockets Sealed with Cover Tape

Specifications are subject to change without notice.
The device characteristics and parameters in this data sheet can and do vary in different applications and actual device performance may vary over time.
Users should verify actual device performance in their specific applications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Bourns:

4814P-T01-824LF 4814P-T02-561LF 4814P-T01-561LF 4818P-T02-103 4816P-3-121/471 4816P-T02-824 4816P-T02-511 4816P-R2R-103 4820P-T01-561 4820P-2-684 4816P-T01-751 4816P-T02-822 4816P-T02-561 4818P-T02-153 4816P-T03-221/331 4816P-T02-121 4816P-T01-331 4816P-T02-151 4816P-T01-391 4816P-T02-111 4814P-2-683LF 4814P-1-683LF 4816P-T02-131 4820P-T01-103 4816P-2-512 4820P-T01-121 4816P-T02-101 4814P-1-564LF 4820P-T01-102 4816P-T02-181 4816P-T02-562LF 4820P-T01-100 4814P-2-564LF 4820P-3-152/332 4816P-2-224LF 4820P-T02-331 4814P-T02-824LF 4820P-T02-391 4814P-2-203LF 4814P-1-203LF 4816P-T02-394LF 4816P-1-821LF 4814P-2-223LF 4814P-1-223LF 4816P-1-220G 4816P-2-821LF 4814P-1-273LF 4816P-1-224 4814P-2-273LF 4816P-1-224F 4816P-T01-394LF 4814P-T01-394LF 4820P-2-222 4816P-T01-563LF 4814P-2-513 4816P-2-563 4816P-2-513 4816P-T02-563LF 4814P-T02-472 4816P-T02-391LF 4816P-T01-391LF 4814P-T02-471 4814P-T02-394LF 4816P-1-684LF 4820P-2-272 4814P-2-563 4816P-T02-270LF 4816P-2-562LF 4816P-T02-470LF 4816P-2-151 4816P-T02-220LF 4814P-2-274LF 4816P-1-563 4814P-2-153 4816P-2-334LF 4816P-2-131 4814P-1-274LF 4816P-1-681LF 4816P-T02-330LF 4814P-2-103F 4814P-2-104 4816P-2-121 4816P-2-184 4816P-2-181 4816P-T02-820LF 4816P-1-513 4816P-T02-390LF 4814P-2-102 4816P-2-101 4816P-2-111 4816P-T02-680LF 4816P-2-682 4816P-1-334LF 4816P-2-681LF 4814P-T02-102LF 4814P-T02-124LF 4820P-2-822 4816P-1-102LF 4814P-T02-105 4814P-T01-124LF