



Model Number

NBB20-L3M-US-V93

Features

- 20 mm flush
- 2-wire AC/DC
- 2-corner LED, metal base & mount

Accessories

V93-G-YE2M-STOOW

Female cordset, 7/8" - 16 UNF, 3-pin, PUR cable

MHW 01

Modular mounting bracket

Technical Data

General specifications

Switching element function	AC/DC	NO
Rated operating distance	s_n	20 mm
Installation		flush
Output polarity		AC/DC
Reduction factor r_{AI}		0.30 - 0.40
Reduction factor r_{304}		0.60 - 0.80

Nominal ratings

Operating voltage	U_B	20 ... 250 V AC/DC
Switching frequency	f	0 ... 30 Hz
Hysteresis	H	3 ... 15 typ. 10 %
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	U_d	≤ 7 V
Operating current	I_L	3 ... 300 mA
Off-state current	I_r	≤ 1.7 mA
Operating voltage display		LED, green
Switching state indication		LED, red

Indicators/operating means

LED red/green	Short circuit/overload indication
---------------	-----------------------------------

Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
---------------------	--------------------------------

Mechanical specifications

Connection type	Connector 7/8"-16 UN , 3-pin
Housing material	metal - Zinc housing
Sensing face	Thermoset Plastic
Housing base	Metal Bracket



Compliance with standards and directives

Standard conformity	
Standards	IEC 61000-4 / EN 60947-5-2:2004


Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	Certified by China Compulsory Certification (CCC)


Dimensions



Electrical Connection



Pinout



Wire colors

1	GN	(green)
2	BK	(black)
3	WH	(white)