

**IRFB52N15DPbF**  
**IRFS52N15DPbF**  
**IRFSL52N15DPbF**  
HEXFET® Power MOSFET


**Applications**

- High frequency DC-DC converters
- Plasma Display Panel

**Benefits**

- Low Gate-to-Drain Charge to Reduce Switching Losses
- Fully Characterized Capacitance Including Effective  $C_{OSS}$  to Simplify Design, (See App. Note AN1001)
- Fully Characterized Avalanche Voltage and Current
- Lead-Free

| Key Parameters           |     |            |
|--------------------------|-----|------------|
| $V_{DS}$                 | 150 | V          |
| $V_{DS(Avalanche)}$ min. | 200 | V          |
| $R_{DS(ON)}$ max @ 10V   | 32  | m $\Omega$ |
| $T_J$ max                | 175 | °C         |



**Absolute Maximum Ratings**

|                                   | Parameter                                  | Max.                   | Units |
|-----------------------------------|--------------------------------------------|------------------------|-------|
| $I_D$ @ $T_C = 25^\circ\text{C}$  | Continuous Drain Current, $V_{GS}$ @ 10V ⑦ | 51*                    | A     |
| $I_D$ @ $T_C = 100^\circ\text{C}$ | Continuous Drain Current, $V_{GS}$ @ 10V ⑦ | 36*                    |       |
| $I_{DM}$                          | Pulsed Drain Current ①                     | 240                    |       |
| $P_D$ @ $T_A = 25^\circ\text{C}$  | Power Dissipation ⑦                        | 3.8                    | W     |
| $P_D$ @ $T_C = 25^\circ\text{C}$  | Power Dissipation ⑦                        | 230*                   |       |
|                                   | Linear Derating Factor ⑦                   | 1.5*                   | W/°C  |
| $V_{GS}$                          | Gate-to-Source Voltage                     | $\pm 30$               | V     |
| $dv/dt$                           | Peak Diode Recovery $dv/dt$ ③              | 5.5                    | V/ns  |
| $T_J$                             | Operating Junction and                     | -55 to + 175           | °C    |
| $T_{STG}$                         | Storage Temperature Range                  |                        |       |
|                                   | Soldering Temperature, for 10 seconds      | 300 (1.6mm from case ) |       |
|                                   | Mounting torque, 6-32 or M3 screw ⑥        | 10 lbf•in (1.1N•m)     |       |

**Thermal Resistance**

|                 | Parameter                             | Typ. | Max.  | Units |
|-----------------|---------------------------------------|------|-------|-------|
| $R_{\theta JC}$ | Junction-to-Case                      | —    | 0.47* | °C/W  |
| $R_{\theta CS}$ | Case-to-Sink, Flat, Greased Surface ⑥ | 0.50 | —     |       |
| $R_{\theta JA}$ | Junction-to-Ambient ⑥                 | —    | 62    |       |
| $R_{\theta JA}$ | Junction-to-Ambient ⑦                 | —    | 40    |       |

\*  $R_{\theta JC}$  (end of life) for D²Pak and TO-262 = 0.65°C/W. This is the maximum measured value after 1000 temperature cycles from -55 to 150°C and is accounted for by the physical wearout of the die attach medium.

Notes ① through ⑦ are on page 11

www.irf.com

**Static @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**

|                                 | Parameter                            | Min. | Typ. | Max. | Units               | Conditions                                            |
|---------------------------------|--------------------------------------|------|------|------|---------------------|-------------------------------------------------------|
| $V_{(BR)DSS}$                   | Drain-to-Source Breakdown Voltage    | 150  | —    | —    | V                   | $V_{GS} = 0V, I_D = 250\mu A$                         |
| $\Delta V_{(BR)DSS}/\Delta T_J$ | Breakdown Voltage Temp. Coefficient  | —    | 0.16 | —    | V/ $^\circ\text{C}$ | Reference to $25^\circ\text{C}$ , $I_D = 1\text{mA}$  |
| $R_{DS(on)}$                    | Static Drain-to-Source On-Resistance | —    | —    | 32   | m $\Omega$          | $V_{GS} = 10V, I_D = 36A$ ④                           |
| $V_{GS(th)}$                    | Gate Threshold Voltage               | 3.0  | —    | 5.0  | V                   | $V_{DS} = V_{GS}, I_D = 250\mu A$                     |
| $I_{DSS}$                       | Drain-to-Source Leakage Current      | —    | —    | 25   | $\mu A$             | $V_{DS} = 150V, V_{GS} = 0V$                          |
|                                 |                                      | —    | —    | 250  |                     | $V_{DS} = 120V, V_{GS} = 0V, T_J = 150^\circ\text{C}$ |
| $I_{GSS}$                       | Gate-to-Source Forward Leakage       | —    | —    | 100  | nA                  | $V_{GS} = 30V$                                        |
|                                 | Gate-to-Source Reverse Leakage       | —    | —    | -100 |                     | $V_{GS} = -30V$                                       |


**Dynamic @  $T_J = 25^\circ\text{C}$  (unless otherwise specified)**

|                        | Parameter                       | Min. | Typ. | Max. | Units | Conditions                                      |
|------------------------|---------------------------------|------|------|------|-------|-------------------------------------------------|
| $g_{fs}$               | Forward Transconductance        | 19   | —    | —    | S     | $V_{DS} = 50V, I_D = 36A$                       |
| $Q_g$                  | Total Gate Charge               | —    | 60   | 89   | nC    | $I_D = 36A$                                     |
| $Q_{gs}$               | Gate-to-Source Charge           | —    | 18   | 27   |       | $V_{DS} = 75V$                                  |
| $Q_{gd}$               | Gate-to-Drain ("Miller") Charge | —    | 28   | 42   |       | $V_{GS} = 10V$ , ④                              |
| $t_{d(on)}$            | Turn-On Delay Time              | —    | 16   | —    | ns    | $V_{DD} = 75V$                                  |
| $t_r$                  | Rise Time                       | —    | 47   | —    |       | $I_D = 36A$                                     |
| $t_{d(off)}$           | Turn-Off Delay Time             | —    | 28   | —    |       | $R_G = 2.5\Omega$                               |
| $t_f$                  | Fall Time                       | —    | 25   | —    |       | $V_{GS} = 10V$ ④                                |
| $C_{iss}$              | Input Capacitance               | —    | 2770 | —    | pF    | $V_{GS} = 0V$                                   |
| $C_{oss}$              | Output Capacitance              | —    | 590  | —    |       | $V_{DS} = 25V$                                  |
| $C_{rss}$              | Reverse Transfer Capacitance    | —    | 110  | —    |       | $f = 1.0\text{MHz}$                             |
| $C_{oss}$              | Output Capacitance              | —    | 3940 | —    |       | $V_{GS} = 0V, V_{DS} = 1.0V, f = 1.0\text{MHz}$ |
| $C_{oss}$              | Output Capacitance              | —    | 260  | —    |       | $V_{GS} = 0V, V_{DS} = 120V, f = 1.0\text{MHz}$ |
| $C_{oss \text{ eff.}}$ | Effective Output Capacitance    | —    | 550  | —    |       | $V_{GS} = 0V, V_{DS} = 0V \text{ to } 120V$ ⑤   |

**Avalanche Characteristics**

|                     | Parameter                        | Min. | Typ. | Max. | Units |
|---------------------|----------------------------------|------|------|------|-------|
| $E_{AS}$            | Single Pulse Avalanche Energy ②⑥ | —    | —    | 470  | mJ    |
| $I_{AR}$            | Avalanche Current ①              | —    | —    | 36   | A     |
| $E_{AR}$            | Repetitive Avalanche Energy ①    | —    | 450  | —    | mJ    |
| $V_{DS(Avalanche)}$ | Repetitive Avalanche Voltage ①   | 200  | —    | —    | V     |

**Diode Characteristics**

|          | Parameter                              | Min.                                                                        | Typ. | Max. | Units | Conditions                                                                                                                                           |
|----------|----------------------------------------|-----------------------------------------------------------------------------|------|------|-------|------------------------------------------------------------------------------------------------------------------------------------------------------|
| $I_S$    | Continuous Source Current (Body Diode) | —                                                                           | —    | 60   | A     | MOSFET symbol showing the integral reverse p-n junction diode.  |
| $I_{SM}$ | Pulsed Source Current (Body Diode) ①⑥  | —                                                                           | —    | 240  |       |                                                                                                                                                      |
| $V_{SD}$ | Diode Forward Voltage                  | —                                                                           | —    | 1.5  | V     | $T_J = 25^\circ\text{C}, I_S = 36A, V_{GS} = 0V$ ④                                                                                                   |
| $t_{rr}$ | Reverse Recovery Time                  | —                                                                           | 140  | 210  | nS    | $T_J = 25^\circ\text{C}, I_F = 36A$                                                                                                                  |
| $Q_{rr}$ | Reverse Recovery Charge                | —                                                                           | 780  | 1170 | nC    | $di/dt = 100A/\mu s$ ④                                                                                                                               |
| $t_{on}$ | Forward Turn-On Time                   | Intrinsic turn-on time is negligible (turn-on is dominated by $L_S + L_D$ ) |      |      |       |                                                                                                                                                      |




Fig 1. Typical Output Characteristics




Fig 2. Typical Output Characteristics




Fig 3. Typical Transfer Characteristics










Fig 4. Normalized On-Resistance Vs. Temperature







**Fig 9.** Maximum Drain Current Vs. Case Temperature




**Fig 10a.** Switching Time Test Circuit




**Fig 10b.** Switching Time Waveforms




**Fig 11.** Maximum Effective Transient Thermal Impedance, Junction-to-Case




**Fig 12a.** Unclamped Inductive Test Circuit




**Fig 12b.** Unclamped Inductive Waveforms



**Fig 12c.** Maximum Avalanche Energy Vs. Drain Current





**Fig 13a.** Basic Gate Charge Waveform



**Fig 13b.** Gate Charge Test Circuit

### Peak Diode Recovery $dv/dt$ Test Circuit



\*  $V_{GS} = 5V$  for Logic Level Devices


**Fig 14.** For N-Channel HEXFET® Power MOSFETs

# IRFB52N15DPbF/IRFS52N15DPbF/IRFSL52N15DPbF

International  
**IR** Rectifier

## TO-220AB Package Outline

Dimensions are shown in millimeters (inches)



### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5 M- 1994.
2. DIMENSIONS ARE SHOWN IN INCHES (MILLIMETERS).
3. LEAD DIMENSION AND FINISH UNCONTROLLED IN L1.
4. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED .005" (0.127) PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
5. DIMENSION b1 & c1 APPLY TO BASE METAL ONLY.
6. CONTROLLING DIMENSION : INCHES.
7. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS E, H1, D2 & E1
8. DIMENSION E2 X H1 DEFINE A ZONE WHERE STAMPING AND SINGULATION IRREGULARITIES ARE ALLOWED.

### LEAD ASSIGNMENTS

#### HERFET

- 1.- GATE
- 2.- DRAIN
- 3.- SOURCE

#### IRBL CoPACK

- 1.- GATE
- 2.- COLLECTOR
- 3.- EMITTER

#### DIODES


- 1.- ANODE/OPEN
- 2.- CATHODE
- 3.- ANODE

| SYMBOL | DIMENSIONS  |       |          |      | NOTES |
|--------|-------------|-------|----------|------|-------|
|        | MILLIMETERS |       | INCHES   |      |       |
|        | MIN.        | MAX.  | MIN.     | MAX. |       |
| A      | 3.56        | 4.82  | .140     | .190 |       |
| A1     | 0.51        | 1.40  | .020     | .055 |       |
| A2     | 2.04        | 2.92  | .080     | .115 |       |
| b      | 0.38        | 1.01  | .015     | .040 |       |
| b1     | 0.38        | 0.96  | .015     | .038 | 5     |
| b2     | 1.15        | 1.77  | .045     | .070 |       |
| b3     | 1.15        | 1.73  | .045     | .068 |       |
| c      | 0.36        | 0.61  | .014     | .024 |       |
| c1     | 0.36        | 0.56  | .014     | .022 | 5     |
| D      | 14.22       | 16.51 | .560     | .650 | 4     |
| D1     | 8.38        | 9.02  | .330     | .355 |       |
| D2     | 12.19       | 12.88 | .480     | .507 | 7     |
| E      | 9.66        | 10.66 | .380     | .420 | 4,7   |
| E1     | 8.38        | 8.89  | .330     | .350 | 7     |
| e      | 2.54 BSC    |       | .100 BSC |      |       |
| e1     | 5.08        |       | .200 BSC |      |       |
| H1     | 5.85        | 6.55  | .230     | .270 | 7,8   |
| L      | 12.70       | 14.73 | .500     | .580 |       |
| L1     | -           | 6.35  | -        | .250 | 3     |
| øP     | 3.54        | 4.08  | .139     | .161 |       |
| Q      | 2.54        | 3.42  | .100     | .135 |       |
| ø      | 90°-93°     |       | 90°-93°  |      |       |

## TO-220AB Part Marking Information

EXAMPLE: THIS IS AN IRF1010  
LOT CODE 1789  
ASSEMBLED ON WW 19, 1997  
IN THE ASSEMBLY LINE "C"

Note: "P" in assembly line position  
indicates "Lead - Free"



TO-220 package is not recommended for Surface Mount Application.


### Notes:

1. For an Automotive Qualified version of this part please see <http://www.irf.com/product-info/auto/>
2. For the most current drawing please refer to IR website at <http://www.irf.com/package/>



## D<sup>2</sup>Pak Package Outline

Dimensions are shown in millimeters (inches)



### NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [0.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
4. DIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.
5. CONTROLLING DIMENSION: INCH.

| SYMBOL | DIMENSIONS  |       |          |      | NOTES |
|--------|-------------|-------|----------|------|-------|
|        | MILLIMETERS |       | INCHES   |      |       |
|        | MIN.        | MAX.  | MIN.     | MAX. |       |
| A      | 4.06        | 4.83  | .160     | .190 | 4     |
| A1     | 0.00        | 0.254 | .000     | .010 |       |
| b      | 0.51        | 0.99  | .020     | .039 |       |
| b1     | 0.51        | 0.89  | .020     | .035 |       |
| b2     | 1.14        | 1.78  | .045     | .070 | 4     |
| c      | 0.38        | 0.74  | .015     | .029 |       |
| c1     | 0.38        | 0.58  | .015     | .023 |       |
| c2     | 1.14        | 1.65  | .045     | .065 |       |
| D      | 8.51        | 9.65  | .335     | .380 | 3     |
| D1     | 6.86        |       | .270     |      |       |
| E      | 9.65        | 10.67 | .380     | .420 |       |
| E1     | 6.22        |       | .245     |      |       |
| e      | 2.54 BSC    |       | .100 BSC |      | 3     |
| H      | 14.61       | 15.88 | .575     | .625 |       |
| L      | 1.78        | 2.79  | .070     | .110 |       |
| L1     |             | 1.65  |          | .065 |       |
| L2     | 1.27        | 1.78  | .050     | .070 | 3     |
| L3     | 0.25 BSC    |       | .010 BSC |      |       |
| L4     | 4.78        | 5.28  | .188     | .208 |       |
| m      | 17.78       |       | .700     |      |       |
| m1     | 8.89        |       | .350     |      | 3     |
| n      | 11.43       |       | .450     |      |       |
| o      | 2.08        |       | .082     |      |       |
| p      | 3.81        |       | .150     |      |       |
| R      | 0.51        | 0.71  | .020     | .028 | 3     |
| θ      | 90°         | 93°   | 90°      | 93°  |       |

### LEAD ASSIGNMENTS

#### HEXFET

- 1.- GATE
- 2, 4.- DRAIN
- 3.- SOURCE

#### IGBTs, CoPACK

- 1.- GATE
- 2, 4.- COLLECTOR
- 3.- EMITTER

#### DIODES


- 1.- ANODE \*
- 2, 4.- CATHODE
- 3.- ANODE

\* PART DEPENDENT.


## D<sup>2</sup>Pak Part Marking Information

EXAMPLE: THIS IS AN IRF530S WITH  
LOT CODE 8024  
ASSEMBLED ON WW 02, 2000  
IN THE ASSEMBLY LINE "L"

Note: "P" in assembly line position  
indicates "Lead - Free"



OR



### Notes:


1. For an Automotive Qualified version of this part please see <http://www.irf.com/product-info/auto/>
2. For the most current drawing please refer to IR website at <http://www.irf.com/package/>

# IRFB52N15DPbF/IRFS52N15DPbF/IRFSL52N15DPbF

International  
**IR** Rectifier

## TO-262 Package Outline

Dimensions are shown in millimeters (inches)



| SYMBOL | DIMENSIONS  |       |          |      | NOTES |
|--------|-------------|-------|----------|------|-------|
|        | MILLIMETERS |       | INCHES   |      |       |
|        | MIN.        | MAX.  | MIN.     | MAX. |       |
| A      | 4.06        | 4.83  | .160     | .190 | 4     |
| A1     | 2.03        | 2.92  | .080     | .115 |       |
| b      | 0.51        | 0.99  | .020     | .039 |       |
| b1     | 0.51        | 0.89  | .020     | .035 |       |
| b2     | 1.14        | 1.40  | .045     | .055 | 4     |
| c      | 0.38        | 0.63  | .015     | .025 |       |
| c1     | 1.14        | 1.40  | .045     | .055 |       |
| c2     | 0.43        | .063  | .017     | .029 |       |
| D      | 8.51        | 9.65  | .335     | .380 | 3     |
| D1     | 5.33        |       | .210     |      |       |
| E      | 9.65        | 10.67 | .380     | .420 | 3     |
| E1     | 6.22        |       | .245     |      |       |
| e      | 2.54 BSC    |       | .100 BSC |      |       |
| L      | 13.46       | 14.09 | .530     | .555 |       |
| L1     | 3.56        | 3.71  | .140     | .146 |       |
| L2     |             | 1.65  |          | .065 |       |

### LEAD ASSIGNMENTS


HEXFET —IGBT  
1.— GATE 1- GATE  
2.— DRAIN  
3.— SOURCE  
4.— DRAIN

- NOTES:
1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994
  2. DIMENSIONS ARE SHOWN IN MILLIMETERS (INCHES)
  3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 (.005") PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
  4. DIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.
  5. CONTROLLING DIMENSION: INCH.


## TO-262 Part Marking Information

EXAMPLE: THIS IS AN IRL3103L  
LOT CODE 1789  
ASSEMBLED ON WW 19, 1997  
IN THE ASSEMBLY LINE "C"

Note: "P" in assembly line position  
indicates "Lead - Free"




OR



### Notes:

1. For an Automotive Qualified version of this part please see <http://www.irf.com/product-info/auto/>
2. For the most current drawing please refer to IR website at <http://www.irf.com/package/>

## D<sup>2</sup>Pak Tape & Reel Information



### Notes:

- ① 1% Duty cycle, 100 pulses, limited by max. junction temperature.
- ② Starting  $T_J = 25^\circ\text{C}$ ,  $L = 0.72\text{mH}$   
 $R_G = 25\Omega$ ,  $I_{AS} = 36\text{A}$ .
- ③  $I_{SD} \leq 36\text{A}$ ,  $di/dt \leq 400\text{A}/\mu\text{s}$ ,  $V_{DD} \leq V_{(BR)DSS}$ ,  
 $T_J \leq 175^\circ\text{C}$ .
- ④ Pulse width  $\leq 300\mu\text{s}$ ; duty cycle  $\leq 2\%$ .
- ⑤  $C_{OSS}$  eff. is a fixed capacitance that gives the same charging time as  $C_{OSS}$  while  $V_{DS}$  is rising from 0 to 80%  $V_{DSS}$ .
- ⑥ This is only applied to TO-220AB package.
- ⑦ This is applied to D<sup>2</sup>Pak, when mounted on 1" square PCB (FR-4 or G-10 Material). For recommended footprint and soldering techniques refer to application note #AN-994.

Data and specifications subject to change without notice.  
This product has been designed and qualified for the Industrial market.  
Qualification Standards can be found on IR's Web site.

International  
**IR** Rectifier

IR WORLD HEADQUARTERS: 233 Kansas St., El Segundo, California 90245, USA Tel: (310) 252-7105  
TAC Fax: (310) 252-7903

Visit us at [www.irf.com](http://www.irf.com) for sales contact information.09/2010