

Surface Mountable PTC Resettable Fuse



**RoHS
Compliant**




Specifications:


Terminal Pad Material	: Pure Tin
Soldering Characteristic	: Meets EIA specs. RS 186-9E, ANSI/J-std-002 Category 3
Series	: FSMD
PTC Fuse Case	: SMD
External Depth	: 1.35mm
External Length / Height	: 0.775mm
External Width	: 2.15mm
Operating Temperature	: -40°C to +85°C

Profile Feature	Pb-Free Assembly
Average Ramp-Up Rate (T _{smax} to T _p)	3°C/second max.
Preheat: Temperature Min. (T _{smin}) Temperature Max. (T _{smax}) Time (t _{smin} to t _{smax})	150°C 200°C 60-180 seconds
Time maintained above: Temperature (T _L) Time (t _L)	217°C 60-150 seconds
Peak/Classification Temperature (T_p)	260°C
Time within 5°C of actual Peak: Temperature (t _p)	20-40 seconds
Ramp-Down Rate:	6°C /second max.
Time 25°C to Peak Temperature:	8 minute max.

Typical Time-to-Trip at 23°C



Thermal Derating Curve




Hold Current	Trip Current	Max. Time-to-trip		Rated Voltage	Max. Current	Typical Power	Resistance Tolerance	
		Current	Time				R _{MIN}	R _{1MAX}
I _H , A	I _T , A	A	Sec	V _{MAX} , V DC	I _{MAX} , A	Pd, W	Ω	Ω
0.1	0.3	0.5	1.5	15	100	0.5	0.7	6


Surface Mountable PTC Resettable Fuse



Dimension




Pad Layout



Dimensions : Millimetres

Reflow Profile



Solder Reflow:

*Due to "Lead Free" nature, Temperature and Dwelling time for the soldering zone is higher than those for regular. This may cause damage to other components.

1. Recommended max past thickness > 0.25mm.
2. Devices can be cleaned using standard methods and aqueous solvent.
3. Rework use standard industry practices.
4. Storage Environment: < 30°C / 60%RH

Caution:

1. If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.
2. Devices are not designed to be wave soldered to the bottom side of the board.

Part Number Table

Description	Part Number
Fuse, Resettable, SMD, 0.1A	MC33186

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.