





LOC	DIST	REVISIONS					
AD	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			A1	REVISED PER ECO-07-024382	5/1/08	SS	MW



		Materials	
No.	Component name	Base material	Finish
1	Housing	ALKYD, GREEN, UL94 V-0	
2	End terminal	silver clad copper alloy	5 microinches min. gold
3	Center terminal	copper alloy	5 microinches min. gold
4	Rocker contact	silver clad copper alloy	5 microinches min. gold
5	Actuator	Phenol resin, UL94 HB, black	
6	Plunger	stainless steel	
7	Spring	music wire	
8	Toggle	brass	100 microinches min. bright nickel, electrodeposited
9	Retainer	Polyamide, UL94 HB, black	
10	Frame	STAINLESS STEEL	PASSIVATED
11	Bushing	Zinc	100 microinches min. nickel electrodeposited over 200 microinches min. copper
12	Mounting nuts (2)	brass	100 microinches min. bright nickel electrodeposited.
13	Locating ring	cold rolled steel	100 microinches min. bright nickel, electrodeposited
14	Internal tooth lockwasher	steel	100 microinches min. bright nickel, electrodeposited

Specifications-see note 3				
Current rating UL & CSA	6A @ 125 VAC (resistive) 3A @ 250 VAC (resistive) 4A @ 28 VDC (resistive)			
Termination resistance	20 milliohms max @ 2-4 VDC, 1A			
Insulation resistance	1,000 megohms min.			
Withstanding voltage	1,000 VAC			
Travel	24 +/-2 degrees			
Actuation force	.05 to 1.5 kgf			
Operating temperature	-20C to +85C			
Storage temperature	-40C to +85C			
Contact timing	break before make			
Terminal seal	epoxy			
Durability	Parameter	2 Position	3 Position	Momentary
	mechanical (no load)	150,000	100,000	80,000
	250 VAC (3A resistive)	80,000	60,000	60,000
	125 VAC (6A resistive)	80,000	60,000	60,000
	28 VDC (4A resistive)	60,000	50,000	40,000






NOT TO SCALE

	PART NUMBER	Alco P/N	Poles	Throws	Function	Terminal				Comments
	4-1571920-3	MTA406PPC04	4	2	ON OFF ON	PC	2-3, 5-6, 8-9, 11-12	OFF	2-1, 5-4, 8-7, 11-10	
	4-1571920-2	MTA406PAPC04	2	3	ON ON ON	PC	5-6, 11-12	5-3, 11-9	5-1, 11-7	note 7
	4-1571920-1	MTA406PA04	2	3	ON ON ON	Wire lug	5-6, 11-12	5-3, 11-9	5-1, 11-7	note 7
	4-1571920-0	MTA406P04	4	2	ON OFF ON	Wire lug	2-3, 5-6, 8-9, 11-12	OFF	2-1, 5-4, 8-7, 11-10	
	3-1571920-9	MTA406NPC04	4	2	ON ON	PC	2-3, 5-6, 8-9, 11-12	---	2-1, 5-4, 8-7, 11-10	
	3-1571920-8	MTA406N04	4	2	ON ON	Wire lug	2-3, 5-6, 8-9, 11-12	---	2-1, 5-4, 8-7, 11-10	
	3-1571920-7	MTA306HPC04	3	2	ON OFF(ON)	PC	2-3, 5-6, 8-9	OFF	2-1, 5-4, 8-7	
	3-1571920-6	MTA306H04	3	2	ON OFF(ON)	Wire lug	2-3, 5-6, 8-9	OFF	2-1, 5-4, 8-7	
	3-1571920-5	MTA306FPC04	3	2	ON (ON)	PC	2-3, 5-6, 8-9	---	2-1, 5-4, 8-7	
	3-1571920-4	MTA306F04	3	2	ON (ON)	Wire lug	2-3, 5-6, 8-9	---	2-1, 5-4, 8-7	
	3-1571920-3	MTA306EPC04	3	2	ON OFF ON	PC	2-3, 5-6, 8-9	OFF	2-1, 5-4, 8-7	
	3-1571920-2	MTA306E04	3	2	ON OFF ON	Wire lug	2-3, 5-6, 8-9	OFF	2-1, 5-4, 8-7	
	3-1571920-1	MTA306DPC04	3	2	ON ON	PC	2-3, 5-6, 8-9	---	2-1, 5-4, 8-7	
	3-1571920-0	MTA306D04	3	2	ON ON	Wire lug	2-3, 5-6, 8-9	---	2-1, 5-4, 8-7	
△	2-1571920-9	MTA206TPC04	2	2	ON OFF(ON)	PC	2-3, 5-6	OFF	2-1, 5-4	
	2-1571920-8	MTA206TA04	1	3	ON ON (ON)	Wire lug	5-6	5-3	5-1	note 6
	2-1571920-7	MTA206T04	2	2	ON OFF(ON)	PC	2-3, 5-6	OFF	2-1, 5-4	
△	2-1571920-6	MTA206SPC04	2	2	(ON) OFF (ON)	Wire lug	2-3, 5-6	OFF	2-1, 5-4	
△	2-1571920-5	MTA206SAPC04	1	3	(ON) ON (ON)	PC	5-6	5-3	5-1	note 6
	2-1571920-4	MTA206SA04	1	3	(ON) ON (ON)	Wire lug	5-6	5-3	5-1	note 6
	2-1571920-3	MTA206S04	2	2	(ON) OFF (ON)	Wire lug	2-3, 5-6	OFF	2-1, 5-4	
	2-1571920-2	MTA206RPC04	2	2	ON (ON)	PC	2-3, 5-6	---	2-1, 5-4	
	2-1571920-1	MTA206R04	2	2	ON (ON)	Wire lug	2-3, 5-6	---	2-1, 5-4	
	2-1571920-0	MTA206PPC04	2	2	ON OFF ON	PC	2-3, 5-6	OFF	2-1, 5-4	
	1-1571920-9	MTA206PAPC04	1	3	ON ON ON	PC	5-6	5-3	5-1	note 6
	1-1571920-8	MTA206PA04	1	3	ON ON ON	Wire lug	5-6	5-3	5-1	note 6
	1-1571920-7	MTA206P04	2	2	ON OFF ON	Wire lug	2-3, 5-6	OFF	2-1, 5-4	
	1-1571920-6	MTA206NPC04	2	2	ON ON	PC	2-3, 5-6	---	2-1, 5-4	
	1-1571920-5	MTA206N04	2	2	ON ON	Wire lug	2-3, 5-6	---	2-1, 5-4	
OBSOLETE	1-1571920-4	MTA206KPC04	2	1	ON OFF	PC	2-3, 5-6	---	OFF	
OBSOLETE	1-1571920-3	MTA206K04	2	1	ON OFF	Wire lug	2-3, 5-6	---	OFF	
	1-1571920-2	MTA106HPC04	1	2	ON OFF(ON)	PC	2-3	OFF	2-1	
	1-1571920-1	MTA106H04	1	2	ON OFF(ON)	Wire lug	2-3	OFF	2-1	
	1-1571920-0	MTA106GPC04	1	2	(ON) OFF (ON)	PC	2-3	OFF	2-1	
	1571920-9	MTA106G04	1	2	(ON) OFF (ON)	Wire lug	2-3	OFF	2-1	
	1571920-8	MTA106FPC04	1	2	ON (ON)	PC	2-3	---	2-1	
	1571920-7	MTA106F04	1	2	ON (ON)	Wire lug	2-3	---	2-1	
	1571920-6	MTA106EPC04	1	2	ON OFF ON	PC	2-3	OFF	2-1	
	1571920-5	MTA106E04	1	2	ON OFF ON	Wire lug	2-3	OFF	2-1	
	1571920-4	MTA106DPC04	1	2	ON ON	PC	2-3	---	2-1	
	1571920-3	MTA106D04	1	2	ON ON	Wire lug	2-3	---	2-1	
OBSOLETE	1571920-2	MTA106APC04	1	1	ON OFF	PC	2-3	---	OFF	
OBSOLETE	1571920-1	MTA106A04	1	1	ON OFF	Wire lug	2-3	---	OFF	





- NOTES:
1. TERMINAL NUMBERS ARE FOR REFERENCE ONLY AND DO NOT APPEAR ON THE SWITCHES.
 2. EACH SWITCH SUPPLIED WITH THE FOLLOWING MOUNTING HARDWARE:
 - (2) 1/4-40 UNS-2B HEX NUTS
 - (1) INTERNAL TOOTH LOCKWASHER
 - (1) LOCATING RING
 3. SWITCHES TESTED TO AND MEET THE REQUIREMENTS OF UL 61058-1A, SWITCHES FOR APPLIANCES SWITCHES WILL ALSO BE TESTED TO AND MEET THE REQUIREMENTS OF TE 102-2469, REV 0, MINIATURE SWITCH QUALIFICATION REQUIREMENTS.
SWITCHES ARE PENDING UL RECOGNITION TO US AND CANADIAN STANDARDS.
 4. WIRE LUG CONTACTS WILL ACCEPT 2 #20 AWG SOLID OR STRANDED WIRES.
 5. CUSTOMER INSTALLED EXTERNAL JUMPER BETWEEN TERMINALS 2 AND 4 REQUIRED FOR 1 POLE 3 THROW FUNCTION.
 6. CUSTOMER INSTALLED EXTERNAL JUMPERS BETWEEN TERMINALS 2 AND 4 AS WELL AS 8 AND 10 REQUIRED FOR 2 POLE 3 THROW FUNCTION.
 7. SWITCHES ARE MARKED PER TE SPEC 202-37 WITH ALCO BENEATH LOGO AS SHOWN.
 8. ALL MATERIALS AND FINISHES SHALL COMPLY WITH EU DIRECTIVE 2002/95/EC OF 27JAN2003 (ROHS).

LOC	DIST	REVISIONS				
AD	00	REV	LTR	DESCRIPTION	DATE	DWN
		—	—	SEE SHEET 1	—	—




MTA106


MTA206




PC TERMINAL



DETAIL A
SCALE 16:1



DETAIL B
SCALE 16:1



WIRE LUG TERMINAL

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN BSV	02DEC2005	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK	—		
DIMENSIONS: INCHES	TOLERANCES UNLESS OTHERWISE SPECIFIED:	APVD M. ZITTO	29DEC03	NAME	ALCOSWITCH GREEN SERIES TOGGLE SWITCH MTA VERTICAL MOUNT
	0. PLC ± — 1. PLC ± — 2. PLC ± — 3. PLC ± .005 4. PLC ± — ANGLES ± 1	PRODUCT SPEC	—	APPLICATION SPEC	—
MATERIAL	FINISH	WEIGHT	—	SIZE	CAGE CODE
—	—	—	—	A1	00779
CUSTOMER DRAWING		SCALE	4:1	SHEET	2 OF 3
		REV	A1		

