



Dimensions are in millimeters

Shell size	Number of contacts	A ^{+0.76} ₀	B ^{+0.25} ₀	C ^{±0.12}	F ^{+0.51} ₀	G	H ^{+0.51} ₀	L ^{+0.22} ₀	Part number
E	09	30.43	16.79	24.99	10.47	5.90 ^{+0.15} ₀	19.02	0.80	DEMF09P052
A	15	38.76	25.12	33.32	10.47	5.90 ^{+0.15} ₀	27.25	0.80	DAMF15P052
B	25	52.65	38.84	47.04	10.43	5.70 ^{+0.25} ₀	41.02	0.80	DBMF25P052
C	37	68.94	55.30	63.50	10.56	5.70 ^{+0.25} ₀	57.45	1.00	DCMF37P052

0 10 20 30 MM

ELECTRICAL DATA

-I max	7.5A
-Contact resistance	≤55mΩ under 7.5 A
-Insulation resistance	≥5000MΩ
-TEST VOLTAGE	
contact/contact	≥1000V
contact/ground	≥1200V

MECHANICAL DATA

-Contact force	≥0.20N
-Retention force	≥40N
-Insertion force	according to MIL-DTL-24308
-Withdrawal force	according to MIL-DTL-24308
-Mechanical endurance	:500 matings / unmatings
-Material shell	steel ,cadmium
-Material insulator	glass filled thermoplastic UL94V0
-Material contacts	socket:brass.
-Finish on contact area	gold 50μ inch min over nickel 30-150μinch min
-Finish on termination end	tin-lead 100μinch min over nickel 30-180μinch min
-Solderability	according to MIL-DTL-24308
-Shock	according to MIL-DTL-24308
-Vibration	according to MIL-DTL-24308

ENVIRONMENTAL DATA

-Climatic category	-55°/ +125°/56
-Corrosion	salt spray:48h

A	28/07/03	First issue	--
ISS	DATE	Latest modification by : M PESSON	MOD N°
Designed by: PESSON date:2/07/03			Type of drawing: CLIENT
TITLE : PIN CONNECTORS D SUB WITH SOLDER TAILS and FLOAT MOUNTING			SHEET 01
SCALE: 1.5			
		FRAMATOME CONNECTORS FRANCE Rue Louis Breguet - BP 05 72024 LE MANS Cedex Tel. 33 (16) 43.84.08.43	
This document is the property of FRAMATOME CONNECTORS FRANCE It must not be reproduced or communicated without permission in writing from the owners			
FORMAT A3	SOURIAU DRG N° C01-8637-1622		PROJECT M94D001