

PQ5EV3/PQ5EV5/PQ5EV7

Large Output Current Type Low Power-Loss Voltage Regulator

■ Features

- Low power-loss (Dropout voltage: MAX.0.5V)
- Package with exposed radiation fin (Equivalent to TO-220)
- Large output current
3.5A: PQ5EV3, 5A: PQ5EV5, 7.5A: PQ5EV7
- Variable output voltage (1.5V to 5V)
- High-precision reference voltage type
(Reference voltage precision: $\pm 1.0\%$)
- Overcurrent, overheat protection functions

■ Applications

- Personal computers
- Power supplies for various electronic equipment such as AV or OA

■ **Absolute Maximum Ratings** (Ta=25°C)

Parameter		Symbol	Rating	Unit
① Input voltage		V_{IN}	7	V
Dropout voltage		V_{I-O}	4	V
① ON/OFF control terminal voltage		V_C	7	V
① Output adjustment terminal voltage		V_{ADJ}	5	V
Output current	PQ5EV3	I_O	3.5	A
	PQ5EV5		5.0	
	PQ5EV7		7.5	
② Power dissipation		P_{D1}	1.6	W
		P_{D2}	45	W
③ Junction temperature		T_j	150	°C
Operating temperature		T_{opr}	−20 to +80	°C
Storage temperature		T_{stg}	−40 to +150	°C
④ Soldering temperature		T_{sol}	260 (10s)	°C


*1 All are open except GND and applicable terminals

*2 P_{D1}:No heat sink, P_{D2}:With infinite heat sink

※3 Overheat protection may operate at the condition $T_i=125^{\circ}\text{C}$ to 150°C

■ Outline Dimensions

(Unit : mm)



- Please refer to the chapter " Handling Precautions ".

SHARP

Notice	In the absence of confirmation by device specification sheets, SHARP takes no responsibility for any defects that may occur in equipment using any SHARP devices shown in catalogs, data books, etc. Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device.
Internet	Internet address for Electronic Components Group http://sharp-world.com/ec/

Electrical Characteristics

(Unless otherwise specified, $V_{IN}=5V$, $V_O=3V$ ($R_1=2k\Omega$), $T_a=25^\circ C$)

Parameter	Symbol	Conditions	MIN.	TYP.	MAX.	Unit
Input voltage	V_{IN}	—	2.35	—	7	V
Output voltage	V_O	—	1.5	—	5	V
Reference voltage	V_{ref}	—	1.2276	1.24	1.2524	V
Load regulation	R_{egL}	$I_O=5mA$ to rating	—	0.1	0.5	%
Line regulation	R_{egI}	$V_{IN}=4$ to $7V$, $I_O=5mA$	—	0.05	0.1	%
Reference voltage temperature coefficient	$T_C V_{ref}$	$T_J=0$ to $125^\circ C$	—	± 1	—	%
Ripple Rejection	RR	Refer to Fig.2	60	70	—	dB
Dropout voltage	V_{I-O}	※5	—	—	0.5	V
※6 ON-state voltage for control	$V_C(ON)$	—	2	—	—	V
ON-state current for control	$I_C(ON)$	$V_C=2.7V$	—	—	20	μA
OFF-state voltage for control	$V_C(OFF)$	—	—	—	0.8	V
OFF-state current for control	$I_C(OFF)$	$V_C=0.4V$	—	—	-0.4	mA
Quiescent current	I_q	$I_O=0A$	—	10	15	mA

※4 PQ5EV3: $I_O=1.75A$, PQ5EV5: $I_O=2.5A$, PQ5EV7: $I_O=3.75A$

※5 PQ5EV3: $I_O=3.5A$, PQ5EV5: $I_O=5A$, PQ5EV7: $I_O=7.5A$. Input voltage shall be the value when output voltage is 95% in comparison with the initial value

※6 In case of opening control terminal ⑤, output voltage turns on.

Fig.1 Test Circuit




Fig.2 Test Circuit for Ripple Rejection




Fig.3 Power Dissipation vs. Ambient Temperature





Fig.4 Overcurrent Protection Characteristics (PQ5EV3)



Note) Oblique line portion:Overheat protection may operate in this area

Fig.5 Overcurrent Protection Characteristics (PQ5EV5)




Fig.6 Overcurrent Protection Characteristics (PQ5EV7)




Fig.7 Reference Voltage Fluctuation vs. Junction Temperature




Fig.8 Output Voltage vs. Input Voltage (PQ5EV3)




Fig.9 Output Voltage vs. Input Voltage (PQ5EV5)




Fig.10 Output Voltage vs. Input Voltage (PQ5EV7)




Fig.11 Circuit Operating Current vs. Input Voltage (PQ5EV3)




Fig.12 Circuit Operating Current vs. Input Voltage (PQ5EV5)




Fig.13 Circuit Operating Current vs. Input Voltage (PQ5EV7)




Fig.14 Dropout Voltage vs. Junction Temperature




Fig.15 ON-OFF Threshold Voltage vs. Junction Temperature




Fig.16 Quiescent Current vs. Junction Temperature




Fig.17 Ripple Rejection vs. Input Ripple Frequency




Fig.18 Output Voltage Adjustment Characteristics






Fig.19 External Connection



Setting of Output Voltage

Output voltage is able to set (1.5V to 5V) when resistors R_1 , R_2 are attached to ②, ③, ④ terminals. As for the external resistors to set output voltage, refer to the following figure and Fig.18.



NOTICE

- The circuit application examples in this publication are provided to explain representative applications of SHARP devices and are not intended to guarantee any circuit design or license any intellectual property rights. SHARP takes no responsibility for any problems related to any intellectual property right of a third party resulting from the use of SHARP's devices.
- Contact SHARP in order to obtain the latest device specification sheets before using any SHARP device. SHARP reserves the right to make changes in the specifications, characteristics, data, materials, structure, and other contents described herein at any time without notice in order to improve design or reliability. Manufacturing locations are also subject to change without notice.
- Observe the following points when using any devices in this publication. SHARP takes no responsibility for damage caused by improper use of the devices which does not meet the conditions and absolute maximum ratings to be used specified in the relevant specification sheet nor meet the following conditions:
 - (i) The devices in this publication are designed for use in general electronic equipment designs such as:
 - Personal computers
 - Office automation equipment
 - Telecommunication equipment [terminal]
 - Test and measurement equipment
 - Industrial control
 - Audio visual equipment
 - Consumer electronics
 - (ii) Measures such as fail-safe function and redundant design should be taken to ensure reliability and safety when SHARP devices are used for or in connection with equipment that requires higher reliability such as:
 - Transportation control and safety equipment (i.e., aircraft, trains, automobiles, etc.)
 - Traffic signals
 - Gas leakage sensor breakers
 - Alarm equipment
 - Various safety devices, etc.
 - (iii) SHARP devices shall not be used for or in connection with equipment that requires an extremely high level of reliability and safety such as:
 - Space applications
 - Telecommunication equipment [trunk lines]
 - Nuclear power control equipment
 - Medical and other life support equipment (e.g., scuba).
- Contact a SHARP representative in advance when intending to use SHARP devices for any "specific" applications other than those recommended by SHARP or when it is unclear which category mentioned above controls the intended use.
- If the SHARP devices listed in this publication fall within the scope of strategic products described in the Foreign Exchange and Foreign Trade Control Law of Japan, it is necessary to obtain approval to export such SHARP devices.
- This publication is the proprietary product of SHARP and is copyrighted, with all rights reserved. Under the copyright laws, no part of this publication may be reproduced or transmitted in any form or by any means, electronic or mechanical, for any purpose, in whole or in part, without the express written permission of SHARP. Express written permission is also required before any use of this publication may be made by a third party.
- Contact and consult with a SHARP representative if there are any questions about the contents of this publication.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Sharp Microelectronics:](#)

[PQ5EV7J0000H](#)