



Schnitt A-A / cross section A-A



Schichtaufbau im metallisierten Loch für Einpressbolzen siehe Zeichnung 114109
metal plating of plated-through hole for press-fit bolt see drawing 114109

* zusätzliche Befestigung auf der LP erforderlich
additional fastening on the PCB required

Ident-Nr. / Part No. : Refer to table on page 2

Polzahl / No. of contacts : Refer to table on page 2

Anschlußart / Terminal Type : Pressfit, Pressfit zone EE 2.5 mm

Anschlußlänge / Terminal Length : Refer to table on page 2

Bauart / Type : 7

Anforderungsstufe / Class : 207=0.8µm (30 µin) Au CONTACT, TIN/LEAD TERMINAL

Aufdruck / Logo : ERNI

Zubehör / Accessory : Refer to table on page 2

Sonderausführung / Special : Refer to table on page 2

9	30.8	16.8	25.0	8.3	12.5	10.8	5.8	19.3	10.8		0.8		
15	39.1	25.1	33.3	8.3	12.5	10.8	5.8	27.5	10.8		0.8		
25	53.0	38.9	47.0	8.3	12.5	10.8	5.8	41.3	10.8		0.8		
37	69.3	55.3	63.5	8.3	12.5	10.8	5.8	57.7	10.8		0.8		
50	67.0	52.7	61.1	11.0	15.4	10.8	5.8	55.3	13.6		0.9		
Polzahl/ No. of contacts	A ±0.3	B +0.2	C ±0.2	D +0.2	E ±0.3	F ±0.2	G +0.3	H ±0.3	J ±0.2		L ±0.1		

Fehlende Masse und Angaben siehe DIN 41652 /				Missing information and dimensions according to DIN 41652			
Sonstige Angaben siehe Fertigungsunterlagen /				Additional indications please see the production documentation			
Information:			Tolerances	 All Dimensions in mm	Scale	2:1	
All rights reserved. Only for information. To insure that this is the latest version of this drawing, please contact one of the ERNI companies before using.			Subject to modification without prior notice. Drawing will not be updated.		Designation TMC-P 9 bis 50-EE25-4.5 TMC-P 9 to 50-EE25-4.5		
						Elektroapparate GmbH D-73099 ADELBERG	
g		28.06.200			MCP		
Index		Date		M-00020886.SZN			

Ordering Information

D-Sub Connector Pressfit Vertical Male Assembly Height 6.3 mm

Number of Pins


9

15

25

37

50



Accessory Termination Side: Pressfit bolt M3

053954

053955

053956

053957

114073

Accessory Termination Side: Pressfit bolt #4-40


063411

063410

063409

063412

114074



Accessory Mating Side: Threaded sleeve M3 Accessory Termination Side: Pressfit bolt

054762

054763

054764

054765

054766

Accessory Mating Side: Threaded sleeve #4-40 Accessory Termination Side: Pressfit bolt


044950

044951

044952

044953

044954



Accessory Termination Side: Rivet nut M3

024965

024966

024967

024968

024969

Accessory Termination Side: Rivet nut #4-40


043310

043309

044524

063042

033698



Accessory Mating Side: Sleeve Accessory Termination Side: Threaded bolt M3

033536

033537

033538

033539

033540

Accessory Mating Side: Sleeve Accessory Termination Side: Threaded bolt #4-40


043420

043421

044525

043728

043422



Accessory Mating Side: Sleeve Accessory Termination Side: Threaded bolt M3 / #4-40


033531

033532

033533

033534

033535



Accessory Termination Side: Standoff

033696

033697

033373

063041

063040