

D-Series




The D-Series toggle switches are single pole and have ratings up to 20 amps and 1-1/2 horsepower. These switches have a nylon toggle and base, and are also available with integrated wire leads.

Specifications


- Certifications*: UL, CSA
- Dielectric Strength: 1,000 V (minimum)
- Insulation Resistance: 100 Megohms (minimum)
- Base Material: Nylon
- Actuator Material: Nylon
- Bushing Material: Polycarbonate

* Due to ongoing technological advances, consult factory for certification specifics.

Dimensional Specifications: in. [mm]



 .156[3.96] DIA .375[9.52] .250[6.35] SOLDER LUG	 .069[1.75] DIA .250[6.35] .250 TAB (Q.C.)	 6.000[152.4] .500[12.70] INTEGRATED WIRE LEAD (no exposed conductors)
TERMINAL TYPE		



D	A	22	1	-	P	B	-	B
SERIES	RATING		TERMINATION		TOGGLE STYLE		TOGGLE COLOR ¹	
D SINGLE POLE TOGGLE	10 5A 250VAC 10A 125VAC 1/2HP 125-250VAC		0 SOLDER LUG 1 .250TAB (QC) 5 WIRE LEAD		B BAT 	B BLACK W WHITE		
CIRCUIT	11 5A 250VAC 10A 125VAC				P PADDLE 	BUSHING ¹		
A ON-NONE-OFF	22 10A 250VAC 20A 125VAC 1 1/2HP 125-250VAC					B BLACK W WHITE		
B ON-NONE-ON	23 10A 250VAC 20A 125VAC							
C ON-OFF-ON	60 3A 250VAC 6A 125VAC 1/4HP 125-250VAC							

NOTES:
Shading indicates standard configurations.
Available with neoprene seal. Consult factory.
1 Custom colors are available. Consult factory.