

Type 2 surge protection replacement module - VAL-SQ SE 120-480D-R - 2804212

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Replacement module, 120 kA surge protection, 480 V Delta system

Product Description

Surge protection device for 480 V AC Delta configurations with 120 kA protection

Key Commercial Data

Packing unit	1 pc
Weight per Piece (excluding packing)	3,683.400 g
Custom tariff number	85363010
Country of origin	United States

Technical data

Ambient conditions

Ambient temperature (operation)	-40 °C ... 60 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Altitude	3658 m

General

NEMA power supply system	480 V Delta
Type	Parallel MOV
Direction of action	3L-N & N-GND

Protective circuit

Maximum continuous operating voltage U_c	640 V
Response time t_A	< 1 ns

Connection, protective circuit

Connection method	Screw terminal blocks
Tightening torque	4 Nm

Type 2 surge protection replacement module - VAL-SQ SE 120-480D-R - 2804212

Technical data

Connection, protective circuit


Conductor cross section AWG min.	10
Conductor cross section AWG max.	2

NEMA / UL data

Maximum Surge Current per Phase	120 kA
Short-circuit current rating (SCCR)	200 kA

Drawings

Circuit diagram



Classifications

eCl@ss

eCl@ss 4.0	27140201
eCl@ss 4.1	27140201
eCl@ss 5.0	27140201
eCl@ss 5.1	27140201
eCl@ss 6.0	27140201
eCl@ss 8.0	27130802
eCl@ss 9.0	27130802

Type 2 surge protection replacement module - VAL-SQ SE 120-480D-R - 2804212

Classifications

ETIM

ETIM 2.0	EC000381
ETIM 3.0	EC000381
ETIM 4.0	EC000381
ETIM 5.0	EC000381

UNSPSC

UNSPSC 6.01	30212010
UNSPSC 7.0901	39121610
UNSPSC 11	39121610
UNSPSC 12.01	39121610
UNSPSC 13.2	39121620