


REV	DOCUMENT	CHANGED BY	CHECK
8	0038091	VS 28APR08	BLR



①-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .087 MAX DIA ON .375 $\pm$.002 CENTERS
2-TERMINALS ARE PLATED FOR SOLDERING
3-MATING CONTACT SURFACES ARE 24 K SOLID GOLD OVERLAY
4-SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

RELEASE NO.	-
REPLACES	-

CHARACTERISTICS		ELECTRICAL DATA			DESIGN UNITS: INCH			DRAWN	VK	27 NOV 07		Honeywell				
OPERATING FORCE – – – – 3-5 OZ		CONTACT ARRANGEMENT S P D T			TOLERANCES UNLESS NOTED:			CHECK	RJ	27 NOV 07						
RELEASE FORCE – – – – – 1 OZ MIN		30 VOLTS DC RATING			NO PLACE X ±			THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH - BASIC				
					ONE PLACE .X ± 0.030											
DIFFERENTIAL TRAVEL – – – .004 MAX		INDUCTIVE 1/2 AMP 1/2 AMP			TWO PLACE .XX ± 0.015											
OVERTRAVEL – – – – – .005 MIN		RESISTIVE 1 AMP 1 AMP			THREE PLACE .XXX ± 0.005											
		MAXIMUM INRUSH 2 AMP			FOUR PLACE .XXXX ±			INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	DRAWING NAME		REV
APPROVALS	KEMA, CE	1A, 250V ~ T85 1E4			THIRD ANGLE PROJECTION 		B					I	11SM76-T		8	
	UL, CSA	1A, 125 VAC														BRAND L 22
							RASTER				SCALE -	WEIGHT .006 LB MAX	SHEET 1 OF 1			