


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	REVISED PER ECN-25-354023	18NOV2025	SN	DR



- 1 WIRE RANGE IS FOR 8 AWG STANDARD WIRE CROSS SECTIONAL AREA RANGE: 13,100-20,800 CMA, STRANDED WIRE
- 2 TERMINAL BODY MATERIAL THK IS 1.219±0.076[0.048±0.003]
- 3 RECOMMENDED OPERATING TEMP -65°C [-85°F] TO +200°C [392°F] FOR HEAT SHRINK TUBING
- 4 HEAT SHRINK TUBING SHELF LIFE OF 144 MONTHS FROM DATE CODE ON LABEL
- 5 TERMINAL BODY PRODUCT SPECIFICATION 108-32046 APPLICATION SPECIFICATION 114-2162

1	8-1190141-0	HIGH AND LOW TEMPERATURE CROSS LINKED FLUOROPOLYMER HEAT SHRINK TUBING 9.53[0.375]MIN IDX25.400±2.032[1.000±0.080] RT555-3/8-0-SP
1	323165	TERMINAL BODY: COPPER PER ASTM B152 ANNEALED FINISH: NICKEL PLATE 0.00762[0.000300] MIN EXT THK PER SAE AMS QQ-N-290
QTY	PART NO	DESCRIPTION

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 30JAN04	TE Connectivity		
DIMENSIONS: mm [INCHES]		CHK MJ SPICER 08APR04			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± 0.127 [0.005] 4 PLC ± - ANGLES ± 1°	APVD MJ SPICER 08APR04	NAME -		
		PRODUCT SPEC	HEAT RESISTANT TERMINAL KIT WIRE SIZE: 8 AWG		
		APPLICATION SPEC	SIZE CAGE CODE DRAWING NO RESTRICTED TO		
MATERIAL SEE TABLE	FINISH SEE TABLE	WEIGHT -	A300779C-696633		
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 1	REV D	