










AK 120






AK 122






AK 123



AK 161





AK 162






Technical drawing of a rectangular plate with dimensions and mounting holes. The drawing shows a top view of the plate with a central dashed red line indicating the center. The dimensions are as follows:




- Overall width: 360
- Inner width: 318
- Overall height: 160
- Inner height: 149
- Distance from top edge to first hole: 88
- Distance between holes: 76
- Distance from bottom edge to last hole: 110
- Overall distance from top edge to last hole: 140
- Overall distance from left edge to first hole: 332
- Overall distance from left edge to last hole: 340
- Overall distance from left edge to last hole: 349
- Mounting holes are labeled M6.






AK 231



AK 232



AK 234



AK 311

