




LTC-3710 SERIES

0.3" FOUR LED CLOCK FREQUENCY DISPLAYS

T.4133

FEATURES

- 0.3 INCH (7.62mm) DIGIT HEIGHT.
- CONTINUOUS UNIFORM SEGMENTS.
- CHOICE OF SIX BRIGHT COLORS RED/BRIGHT RED/GREEN/YELLOW/ORANGE/HIGH EFFICIENCY RED.
- LOW POWER REQUIREMENT.
- EXCELLENT CHARACTERS APPEARANCE.
- HIGH CONTRAST.
- HIGH BRIGHTNESS.
- WIDE VIEWING ANGLE.
- SOLID STATE RELIABILITY.
- CATEGORIZED FOR LUMINOUS INTENSITY.
- I.C. COMPATIBLE.
- EASY MOUNTING ON P.C. BOARD OR SOCKETS.



DESCRIPTION

The LTC-3710 series devices are 0.3 inch (7.62mm) height four digit displays.

The red series devices utilize LED chips which are made from GaAsP on a GaAs substrate. The bright red and green series devices utilize LED chips which are made from GaP on a transparent GaP substrate. The yellow, orange and high efficiency red series devices utilize LED chips which are made from GaAsP on a transparent GaP substrate. Red and bright red displays have black face and red segment color. Green, and orange displays have black face and white segment color. Yellow displays have black face and yellow segment color. High efficiency red displays have red face and red segment color.

DEVICES


PART NO. LTC-						DESCRIPTION
RED	BRIGHT RED	GREEN	YELLOW	ORANGE	HI-EFF. RED	
3710R	3710P	3710G	3710Y	3710E	3710HR	Multiplex, Common Cathode
3718R	3718P	3718G	3718Y	3718E	3718HR	Multiplex, Common Cathode



T-41-33

PACKAGE DIMENSIONS

A. LTC-3710 Series




NOTE: All dimensions are in millimeters (inches) tolerance are:

1. Lead length (from setting plane) MINIMUM VALUE $\frac{+1.00}{-0.00}$ mm $\frac{+.040}{-.000}$ in. 2. $\frac{\pm 0.25}{(0.010)}$ mm unless otherwise noted.

PIN NO.	CONNECTION	PIN NO.	CONNECTION
1	Anode L3	13	Cathode U.D.P.
2	Common Cathode Digit 1	14	Cathode D.P. 2.
3	Anode D, Digit 1, 2, 3, 4	15	Anode U.D.P.
4	Anode L2	16	Cathode D.P.I.
5	Common Cathode, Digit 2	17	Anode A, Digit 1, 2, 3, 4
6	Cathode UC, LC	18	Anode F, Digit 1, 2, 3, 4
7	Anode UC, LC	19	Anode B, Digit 1, 2, 3, 4
8	Common Cathode, Digit 3	20	Anode C, Digit 1, 2, 3, 4
9	Anode D.P.I.	21	Anode E, Digit 1
10	Common Cathode, Digit 4	22	Anode G, Digit 1, 2, 3, 4
11	Anode E, Digit 2, 3, 4	23	Anode L1
12	Anode D.P.2	24	Cathode L1, L2, L3

PACKAGE DIMENSIONS

B. LTC-3718 Series



NOTE: All dimensions are in millimeters (inches) tolerance are:


1. Lead length (from setting plane): MINIMUM VALUM $\frac{+1.00}{-0.00}$ mm 2. $\frac{\pm 0.25 \text{ mm}}{(0.010")}$ unless otherwise noted.

PIN NO.	CONNECTION	PIN NO.	CONNECTION
1	ANODE D1	13	ANODE G
2	ANODE D3	14	COMMON CATHODE DIGIT 4
3	COMMON CATHODE DIGIT 1	15	ANODE B
4	ANODE D	16	ANODE A
5	ANODE 3	17	ANODE F
6	CATHODE UC, LC	18	ANODE UC, LC
7	COMMON CATHODE DIGIT 3	19	COMMON CATHODE DIGIT 2
8	ANODE D.P.	20	ANODE E
9	CATHODE D.P.	21	ANODE D2
10	ANODE D6	22	ANODE 4
11	ANODE D5	23	CATHODE D2, D4
12	CATHODE D5, D6	24	CATHODE D1, D3.




INTERNAL CIRCUIT DIAGRAM

LTC-3710 Series



LTC-3718 Series



ABSOLUTE MAXIMUM RATINGS

PARAMETER	RED	BRIGHT RED	GREEN	YELLOW	ORANGE	HI-EFF. RED	UNIT
Power Dissipation Per Segment	45	30	60	50	60	60	mW
Peak Forward Current Per Segment (1/10 Duty Cycle, 0.1ms Pulse Width)	120	40	80	60	80	80	mA
Continuous Forward Current Per Segment	20	12	20	20	16	20	mA
Derating Linear From 25°C Per Segment	0.24	0.14	0.24	0.2	0.24	0.24	mA/°C
Reverse Voltage Per Segment	5	5	5	5	5	5	V
Operating Temperature Range	-25°C to +85°C						
Storage Temperature Range	-25°C to +85°C						
Solder Temperature 1/16 inch Below Seating Plane for 3 Seconds at	260°C						

ELECTRICAL/OPTICAL CHARACTERISTICS AT TA = 25°C
LTC-3710R

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	IV	200	450		μcd	IF = 10 mA
Peak Emission Wavelength	λp		655		nm	IF = 20 mA
Spectral Line Half-Width	Δλ		24		nm	IF = 20 mA
Forward Voltage any Segment or D.P.	VF		1.7	2.0	V	IF = 20 mA
Reverse Current, any Segment or D.P.	IR			100	μA	VR = 5 V
Luminous Intensity Matching Ratio	IV-m			2:1		IF = 20 mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE%. (REFRESH RATE = F = 1 KHz)




Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE% (AVERAGE If = 10mA PER SEG.)



ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ C$
LTC-3710P

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	250	600		μ cd	$I_F = 10$ mA
Peak Emission Wavelength	λ_p		697		nm	$I_F = 20$ mA
Spectral Line Half-Width	$\Delta\lambda$		90		nm	$I_F = 20$ mA
Forward Voltage any Segment or D.P.	V_F		2.1	2.8	V	$I_F = 20$ mA
Reverse Current, any Segment or D.P.	I_R			100	μ A	$V_R = 5$ V
Luminous Intensity Matching Ratio	$I_v:m$			2:1		$I_F = 20$ mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

($25^\circ C$ Ambient Temperature Unless Otherwise Noted)




Fig.1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig.4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig.5 MAX. PEAK CURRENT Vs. DUTY CYCLE%. (REFRESH RATE = F = 1 KHz)




Fig.6 LUMINOUS INTENSITY Vs. DUTY CYCLE% (AVERAGE $I_F = 10$ mA PER SEG.)

ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ C$
LTC-3710G

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	750	1800		μ cd	$I_F = 10$ mA
Peak Emission Wavelength	λ_p		565		nm	$I_F = 20$ mA
Spectral Line Half-Width	$\Delta\lambda$		30		nm	$I_F = 20$ mA
Forward Voltage any Segment or D.P.	V_F		2.1	2.8	V	$I_F = 20$ mA
Reverse Current, any Segment or D.P.	I_R			100	μ A	$V_R = 5$ V
Luminous Intensity Matching Ratio	I_{v-m}			2:1		$I_F = 20$ mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

($25^\circ C$ Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE. % (REFRESH RATE — $F = 1$ KHz)




Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE% (AVERAGE $I_F = 10$ mA PER SEG.)



ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ\text{C}$
LTC-3710Y

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	600	1300		μcd	$I_F = 10 \text{ mA}$
Peak Emission Wavelength	λ_p		585		nm	$I_F = 20 \text{ mA}$
Spectral Line Half-Width	$\Delta\lambda$		35		nm	$I_F = 20 \text{ mA}$
Forward Voltage any Segment or D.P.	V_F		2.1	2.8	V	$I_F = 20 \text{ mA}$
Reverse Current, any Segment or D.P.	I_R			100	μA	$V_R = 5 \text{ V}$
Luminous Intensity Matching Ratio	I_{v-m}			2:1		$I_F = 20 \text{ mA}$

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)






Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.

Fig. 2 SPECTRAL RESPONSE.

Fig. 3 RELATIVE LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE%. (REFRESH RATE - F = 1 KHz)




Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE% (AVERAGE $I_F = 10 \text{ mA}$ PER SEG.)

ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ\text{C}$
LTC-3710E

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	750	1800		μcd	$I_F = 10 \text{ mA}$
Peak Emission Wavelength	λ_p		630		nm	$I_F = 20 \text{ mA}$
Spectral Line Half-Width	$\Delta\lambda$		40		nm	$I_F = 20 \text{ mA}$
Forward Voltage any Segment or D.P.	V_F		2.1	2.8	V	$I_F = 20 \text{ mA}$
Reverse Current, any Segment or D.P.	I_R			100	μA	$V_R = 5 \text{ V}$
Luminous Intensity Matching Ratio	$I_v\text{-m}$			2:1		$I_F = 20 \text{ mA}$

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE.% (REFRESH RATE = F = 1 KHz)




Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE% (AVERAGE $I_F = 10\text{mA}$ PER SEG.)



T-41-33

ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ C$
LTC-3710HR

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	750	1800		μ cd	$I_F = 10$ mA
Peak Emission Wavelength	λ_p		635		nm	$I_F = 20$ mA
Spectral Line Half-Width	$\Delta\lambda$		40		nm	$I_F = 20$ mA
Forward Voltage any Segment or D.P.	V_F		2.1	2.8	V	$I_F = 20$ mA
Reverse Current, any Segment or D.P.	I_R			100	μ A	$V_R = 5$ V
Luminous Intensity Matching Ratio	I_v-m			2:1		$I_F = 20$ mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

($25^\circ C$ Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE % (REFRESH RATE - $F = 1$ KHz)




Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE % (AVERAGE $I_F = 10$ mA PER SEG.)

ELECTRICAL/OPTICAL CHARACTERISTICS AT TA = 25°C
LTC-3718R

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	IV	200	450		μcd	IF = 10 mA
Peak Emission Wavelength	λp		655		nm	IF = 20 mA
Spectral Line Half-Width	Δλ		24		nm	IF = 20 mA
Forward Voltage any Segment or D.P.	VF		1.7	2.0	V	IF = 20 mA
Reverse Current, any Segment or D.P.	IR			100	μA	VR = 5 V
Luminous Intensity Matching Ratio	IV-m			2:1		IF = 20 mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE. % (REFRESH RATE = F = 1 KHz)





Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE % (AVERAGE If = 10mA PER SEG.)



T-41-33

ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ C$

LTC-3718P

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	250	600		μ cd	$I_F = 10$ mA
Peak Emission Wavelength	λ_p		697		nm	$I_F = 20$ mA
Spectral Line Half-Width	$\Delta\lambda$		90		nm	$I_F = 20$ mA
Forward Voltage any Segment or D.P.	V_F		2.1	2.8	V	$I_F = 20$ mA
Reverse Current, any Segment or D.P.	I_R			100	μ A	$V_R = 5$ V
Luminous Intensity Matching Ratio	I_v-m			2:1		$I_F = 20$ mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.





Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE %. (REFRESH RATE - F = 1 kHz)


Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE % (AVERAGE $I_F = 10$ mA PER SEG.)

ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ\text{C}$
LTC-3718G


PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	750	1800		μcd	$I_F = 10 \text{ mA}$
Peak Emission Wavelength	λ_p		565		nm	$I_F = 20 \text{ mA}$
Spectral Line Half-Width	$\Delta\lambda$		30		nm	$I_F = 20 \text{ mA}$
Forward Voltage any Segment or D.P.	V_F		2.1	2.8	V	$I_F = 20 \text{ mA}$
Reverse Current, any Segment or D.P.	I_R			100	μA	$V_R = 5 \text{ V}$
Luminous Intensity Matching Ratio	I_v-m			2:1		$I_F = 20 \text{ mA}$

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES


(25°C Ambient Temperature Unless Otherwise Noted)




Forward Voltage (V_F) — Volts
 Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Wavelength (λ) — nm.
 Fig. 2 SPECTRAL RESPONSE.




Forward Current (I_F) — mA
 Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).



Ambient Temperature (T_A) — $^\circ\text{C}$
 Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.



Duty Cycle %
 Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE. % (REFRESH RATE — F = 1 KHz)



Duty Cycle %
 Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE % (AVERAGE $I_F = 10 \text{ mA}$ PER SEG.)



ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ\text{C}$
LTC-3718Y

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	600	1300		μcd	$I_F = 10 \text{ mA}$
Peak Emission Wavelength	λ_p		585		nm	$I_F = 20 \text{ mA}$
Spectral Line Half-Width	$\Delta\lambda$		35		nm	$I_F = 20 \text{ mA}$
Forward Voltage any Segment or D.P.	V_F		2.1	2.8	V	$I_F = 20 \text{ mA}$
Reverse Current, any Segment or D.P.	I_R			100	μA	$V_R = 5 \text{ V}$
Luminous Intensity Matching Ratio	I_{v-m}			2:1		$I_F = 20 \text{ mA}$

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE. (%)
 (REFRESH RATE - $F = 1 \text{ KHz}$)




Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE %
 (AVERAGE $I_F = 10 \text{ mA}$ PER SEG.)

ELECTRICAL/OPTICAL CHARACTERISTICS AT $T_A = 25^\circ C$
LTC-3718E

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	I_v	750	1800		μ cd	$I_F = 10$ mA
Peak Emission Wavelength	λ_p		630		nm	$I_F = 20$ mA
Spectral Line Half-Width	$\Delta\lambda$		40		nm	$I_F = 20$ mA
Forward Voltage any Segment or D.P.	V_F		2.1	2.8	V	$I_F = 20$ mA
Reverse Current, any Segment or D.P.	I_R			100	μ A	$V_R = 5$ V
Luminous Intensity Matching Ratio	I_v-m			2:1		$I_F = 20$ mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

($25^\circ C$ Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE, LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE %
 Vs AMBIENT TEMPERATURE. (REFRESH RATE = $F = 1$ KHz)





Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE %
 (AVERAGE $I_F = 10$ mA PER SEG.)



T-41-33

ELECTRICAL/OPTICAL CHARACTERISTICS AT TA = 25°C
LTC-3718HR

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	TEST CONDITION
Average Luminous Intensity	IV	750	1800		μcd	IF = 10 mA
Peak Emission Wavelength	λp		635		nm	IF = 20 mA
Spectral Line Half-Width	Δλ		40		nm	IF = 20 mA
Forward Voltage any Segment or D.P.	VF		2.1	2.8	V	IF = 20 mA
Reverse Current, any Segment or D.P.	IR			100	μA	VR = 5 V
Luminous Intensity Matching Ratio	IV-m			2:1		IF = 20 mA

TYPICAL ELECTRICAL/OPTICAL CHARACTERISTIC CURVES

(25°C Ambient Temperature Unless Otherwise Noted)




Fig. 1 FORWARD CURRENT Vs. FORWARD VOLTAGE.




Fig. 2 SPECTRAL RESPONSE.




Fig. 3 RELATIVE LUMINOUS INTENSITY Vs. FORWARD CURRENT (PER SEGMENT).




Fig. 4 MAX. ALLOWABLE DC CURRENT PER SEG. Vs AMBIENT TEMPERATURE.




Fig. 5 MAX. PEAK CURRENT Vs. DUTY CYCLE %. (REFRESH RATE - F = 1 KHz)




Fig. 6 LUMINOUS INTENSITY Vs. DUTY CYCLE % (AVERAGE If = 10mA PER SEG.)

PACKAGING

T-90-20

Reel Packaging (Axial Lead Units)

DEVICE TYPE	COMPONENT SPACE (MM) "A"	TAPE SPACE (MM) "B"	REEL DIA (MM) "D"	QUANTITY (EA)		CARTON	
				REEL	CARTON	SIZE (MM)	WEIGHT (KG)
DO-41 DO-41L	5±0.5	52.4±1.5	326~336	5000	20K	355 x 355 x 355	10.5
DO-201AD	10±0.5	52.4±1.5	326~336	1200	4.8K	355 x 355 x 355	9.0
P6(Aleg)	10.5±0.5	52.4±1.5	326~336	700	2.8K	355 x 355 x 355	8.8

The C dimension of Fig. 3 is between 3.17m.m. and 635mm greater than the length of the component involved.

FIG. 1




FIG.2





FIG.3




Bulk Packaging (Axial Lead Devices and Bridge Rectifiers)

DEVICE TYPE	PACKAGING SIZE (MM)		QUANTITY (EA)		APPROX GROSS WEIGHT (KG)	
	BOX	CARTON	BOX	CARTON	BOX	CARTON
DO-41 DO-41L	196 x 84 x 20	450 x 210 x 250	1000	50K	0.38	20
DO-201AD	305 x 93 x 59	355 x 355 x 355	1000	20K	1.35	28
P6(Aleg)	305 x 93 x 59	355 x 355 x 355	500	10K	1.2	24.5
PBM	357 x 125 x 60	530 x 360 x 340	1000	20K	1.5	32.3
PBDF	495 x 155 x 145	500 x 325 x 305	5000	20K	5.1	21.5
PBP	357 x 125 x 60	530 x 360 x 340	500	10K	1.5	31.5
PBL	375 x 220 x 155	470 x 385 x 455	1000	5K	5.7	30.5
PBPC-6	357 x 125 x 60	560 x 360 x 340	250	5K	1.1	22
PBPC-8	357 x 125 x 60	560 x 360 x 340	250	5K	1.7	35
KBPC	375 x 220 x 365	470 x 390 x 385	500	1K	15.1	31.5
KBPC-W	375 x 220 x 365	470 x 390 x 385	500	1K	14.5	30.0

AMMO BOX PACKAGING

BOX SIZE



Unit:m. m.


Packaging	Products Outline	Dimension *A*	Dimension *B*	Dimension *C*	Q'ty per BOX
26MM Horizontal Ammo Pack	DO-41	255	50	95	3K
	DO-41L(0.6mm Lead)				3K
'52MM Horizontal Ammo Pack	DO-41 and DO-41L	250	75	92	3K
	DO 201AD				0.8K

CARTON SIZE

Unit:m. m.

Packaging	Products Outline	Length	Width	High	Q'ty Per Carton
26MM Horizontal Ammo Pack	DO-41 DO-41L(0.6mm Lead)	330	310	268	42K
'52MM Horizontal Ammo Pack	DO-41 and DO-41L	355	355	340	48K
	DO 201AD				12K

PREFORMED LEAD DRAWING



Case type	Preformed type	A (mm)		B (mm)		C (mm)		D (mm)		R (mm)	
		range	tolerance	range	tolerance	range	tolerance	range	tolerance	range	tolerance
D041	M	9.0-20.0	1.0	8.0-22.0	± 0.5	—	—	1.5	max	—	—
	E	11.0-20.0	± 1.0	11.0-16.0	± 1.0	4.0-5.0	± 0.5	1.5	max	—	—
	B	7.5	± 0.5	19.0-22.0	± 0.5	7.5	± 0.5	1.5	max	2.5-4.0	Typ
	C	4.5	± 0.8	18.0-19.0	± 0.5	9.0	± 0.5	1.5	max	2.5-4.0	Typ
D0201AD	M	15.0-20.0	± 1.0	8.0-22.0	± 1.0	—	—	2.0	max	—	—
	E	15.0-20.0	± 1.0	10.0-22.0	± 1.0	3.0-15.0	± 0.5	2.0	max	—	—
P6(Aleg)	M	15.0-20.0	± 1.0	8.0-22.0	± 1.0	—	—	2.0	max	—	—