




10		9		8		7		6		5		4		3		2		1		
F	CIRCUIT SIZE	PLATING TYPE A		PLATING TYPE E		PLATING TYPE F														F
		PART NO.	CUSTOMER SPECIFIC PART NO.	PART NO.	CUSTOMER SPECIFIC PART NO.	PART NO.	CUSTOMER SPECIFIC PART NO.													
	I X 1	90120-0121	90120-9121	90120-0761	90120-9761	90120-0921	90120-9921													
	I X 2	▲ -0122	▲ -9122	▲ -0762	▲ -9762	▲ -0922	▲ -9922													
	I X 3	▲ -0123	▲ -9123	▲ -0763	▲ -9763	▲ -0923	▲ -9923													
	I X 4	▲ -0124	▲ -9124	▲ -0764	▲ -9764	▲ -0924	▲ -9924													
	I X 5	▲ -0125	▲ -9125	▲ -0765	▲ -9765	▲ -0925	▲ -9925													
	I X 6	▲ -0126	▲ -9126	▲ -0766	▲ -9766	▲ -0926	▲ -9926													
	I X 7	▲ -0127	▲ -9127	▲ -0767	▲ -9767	▲ -0927	▲ -9927													
	I X 8	▲ -0128	▲ -9128	▲ -0768	▲ -9768	▲ -0928	▲ -9928													
	I X 9	▲ -0129	▲ -9129	▲ -0769	▲ -9769	▲ -0929	▲ -9929													
E	I X 10	▲ -0130	▲ -9130	▲ -0770	▲ -9770	▲ -0930	▲ -9930													E
	I X 11	▲ -0131	▲ -9131	▲ -0771	▲ -9771	▲ -0931	▲ -9931													
	I X 12	▲ -0132	▲ -9132	▲ -0772	▲ -9772	▲ -0932	▲ -9932													
	I X 13	▲ -0133	▲ -9133	▲ -0773	▲ -9773	▲ -0933	▲ -9933													
	I X 14	▲ -0134	▲ -9134	▲ -0774	▲ -9774	▲ -0934	▲ -9934													
	I X 15	▲ -0135	▲ -9135	▲ -0775	▲ -9775	▲ -0935	▲ -9935													
	I X 16	▲ -0136	▲ -9136	▲ -0776	▲ -9776	▲ -0936	▲ -9936													
	I X 17	▲ -0137	▲ -9137	▲ -0777	▲ -9777	▲ -0937	▲ -9937													
	I X 18	▲ -0138	▲ -9138	▲ -0778	▲ -9778	▲ -0938	▲ -9938													
	I X 19	▲ -0139	▲ -9139	▲ -0779	▲ -9779	▲ -0939	▲ -9939													
D	I X 20	▲ -0140	▲ -9140	▲ -0780	▲ -9780	▲ -0940	▲ -9940													D
	I X 21	▲ -0141	▲ -9141	▲ -0781	▲ -9781	▲ -0941	▲ -9941													
	I X 22	▲ -0142	▲ -9142	▲ -0782	▲ -9782	▲ -0942	▲ -9942													
	I X 23	▲ -0143	▲ -9143	▲ -0783	▲ -9783	▲ -0943	▲ -9943													
	I X 24	▲ -0144	▲ -9144	▲ -0784	▲ -9784	▲ -0944	▲ -9944													
	I X 25	▲ -0145	▲ -9145	▲ -0785	▲ -9785	▲ -0945	▲ -9945													
	I X 26	▲ -0146	▲ -9146	▲ -0786	▲ -9786	▲ -0946	▲ -9946													
	I X 27	▲ -0147	▲ -9147	▲ -0787	▲ -9787	▲ -0947	▲ -9947													
	I X 28	▲ -0148	▲ -9148	▲ -0788	▲ -9788	▲ -0948	▲ -9948													
	I X 29	▲ -0149	▲ -9149	▲ -0789	▲ -9789	▲ -0949	▲ -9949													
C	I X 30	▲ -0150	▲ -9150	▲ -0790	▲ -9790	▲ -0950	▲ -9950													C
	I X 31	▲ -0151	▲ -9151	▲ -0791	▲ -9791	▲ -0951	▲ -9951													
	I X 32	▲ -0152	▲ -9152	▲ -0792	▲ -9792	▲ -0952	▲ -9952													
	I X 33	▲ -0153	▲ -9153	▲ -0793	▲ -9793	▲ -0953	▲ -9953													
	I X 34	▲ -0154	▲ -9154	▲ -0794	▲ -9794	▲ -0954	▲ -9954													
	I X 35	▲ -0155	▲ -9155	▲ -0795	▲ -9795	▲ -0955	▲ -9955													
	I X 36	▲ -0156	▲ -9156	▲ -0796	▲ -9796	▲ -0956	▲ -9956													
	I X 37	▲ -0157	▲ -9157	▲ -0797	▲ -9797	▲ -0957	▲ -9957													
	I X 38	▲ -0158	▲ -9158	▲ -0798	▲ -9798	▲ -0958	▲ -9958													
	I X 39	▲ -0159	▲ -9159	▲ -0799	▲ -9799	▲ -0959	▲ -9959													
B	I X 40	90120-0160	90120-9160	90120-0800	90120-9800	90120-0960	90120-9960													B
A	NOTES: FOR PLATING VARIATIONS SEE ENG.STD. SDES-99000-0003.		PART NO'S ADDED EC NO: E2006-0667 DRWN: JDENNEHY 2006/01/23 CHKD: DWASZKIEWICZ 2006/01/23 APPR: JDENNEHY 2006/02/07		QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE ---	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION		C-GRID III SINGLE ROW STRAIGHT PIN HEADER		MOLEX INCORPORATED		SHEET NO. 2 OF 6		
	STANDARD PRODUCTS					4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± ---°		DRAWN BY DATE JDENNEHY 2006/01/18 CHECKED BY DATE DWASZKIEWICZ 2006/01/18 APPROVED BY DATE JDENNEHY 2006/01/18		TITLE C-GRID III SINGLE ROW STRAIGHT PIN HEADER		MOLEX INCORPORATED								
						DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SEE CHART		DOCUMENT NO. SDA-90120										
								SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION										