







Recommended Panel Cutout (e)



Notes:

- Electrical Specifications:
 - Meets USB 2.0 Specification
 - Contact Resistance: 30 mOhm max.
 - Insulation Resistance: 1000 MOhm min. @ 100 VDC
 - Current Rating: 1.5 A max. at 25° C
 - Working Voltage: 30 V (RMS) max.
 - DWV: 500 VAC/60s at sea level
 - Operating Temperature: -40° C to +85° C

2. Material and Finish:

- Receptacle Housing: Polyester (Black), UL94 V-0 or Metallized ABS (Nickel Plated), UL94 V-0
- Cover Coupling Ring: Polyester (Black), UL94 V-0 or Metallized ABS (Nickel Plated), UL94 V-0
- Panel Nut: Brass, Finish: Nickel Plated
- Panel Gasket: Silicon, Color: White
- Cover Gasket: Silicon, Color: White
- USB Adaptor Metal Shell: Copper Alloy, Nickel Plated
- USB Adaptor Overmold material: PBT UL94 V-0, Color: Black
- USB Contacts: Copper Alloy, Finish: 30 u" Gold min. over Nickel

3. Connector can be front or rear mounted to a maximum panel thickness of 3.2 mm.

4. IP67 rated when covered or fully mated with the appropriate mating connector

Pin-Assignment

Type A F	Type A F
Pin1 -----	Pin1
Pin2 -----	Pin2
Pin3 -----	Pin3
Pin4 -----	Pin4
Shell -----	Shell

Directive 2002/95/EC RoHS Compliant

(c)	Description	Part Number
	Plastic Version with USB 2.0 Type A F/F Adaptor with Cover Assembly	17-200161
	Metallized Plastic Version with USB 2.0 Type A F/F Adaptor with Cover Assembly	17-200721

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC CORPORATION.	Customer:			Tolerance Unless otherwise specified			Scale: 1:2:1	Dim. in mm
	Name	Title	Approval Date	0 PLC ± 0.50	1 PLC ± 0.38			
				2 PLC ± 0.25	3 PLC ± 0.10			
				ANGLES ± 3°				
DO NOT ALTER CAD DRAWING BY HAND	f	1 x f	May/15/2013	Vincent ke	Draw.	Sept. 09	Vincent Ke	Title: IP67 USB Receptacle + Cover Assembly Kit with USB 2.0 Type A F / F Adaptor
	e	2 x e	Mar/08/2011	Vincent Ke	Appd.	Sept. 09	J. Chaudry	
	d	1 x d	Jun/03/2010	Vincent Ke	Norm			
	c	1 x c	Mar/18/2010	Vincent ke	D-old			
CONEC®	b		Jun/01/2009	Vincent Ke				Drawing No.: 17K1A100 Part No.: SEE PART NUMBER TABLE
	a	original						
	Rev.	Changes	Date	Name				

A

DIN A3 Sheet 1/1