

4

3

2


1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT - BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
G	14	P	LTR	DESCRIPTION	DATE	APVD
			M	REV PER 0G3A-0582-04	31AUG04	JR TM

AMP
WIRE RANGE26-22 AWG
STRANDED

- 1 WIRE INSULATION DIA 1.27 [.050] TO 2.08 [.082].
- 2 26-22 COMMERCIAL
- 3 SUPERSEDED BY 53546-1
- 4 FINISH: BODY AND SLEEVE: TIN/LEAD (93-7) PLATE PER ASTM B545. (3% MIN LEAD CONTENT)
- 5 MATERIAL: BODY AND SLEEVE, COPPER PER ASTM B152 INSULATION: PVF² COLOR- NATURAL

-	1000	LOOSE PIECE	2 53546-3 3
26-24 M7928/6-1 CLASS 1 & 2	1000		53546-1
MILITARY P/N & CLASS PER MIL-T-7928	QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED
CUSTOMER SERVICE SYSTEMSMAX RECOMMENDED OPERATING
TEMPERATURE:
150°C

THIS DRAWING IS A CONTROLLED DOCUMENT.

FOR ADDITIONAL
PRODUCT INFORMATION OR
COPIES OF DRAWINGS
AND TECHNICAL DOCUMENTSPRODUCT INFORMATION CENTER
1-800-522-6752VOLTAGE RATING:
-FOR APPLICATION
TOOLING INFORMATIONTOOLING ASSISTANCE CENTER
1-800-722-1111CIRCULAR MIL AREA:
0.10-0.41mm² [202-810]
STRANDED

FOR ORDER ENTRY

1-800-526-5142

THIS DRAWING IS A CONTROLLED DOCUMENT FOR
AMP INCORPORATED. IT IS SUBJECT TO CHANGE
AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

MATERIAL

- 5

FINISH

- 4

DWN S.S. GOULDEN 9-28-93

CHK R. HERSEY 9-28-93

APVD M ELLIS 9-28-93

PRODUCT SPEC

108-11023

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

Tyco Electronics Corporation
Harrisburg, Pa 17105-3608NAME
SPlice, BUTT, PVF², P.I.D.G.
WIRE SIZE: 26-22 AWG
, P.I.D.G.,

SIZE A3 CAGE CODE 00779 DRAWING NO C-53546 RESTRICTED TO -

SCALE 1:1 SHEET 1 OF 1 REV M