


MR-28406-000

SHT 1.1



DIMENSIONS IN MILLIMETERS [INCHES]

KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.

Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION
			Released	A
A	MI0101178	8-21-06		
SCALE: 1:1			DR. BY LSY	DATE 8-21-06
DO NOT SCALE DRAWING			CK. BY GJP	DATE 8-25-06
TITLE: WATERPROOF MICROPHONE			APP. BY GJP	DATE 8-25-06
OUTLINE DRAWING			Rev: B	


MR-28406-000

SHT 1.1

NO DAMPING

MR-28406-000

SHEET 2.1


SENSITIVITY IN dB RELATIVE TO 1.0 VOLT/0.1 Pa (N/M²)
FOR CONDITIONS SHOWN BELOW.

FREQUENCY	SENSITIVITY			DEVICE CONFORMITY	
	MIN.	NOM.	MAX.	RANGE OF DEVIATION FROM 1KHZ	
100	---	-61.5	---	-4.0	+2.0
1000	-65.0	-60.0	-58.0	---	---
4700 APPROX	---	-47.0	---	+8.0	+20.0

NOTES:

- 1.CASE OF MICROPHONE CONNECTED TO NEGATIVE BLACK LEAD.
- 2.BELLOWS HOUSING INSULATED FROM MICROPHONE CASE.
- 3.MICROPHONE TO BE FUNCTIONAL WITH 20 VDC SUPPLY.
- 4.CONFORMS TO REQUIREMENTS SHOWN ON "ELECTRET MICROPHONE ENVIRONMENTAL QUALIFICATION TEST, BT-1759 SHEET 2.2.
- 5.INDIVIDUAL SPECIFICATIONS.

LOAD RESISTANCE ON OUTPUT FOR SENSITIVITY OHMS	DC SUPPLY V	OUTPUT IMPEDANCE OHMS			AMPLIFIER CURRENT DRAIN uA MAX.	SENSITIVITY CHANGE ON REDUCING SUPPLY TO .9VDC	"A" WEIGHTED NOISE 1KHZ EQUIVALENT SPL dB SPL MAX
		MIN.	MOM.	MAX.			
10000	1.3	2000	3500	6000	50	3 dB MAX.	30



KNOWLES ELECTRONICS
ITASCA, ILLINOIS U.S.A.

Revision	C.O. #	Implementation Date	RELEASE LEVEL	REVISION
			Released	A
A	M10101178	8-21-06		
WHEN TEST LIMITS ARE USED TO ESTABLISH INCOMING INSPECTION ACCEPTANCE/REJECTION CRITERIA, CORRELATION OF TEST EQUIPMENT WITH KNOWLES IS ALSO REQUIRED FOR ELIMINATION OF EQUIPMENT AND TEST METHOD VARIATION			DR. BY	DATE
TITLE: WATERPROOF MICROPHONE PERFORMANCE SPECIFICATION			LSY	8-21-06
			CK. BY	DATE
			GJP	8-25-06
			APP. BY	DATE
			GJP	8-25-06

MR-28406-000

SHT 2.1