

## REVISIONS


DOC. NO. SPC-F005 \* Effective: 7/8/02 \* DCP No: 1398

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
370	B	Redraw from individ. dwgs	JWM	3/18/02	JC	3/27/02	JC	3/27/02
1779	C	RoHS ADDED	DCM	1/24/06	JWM	1/24/06	JWM	1/24/06




## NOTES:

- Material: Black, Heat Stabilized Nylon
- Temperature Index: 105°C
- Flammability Rating: UL94V-2



Mounting Holes



SPC Type No.	Cross Section	Cable Size	Cable Type	Gauge (AWG)	Mounting Hole		Bushing		
					A (Diameter)	B (Flats)	C (Max. Panel Thickness)	D (Length)	E (Width)
SRF-10	Flat	.120 x .220 [3.0 x 5.6]	SP-1 SPT-1	18/2 18/2	.437 [11.1]	.390 [9.9]	.062 [1.6]	.410 [10.4]	.484 [12.3]
SRF-15	Flat	.120 x .300 [3.0 x 7.6]	SPT-1 SPT-2 HPN	18/3 18/2 18/2	.500 [12.7]	.465 [11.8]	.062 [1.6]	.406 [10.3]	.578 [14.7]
SRF-30	Flat	.120 x .300 [3.0 x 7.6]	SPT-1 SPT-2 HPN	18/3 18/2 18/2	.500 [12.7]	.465 [11.8]	.100 [2.5]	.406 [10.3]	.578 [14.7]
SRF-40	Flat	.120 x .300 [3.0 x 7.6]	SPT-2	18/3	.562 [14.3]	.530 [13.5]	.125 [3.2]	.609 [15.5]	.625 [15.9]
		.160 x .300 [4.1 x 7.6]	SPT-2	16/2					
		.160 x .410 [4.1 x 10.4]	SPT-2	16/3					
		.160 x .370 [4.1 x 9.4]	HPN	16/3					
SRF-50	Flat	.160 x .410 [4.1 x 10.4]	SPT-2	16/3	.506 [14.2]	.730 [18.5]	.125 [3.2]	.670 [17.0]	.750 [19.6]
		.120 x .300 [3.0 x 7.6]	SPT-1						

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

## TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

## DRAWN BY:

JC

## CHECKED BY:

## APPROVED BY:

## DATE:

2/18/91

## DATE:

## DATE:

## DRAWING TITLE:

Strain Relief bushing

## SIZE DWG. NO.

A

TA-508

## ELECTRONIC FILE

TA-508

## REV

C

SCALE: NTS

U.O.M.: INCHES [mm]

SHEET: 1 OF 1