

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION

**Part Number:** [0010897141](#)  
**Status:** **Active**  
**Description:** 2.54mm (.100") Pitch C-Grid® Breakaway Header, Dual Row, Vertical, High Temperature, 14 Circuits, Tin (Sn) Plating, 2.72mm (.107") PC Tail Length

**Documents:**

|                               |                                                      |
|-------------------------------|------------------------------------------------------|
| <a href="#">3D Model</a>      | <a href="#">Product Specification PS-70280 (PDF)</a> |
| <a href="#">Drawing (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a> |

**General**


|                |                |
|----------------|----------------|
| Product Family | PCB Headers    |
| Series         | 70280          |
| Application    | Board-to-Board |
| Application    | Wire-to-Board  |
| Product Name   | C-Grid®        |

**Physical**

|                                |                                |
|--------------------------------|--------------------------------|
| Breakaway                      | Yes                            |
| Circuits (Loaded)              | 14                             |
| Circuits (maximum)             | 14                             |
| Color - Resin                  | Black                          |
| Durability (mating cycles max) | 25                             |
| First Mate / Last Break        | No                             |
| Flammability                   | 94V-0                          |
| Glow-Wire Compliant            | No                             |
| Guide to Mating Part           | No                             |
| Keying to Mating Part          | None                           |
| Lock to Mating Part            | None                           |
| Material - Metal               | Copper Alloy                   |
| Material - Plating Mating      | Tin                            |
| Material - Plating Termination | Tin                            |
| Material - Resin               | High Temperature Thermoplastic |
| Number of Rows                 | 2                              |
| Orientation                    | Vertical                       |
| PC Tail Length (in)            | 0.110 In                       |
| PC Tail Length (mm)            | 2.79 mm                        |
| PCB Locator                    | No                             |
| PCB Retention                  | None                           |
| PCB Thickness Recommended (in) | 0.062 In                       |
| PCB Thickness Recommended (mm) | 1.60 mm                        |
| Packaging Type                 | Bag                            |
| Pitch - Mating Interface (in)  | 0.100 In                       |
| Pitch - Mating Interface (mm)  | 2.54 mm                        |
| Plating min: Mating (µin)      | 152.4                          |
| Plating min: Mating (µm)       | 3.81                           |
| Plating min: Termination (µin) | 152.4                          |
| Plating min: Termination (µm)  | 3.81                           |
| Polarized to Mating Part       | No                             |
| Polarized to PCB               | No                             |
| Shrouded                       | No                             |
| Stackable                      | Yes                            |
| Temperature Range - Operating  | -40°C to +105°C                |
| Termination Interface: Style   | Through Hole                   |

**Electrical**

|                   |         |
|-------------------|---------|
| CSA               | LR19980 |
| Current - Maximum | 3A      |



Series image - Reference only

**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC  
Contains SVHC: No**  
**Halogen-Free  
Status**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

**Search Parts in this Series**  
[70280 Series](#)

|                                    |                              |
|------------------------------------|------------------------------|
| UL                                 | E29179                       |
| Voltage - Maximum                  | 250V                         |
| <b>Solder Process Data</b>         |                              |
| Lead-free Process Capability       | SMC & Wave Capable (TH only) |
| Process Temperature max. C         | 260                          |
| <b>Material Info</b>               |                              |
| Old Part Number                    | A-70280-0007                 |
| <b>Reference - Drawing Numbers</b> |                              |
| Product Specification              | PS-70280                     |
| Sales Drawing                      | SDA-70280-0001-4000          |

This document was generated on 12/07/2009

PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION