
















SECTION Y-Y
SCALE 20:1
ROTATED 180°

SECTION Z-Z
SCALE 20:1
ROTATED 180°

NOTES:

1. MATERIAL: COPPER ALLOY
2. FINISH:
 - 2.5µm MIN OVERALL ELECTROPLATE MATTE TIN OVER
 - 1.25µm MIN OVERALL ELECTROPLATED MATTE NICKEL
3. PRODUCT SPECIFICATION: 2042200000-PS
4. APPLICATION SPECIFICATION: 2042200000-AS
5. PACKAGING SPECIFICATION: 2043010000-PK
6. THIS CRIMP TERMINAL TO BE USED WITH ASSEMBLY SERIES 204220.
7. THIS CRIMP TERMINAL MATES WITH RECEPTACLE CRIMP TERMINAL SERIES 2042261.
8. THIS PART CONFORMS TO CLASS 'B' REQUIREMENTS OF COSMETIC SPECIFICATION PS-45499-002.
9. WIRE SPECIFICATIONS:
 - AWG: 22 and 24 awg
 - INSULATION OD RANGE: 0.95mm - 1.4mm
10. CRIMP TOOLING:
 - APPLICATOR PART NUMBER: 638083700
 - HAND TOOL PART NUMBER: 2002180400

QUALITY SYMBOLS										THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION											
 = 0		2018/03/02 2018/03/02 2018/03/02	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION UNITS		SCALE															
 = 0				mm		15:1															
 = 0				ANGULAR TOL ± °		DRWN BY		DATE		RECEPTACLE CRIMP TERMINAL SQUBA 1.8											
 = 0				4 PLACES ±		TGREGORI		2018/01/03													
 = 0				3 PLACES ±		CHK'D BY		DATE													
 = 0				2 PLACES ±		APPR BY		DATE													
 = 0				1 PLACE ± 0.2		RHODGE		2018/01/26		PRODUCT CUSTOMER DRAWING											
 = 0				0 PLACES ±		DRAWING SIZE		THIRD ANGLE PROJECTION								SERIES		MATERIAL NUMBER		CUSTOMER	
 = 0				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		D										204301		2043010001			
 = 0				A2	REV					DOCUMENT NUMBER		DOC TYPE		DOC PART		SHEET NUMBER					
 = 0								2043010000-SD		PSD		000		1 OF 1							