



Micro Commercial Components

Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

MC79L09F

Features

- Internal Short Circuit Current Limiting
- Internal Thermal Overload Protection
- No External Components Required
- Case Material: Molded Plastic. UL Flammability Classification Rating 94-0 and MSL Rating 1

Absolute Maximum Ratings


Parameter	Symbol	Value	Unit
Input Voltage	V_1	30	V
Operating Junction Temperature	T_{OPR}	-30---+75	°C
Storage Temperature Range	T_{STG}	-40---+125	°C

Electrical Characteristics($V_i=15V$, $I_o=40mA$, $0^\circ C < T_j < 125^\circ C$, $C_1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified)

Parameter	Sym	Min	Typ	Max	Test conditions
Output Voltage	V_o	8.64V	9.0V	9.36V	$V_i=15V$, $I_o=40mA$
Load Regulation	$V_o - I_o$		12mV	90mV	$I_o=1mA-100mA$, $V_i=15V$
Line regulation	$V_o - V_i$		27mV	200mV	$12.5V \leq V_i \leq 24V$, $I_o=40mA$
Quiescent Current	I_q		3.5mA	6.0mA	$V_i=15V$, $I_o=40mA$
Output Noise Voltage	V_N		210 μV		10Hz $\leq f \leq$ 100KHz $V_i=15V$, $I_o=40mA$
Ripple Rejection	RR	37dB	64dB		$12V \leq V_i \leq 22V$, $I_o=40mA$ $f=120Hz$, $T_j=25^\circ C$ $e_{IN}=1V_{P-P}$



*Note: Bypass Capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators

Typical Application:



Three-Terminal Low Current Negative Voltage Regulator

SOT-89



1. GND
2. IN(Case)
3. OUT

DIM	DIMENSINS				NOTES
	INCHES		MM		
A	.173	.181	4.39	4.60	REF.
B	.061	----	1.55	----	
C	.154	.165	3.91	4.25	
D	.031	.039	0.80	1.00	
E	.092	.100	2.34	2.54	TYP
F	.118	----	3.00	----	
G	.013	.019	0.33	0.48	
H	.015	.021	0.38	0.53	
J	.015	.016	0.38	0.41	
K	.055	.063	1.40	1.60	

Ordering Information

Device	Packing
(Part Number)-TP	Tape&Reel;1Kpcs/Reel

IMPORTANT NOTICE

Micro Commercial Components Corp. reserves the right to make changes without further notice to any product herein to make corrections, modifications , enhancements , improvements , or other changes .
Micro Commercial Components Corp. does not assume any liability arising out of the application or use of any product described herein; neither does it convey any license under its patent rights ,nor the rights of others . The user of products in such applications shall assume all risks of such use and will agree to hold *Micro Commercial Components Corp.* and all the companies whose products are represented on our website, harmless against all damages.

APPLICATIONS DISCLAIMER

Products offer by *Micro Commercial Components Corp.* are not intended for use in Medical, Aerospace or Military Applications.