

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION




FEB ,2006.

© COPYRIGHT 2006 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.


LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	C	ECR-06-002568	15FEB06	JMS	FWK	

NOTES:

- 1 PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2 100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3 Au PLATING
- 4 ELECTRICAL CHARACTERISTICS
FREQUENCY RANGE: DC - 10 GHz
NOMINAL IMPEDANCE: 50 Ohm
INSULATION RESISTANCE: 1000 MOhm
WORKING VOLTAGE: 250 Volts RMS at Sea Level
DIELECTRIC WITHSTAND VOLTAGE: 750 Volts RMS Max
CONTACT RESISTANCE: 6.00 mOhm Max
CENTRE CONTACT: 1.00 mOhm Max
OUTER CONTACT:
- 5 MECHANICAL CHARACTERISTICS
DURABILITY: 500 Cycles Min
- 6 ENVIRONMENTAL CHARACTERISTICS
OPERATING TEMPERATURE: -65 to +165 DegC



		1	1	BRASS	3	CAP	7
		1	1	BRASS	3	CONTACT	6
		1	1	BRASS	3	BODY	5
		1	1	PTFE		INSULATION	4
		1	1	BRASS	3	CONTACT	3
		1	1	PTFE		INSULATION	2
		1	1	BRASS	3	BODY	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		3	3				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL 15FEB06	tyco Electronics Tyco Electronics Corporation Bideford EX39 4HE			
DIMENSIONS: mm		CHK S.PARLOW 15FEB06				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APVD F.WHEELER-KING 15FEB06	NAME SMC ELBOW PCB SOCKET 50 OHM			
		PRODUCT SPEC —				
		MATERIAL SEE TABLE	FINISH —	APPLICATION SPEC — WEIGHT —	SIZE A3	CAGE CODE 00779
CUSTOMER DRAWING			SCALE NTS	SHEET 1	OF 1	REV C