

# STUN06I - STUN5D0

## SURFACE MOUNT TRANSIENT VOLTAGE SUPPRESSOR

**V<sub>BR</sub> : 6.8 - 200 Volts**


**P<sub>PK</sub> : 1500 Watts**

### FEATURES :

- \* 1500W surge capability at 1ms
- \* Excellent clamping capability
- \* Low zener impedance
- \* Fast response time : typically less than 1.0 ps from 0 volt to V<sub>BR(min.)</sub>
- \* Typical I<sub>R</sub> less than 1μA above 10V
- \* **Pb / RoHS Free**

### MECHANICAL DATA

- \* Case : SMC Molded plastic
- \* Epoxy : UL94V-O rate flame retardant
- \* Lead : Lead Formed for Surface Mount
- \* Polarity : Color band denotes cathode end except Bipolar.
- \* Mounting position : Any
- \* Weight : 0.21 grams



### DEVICES FOR BIPOLAR APPLICATIONS

For bi-directional altered the third letter of type from "U" to be "B".  
Electrical characteristics apply in both directions

### MAXIMUM RATINGS

Rating at 25 °C ambient temperature unless otherwise specified.

| Rating                                                                                                     | Symbol                            | Value         | Unit |
|------------------------------------------------------------------------------------------------------------|-----------------------------------|---------------|------|
| Peak Power Dissipation at Ta = 25 °C, Tp=1ms (Note1)                                                       | P <sub>PK</sub>                   | Minimum 1500  | W    |
| Steady State Power Dissipation at T <sub>L</sub> = 75 °C (Note 2)                                          | P <sub>D</sub>                    | 5.0           | W    |
| Peak Forward Surge Current, 8.3ms Single Half Sine-Wave Superimposed on Rated Load (JEDEC Method) (Note 3) | I <sub>FSM</sub>                  | 200           | A    |
| Operating and Storage Temperature Range                                                                    | T <sub>J</sub> , T <sub>STG</sub> | - 55 to + 150 | °C   |

### Note :

- (1) Non-repetitive Current pulse, per Fig. 5 and derated above Ta = 25 °C per Fig. 1
- (2) Mounted on copper Lead area at 5.0 mm<sup>2</sup> ( 0.013 mm thick ).
- (3) 8.3 ms single half sine-wave, duty cycle = 4 pulses per minutes maximum.

## ELECTRICAL CHARACTERISTICS

Rating at 25 °C ambient temperature unless otherwise specified

| TYPE    | Breakdown Voltage @ It<br>( Note 1 ) |      |      | Working Peak<br>Reverse<br>Voltage | Maximum<br>Reverse Leakage<br>@ VRWM | Maximum<br>Reverse<br>Current | Maximum<br>Clamping<br>Voltage @ IRSM | Maximum<br>Temperature<br>Co-efficient<br>of VBR |      |      |      |      |
|---------|--------------------------------------|------|------|------------------------------------|--------------------------------------|-------------------------------|---------------------------------------|--------------------------------------------------|------|------|------|------|
|         | VBR (V)                              |      | It   |                                    |                                      |                               |                                       |                                                  | VRWM | IR   | IRSM | VRSM |
|         | Min.                                 | Max. | (mA) |                                    |                                      |                               |                                       |                                                  | (V)  | (μA) | (A)  | (V)  |
|         |                                      |      |      |                                    |                                      |                               |                                       |                                                  |      |      |      |      |
| STUN06I | 6.12                                 | 7.48 | 10   | 5.50                               | 1000                                 | 139                           | 10.8                                  | 0.057                                            |      |      |      |      |
| STUN56I | 6.45                                 | 7.14 | 10   | 5.80                               | 1000                                 | 143                           | 10.5                                  | 0.057                                            |      |      |      |      |
| STUN07F | 6.75                                 | 8.25 | 10   | 6.05                               | 500                                  | 128                           | 11.7                                  | 0.061                                            |      |      |      |      |
| STUN57F | 7.13                                 | 7.88 | 10   | 6.40                               | 500                                  | 132                           | 11.3                                  | 0.061                                            |      |      |      |      |
| STUN08C | 7.38                                 | 9.02 | 10   | 6.63                               | 200                                  | 120                           | 12.5                                  | 0.065                                            |      |      |      |      |
| STUN58C | 7.79                                 | 8.61 | 10   | 7.02                               | 200                                  | 124                           | 12.1                                  | 0.065                                            |      |      |      |      |
| STUN09B | 8.19                                 | 10.0 | 1.0  | 7.37                               | 50                                   | 109                           | 13.8                                  | 0.068                                            |      |      |      |      |
| STUN59B | 8.65                                 | 9.55 | 1.0  | 7.78                               | 50                                   | 112                           | 13.4                                  | 0.068                                            |      |      |      |      |
| STUN010 | 9.00                                 | 11.0 | 1.0  | 8.10                               | 10                                   | 100                           | 15.0                                  | 0.073                                            |      |      |      |      |
| STUN510 | 9.50                                 | 10.5 | 1.0  | 8.55                               | 10                                   | 103                           | 14.5                                  | 0.073                                            |      |      |      |      |
| STUN011 | 9.90                                 | 12.1 | 1.0  | 8.92                               | 5.0                                  | 93.0                          | 16.2                                  | 0.075                                            |      |      |      |      |
| STUN511 | 10.5                                 | 11.6 | 1.0  | 9.40                               | 5.0                                  | 96.0                          | 15.6                                  | 0.075                                            |      |      |      |      |
| STUN012 | 10.8                                 | 13.2 | 1.0  | 9.72                               | 5.0                                  | 87.0                          | 17.3                                  | 0.078                                            |      |      |      |      |
| STUN512 | 11.4                                 | 12.6 | 1.0  | 10.2                               | 5.0                                  | 90.0                          | 16.7                                  | 0.078                                            |      |      |      |      |
| STUN013 | 11.7                                 | 14.3 | 1.0  | 10.5                               | 5.0                                  | 79.0                          | 19.0                                  | 0.081                                            |      |      |      |      |
| STUN513 | 12.4                                 | 13.7 | 1.0  | 11.1                               | 5.0                                  | 82.0                          | 18.2                                  | 0.081                                            |      |      |      |      |
| STUN015 | 13.5                                 | 16.5 | 1.0  | 12.1                               | 5.0                                  | 68.0                          | 22.0                                  | 0.084                                            |      |      |      |      |
| STUN515 | 14.3                                 | 15.8 | 1.0  | 12.8                               | 5.0                                  | 71.0                          | 21.2                                  | 0.084                                            |      |      |      |      |
| STUN016 | 14.4                                 | 17.6 | 1.0  | 12.9                               | 5.0                                  | 64.0                          | 23.5                                  | 0.086                                            |      |      |      |      |
| STUN516 | 15.2                                 | 16.8 | 1.0  | 13.6                               | 5.0                                  | 67.0                          | 22.5                                  | 0.086                                            |      |      |      |      |
| STUN018 | 16.2                                 | 19.8 | 1.0  | 14.5                               | 5.0                                  | 56.5                          | 26.5                                  | 0.088                                            |      |      |      |      |
| STUN518 | 17.1                                 | 18.9 | 1.0  | 15.3                               | 5.0                                  | 59.5                          | 25.2                                  | 0.088                                            |      |      |      |      |
| STUN020 | 18.0                                 | 22.0 | 1.0  | 16.2                               | 5.0                                  | 51.5                          | 29.1                                  | 0.090                                            |      |      |      |      |
| STUN520 | 19.0                                 | 21.0 | 1.0  | 17.1                               | 5.0                                  | 54.0                          | 27.7                                  | 0.090                                            |      |      |      |      |
| STUN022 | 19.8                                 | 24.2 | 1.0  | 17.8                               | 5.0                                  | 47.0                          | 31.9                                  | 0.092                                            |      |      |      |      |
| STUN522 | 20.9                                 | 23.1 | 1.0  | 18.8                               | 5.0                                  | 49.0                          | 30.6                                  | 0.092                                            |      |      |      |      |
| STUN024 | 21.6                                 | 26.4 | 1.0  | 19.4                               | 5.0                                  | 43.0                          | 34.7                                  | 0.094                                            |      |      |      |      |
| STUN524 | 22.8                                 | 25.2 | 1.0  | 20.5                               | 5.0                                  | 45.0                          | 33.2                                  | 0.094                                            |      |      |      |      |
| STUN027 | 24.3                                 | 29.7 | 1.0  | 21.8                               | 5.0                                  | 38.5                          | 39.1                                  | 0.096                                            |      |      |      |      |
| STUN527 | 25.7                                 | 28.4 | 1.0  | 23.1                               | 5.0                                  | 40.0                          | 37.5                                  | 0.096                                            |      |      |      |      |
| STUN030 | 27.0                                 | 33.0 | 1.0  | 24.3                               | 5.0                                  | 34.5                          | 43.5                                  | 0.097                                            |      |      |      |      |
| STUN530 | 28.5                                 | 31.5 | 1.0  | 25.6                               | 5.0                                  | 36.0                          | 41.4                                  | 0.097                                            |      |      |      |      |
| STUN033 | 29.7                                 | 36.3 | 1.0  | 26.8                               | 5.0                                  | 31.5                          | 47.7                                  | 0.098                                            |      |      |      |      |
| STUN533 | 31.4                                 | 34.7 | 1.0  | 28.2                               | 5.0                                  | 33.0                          | 45.7                                  | 0.098                                            |      |      |      |      |
| STUN036 | 32.4                                 | 39.6 | 1.0  | 29.1                               | 5.0                                  | 29.0                          | 52.0                                  | 0.099                                            |      |      |      |      |
| STUN536 | 34.2                                 | 37.8 | 1.0  | 30.8                               | 5.0                                  | 30.0                          | 49.9                                  | 0.099                                            |      |      |      |      |
| STUN039 | 35.1                                 | 42.9 | 1.0  | 31.6                               | 5.0                                  | 26.5                          | 56.4                                  | 0.100                                            |      |      |      |      |
| STUN539 | 37.1                                 | 41.0 | 1.0  | 33.3                               | 5.0                                  | 28.0                          | 53.9                                  | 0.100                                            |      |      |      |      |
| STUN043 | 38.7                                 | 47.3 | 1.0  | 34.8                               | 5.0                                  | 24.0                          | 61.9                                  | 0.101                                            |      |      |      |      |
| STUN543 | 40.9                                 | 45.2 | 1.0  | 36.8                               | 5.0                                  | 25.3                          | 59.3                                  | 0.101                                            |      |      |      |      |
| STUN047 | 42.3                                 | 51.7 | 1.0  | 38.1                               | 5.0                                  | 22.2                          | 67.8                                  | 0.101                                            |      |      |      |      |
| STUN547 | 44.7                                 | 49.4 | 1.0  | 40.2                               | 5.0                                  | 23.2                          | 64.8                                  | 0.101                                            |      |      |      |      |
| STUN051 | 45.9                                 | 56.1 | 1.0  | 41.3                               | 5.0                                  | 20.4                          | 73.5                                  | 0.102                                            |      |      |      |      |
| STUN551 | 48.5                                 | 53.6 | 1.0  | 43.6                               | 5.0                                  | 21.4                          | 70.1                                  | 0.102                                            |      |      |      |      |
| STUN056 | 50.4                                 | 61.6 | 1.0  | 45.4                               | 5.0                                  | 18.6                          | 80.5                                  | 0.103                                            |      |      |      |      |
| STUN556 | 53.2                                 | 58.8 | 1.0  | 47.8                               | 5.0                                  | 19.5                          | 77.0                                  | 0.103                                            |      |      |      |      |

## ELECTRICAL CHARACTERISTICS

Rating at 25 °C ambient temperature unless otherwise specified

| TYPE    | Breakdown Voltage @ It<br>( Note 1 ) |      |      | Working Peak<br>Reverse<br>Voltage | Maximum<br>Reverse Leakage<br>@ VRWM | Maximum<br>Reverse<br>Current | Maximum<br>Clamping<br>Voltage @ IRSM | Maximum<br>Temperature<br>Co-efficient<br>of VBR |
|---------|--------------------------------------|------|------|------------------------------------|--------------------------------------|-------------------------------|---------------------------------------|--------------------------------------------------|
|         | VBR (V)                              |      | It   | VRWM                               | IR                                   | IRSM                          | VRSM                                  | of VBR<br>of VBR                                 |
|         | Min.                                 | Max. | (mA) | (V)                                | (μA)                                 | (A)                           | (V)                                   |                                                  |
|         |                                      |      |      |                                    |                                      |                               |                                       |                                                  |
| STUN062 | 55.8                                 | 68.2 | 1.0  | 50.2                               | 5.0                                  | 16.9                          | 89.0                                  | 0.104                                            |
| STUN562 | 58.9                                 | 65.1 | 1.0  | 53.0                               | 5.0                                  | 17.7                          | 85.0                                  | 0.104                                            |
| STUN068 | 61.2                                 | 74.8 | 1.0  | 55.1                               | 5.0                                  | 15.3                          | 98.0                                  | 0.104                                            |
| STUN568 | 64.6                                 | 71.4 | 1.0  | 58.1                               | 5.0                                  | 16.3                          | 92.0                                  | 0.104                                            |
| STUN075 | 67.5                                 | 82.5 | 1.0  | 60.7                               | 5.0                                  | 13.9                          | 108                                   | 0.105                                            |
| STUN575 | 71.3                                 | 78.8 | 1.0  | 64.1                               | 5.0                                  | 14.6                          | 103                                   | 0.105                                            |
| STUN082 | 73.8                                 | 90.2 | 1.0  | 66.4                               | 5.0                                  | 12.7                          | 118                                   | 0.105                                            |
| STUN582 | 77.9                                 | 86.1 | 1.0  | 70.1                               | 5.0                                  | 13.3                          | 113                                   | 0.105                                            |
| STUN091 | 81.9                                 | 100  | 1.0  | 73.7                               | 5.0                                  | 11.4                          | 131                                   | 0.106                                            |
| STUN591 | 86.5                                 | 95.5 | 1.0  | 77.8                               | 5.0                                  | 12.0                          | 125                                   | 0.106                                            |
| STUN0B0 | 90.0                                 | 110  | 1.0  | 81.0                               | 5.0                                  | 10.4                          | 144                                   | 0.106                                            |
| STUN5B0 | 95.0                                 | 105  | 1.0  | 85.5                               | 5.0                                  | 11.0                          | 137                                   | 0.106                                            |
| STUN0B1 | 99.0                                 | 121  | 1.0  | 89.2                               | 5.0                                  | 9.5                           | 158                                   | 0.107                                            |
| STUN5B1 | 105                                  | 116  | 1.0  | 94.0                               | 5.0                                  | 9.9                           | 152                                   | 0.107                                            |
| STUN0B2 | 108                                  | 132  | 1.0  | 97.2                               | 5.0                                  | 8.7                           | 173                                   | 0.107                                            |
| STUN5B2 | 114                                  | 126  | 1.0  | 102                                | 5.0                                  | 9.1                           | 165                                   | 0.107                                            |
| STUN0B3 | 117                                  | 143  | 1.0  | 105                                | 5.0                                  | 8.0                           | 187                                   | 0.107                                            |
| STUN5B3 | 124                                  | 137  | 1.0  | 111                                | 5.0                                  | 8.4                           | 179                                   | 0.107                                            |
| STUN0B5 | 135                                  | 165  | 1.0  | 121                                | 5.0                                  | 7.0                           | 215                                   | 0.108                                            |
| STUN5B5 | 143                                  | 158  | 1.0  | 128                                | 5.0                                  | 7.2                           | 207                                   | 0.108                                            |
| STUN0B6 | 144                                  | 176  | 1.0  | 130                                | 5.0                                  | 6.5                           | 230                                   | 0.108                                            |
| STUN5B6 | 152                                  | 168  | 1.0  | 136                                | 5.0                                  | 6.8                           | 219                                   | 0.108                                            |
| STUN0B7 | 153                                  | 187  | 1.0  | 138                                | 5.0                                  | 6.2                           | 244                                   | 0.108                                            |
| STUN5B7 | 162                                  | 179  | 1.0  | 145                                | 5.0                                  | 6.4                           | 234                                   | 0.108                                            |
| STUN0B8 | 162                                  | 198  | 1.0  | 146                                | 5.0                                  | 5.8                           | 258                                   | 0.108                                            |
| STUN5B8 | 171                                  | 189  | 1.0  | 154                                | 5.0                                  | 6.1                           | 246                                   | 0.108                                            |
| STUN0D0 | 180                                  | 220  | 1.0  | 162                                | 5.0                                  | 5.2                           | 287                                   | 0.108                                            |
| STUN5D0 | 190                                  | 210  | 1.0  | 171                                | 5.0                                  | 5.5                           | 274                                   | 0.108                                            |

### Note:

- ( 1 )  $V_{BR}$  measured after  $I_t$  applied for 300  $\mu$ s.,  $I_t$  = square wave pulse or equivalent.
- ( 2 )  $V_F$  = 3.5  $V_{max.}$ ,  $I_F$  = 100 Amps. ( 6.8 Volts thru 91 Volts )  
 $V_F$  = 5.0  $V_{max.}$ ,  $I_F$  = 100 Amps. ( 100 Volts thru 200 Volts ) per 1/2 square or equivalent sine wave.  
PW = 8.3 ms, duty cycle = 4 pulses per minute maximum.
- ( 3 ) "STU" or "STB" will be omitted in marking on the diode.

## RATING AND CHARACTERISTIC CURVES ( STUN06I - STUN5D0 )

FIG.1 - PULSE DERATING CURVE




FIG.2 - MAXIMUM NON-REPETITIVE SURGE CURRENT




FIG.3 - STEADY STATE POWER DERATING




FIG.4 - PULSE RATING CURVE




FIG.5 - PULSE WAVEFORM

