

Solid Tantalum Surface Mount Chip Capacitors

TANTAMOUNT®, Molded Case, Hi-Rel COTS, Built-In-Fuse



PERFORMANCE / ELECTRICAL CHARACTERISTICS

www.vishay.com/doc?40209

Operating Temperature: -55 °C to +125 °C
(Above 85 °C voltage derating is required)

Capacitance Range: 0.47 µF to 470 µF

Capacitance Tolerance: ± 10 %, ± 20 %

Voltage Rating: 4 V_{DC} to 50 V_{DC}

FEATURES

- Weibull grading and surge current test options per MIL-PRF-55365
- Standard and low ESR options
- Terminations: 100 % matte tin standard
- Molded case available in three case sizes
- Compliant terminations
- Compatible with high volume" automatic pick and place equipment
- Moisture sensitivity level 1
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912



RoHS*
Available

Note

* This datasheet provides information about parts that are RoHS-compliant and / or parts that are non-RoHS-compliant. For example, parts with lead (Pb) terminations are not RoHS-compliant. Please see the information / tables in this datasheet for details.

APPLICATIONS

- Industrial
- Medical
- Military / aerospace
- Telecom

ORDERING INFORMATION

T86	D	107	K	010	E	A	A	S
TYPE	CASE CODE	CAPACITANCE	CAPACITANCE TOLERANCE	DC VOLTAGE RATING AT +85 °C	TERMINATION/ PACKAGING ⁽¹⁾	RELIABILITY LEVEL	SURGE CURRENT	ESR
	See Ratings and Case Codes Table	This is expressed in picofarads. The first two digits are the significant figures. The third is the number of zeros to follow.	K = ± 10 % M = ± 20 % J = ± 5 % (special order)	This is expressed in V. To complete the three-digit block, zeros precede the voltage rating. A decimal point is indicated by an "R" (6R3 = 6.3 V).	See table Termination and Packaging Codes	A = 1.0 % B = 0.1 % C = 0.01 % S = hi-rel standard Z = non-ER	A = 10 cycles at +25 °C B = 10 cycles at -55 °C / +85 °C S = 3 cycles at +25 °C	S = std. L = low

Note


⁽¹⁾ Vishay will discontinue tin / lead (Sn / Pb) terminations manufacturing.

TERMINATION AND PACKAGING CODES

CODE	TERMINATION	PACKAGING
C	Matte tin	7" (178 mm) reels
H	Matte tin	7" (178 mm) reels, ½ reel
Z	Matte tin	7" (178 mm) reels, partial reel
V	Matte tin	7" (178 mm) reels, dry pack
E	Solder plated, tin / lead	7" (178 mm) reels
L	Solder plated, tin / lead	7" (178 mm) reels, ½ reel
R	Solder plated, tin / lead	7" (178 mm) reels, partial reel
T	Solder plated	7" (178 mm) reels, dry pack
K	Solder fused, tin / lead	7" (178 mm) reels
M	Solder fused, tin / lead	7" (178 mm) reels, ½ reel
N	Solder fused, tin / lead	7" (178 mm) reels, partial reel
S	Solder fused, tin / lead	7" (178 mm) reels, dry pack

Note

- Dry pack as specified in J-STD-033 for MSL3. Applicable for D and E cases only.

DIMENSIONS in inches [millimeters]




CASE CODE	EIA SIZE	L	W	H	P	Tw	TH (MIN.)
C	6032-28	0.236 ± 0.012 [6.0 ± 0.30]	0.126 ± 0.012 [3.2 ± 0.30]	0.098 ± 0.012 [2.5 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.087 ± 0.004 [2.2 ± 0.10]	0.039 [1.0]
D	7343-31	0.287 ± 0.012 [7.3 ± 0.30]	0.169 ± 0.012 [4.3 ± 0.30]	0.110 ± 0.012 [2.8 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.094 ± 0.004 [2.4 ± 0.10]	0.039 [1.0]
E	7343-43	0.287 ± 0.012 [7.3 ± 0.30]	0.169 ± 0.012 [4.3 ± 0.30]	0.157 ± 0.012 [4.0 ± 0.30]	0.051 ± 0.012 [1.3 ± 0.30]	0.094 ± 0.004 [2.4 ± 0.10]	0.039 [1.0]

Note


- Glue pad (non-conductive, part of molded case) is dedicated for glue attachment (as user option).

RATINGS AND CASE CODES

μF	4 V	6.3 V	10 V	16 V	20 V	25 V	35 V	50 V
0.47								C
0.68								C
1.0								C
1.5							C	C
2.2						C	C	C / D
3.3						C	C	C / D
4.7					C	C	C / D	D
6.8				C	C	C	D	D / E
10			C	C	C	C / D	D / E	
15		C	C	C	C / D	D	D / E	
22		C	C	C / D	D	D / E	E	
33		C	C / D	C / D	D / E	E		
47		C / D	C / D	D / E	E			
68	C	C / D	D / E	D	E			
100	C	D / E	D	E				
150	D	D	D / E	E				
220	D	D / E	E					
330	D / E	E						
470	E							

CONSTRUCTION AND MARKING

Marking:

Capacitor marking includes an anode (+) polarity band, capacitance in microfarads and the voltage rating. The Vishay Sprague® trademark is included if space permits. Capacitors rated at 6.3 V are marked 6 V. A manufacturing date code is marked on all capacitors. Capital letter "E" stands for lead (Pb)-free terminations small cap letter "e" stands for SnPb

FUSE ACTIVATION

STANDARD RATINGS

CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	STANDARD (S) MAX. ESR AT +25 °C 100 kHz (Ω)	LOW (L) MAX. ESR AT +25 °C 100 kHz (Ω)	AVAILABLE RELIABILITY LEVEL
4 V_{DC} AT +85 °C; 2.7 V_{DC} AT +125 °C							
68	C	T86C686(1)004(2)(6)(4)(5)	2.7	8	1.40	0.40	A, B, C, S, Z
100	C	T86C107(1)004(2)(3)(4)(5)	4.0	8	0.80	0.40	A, B, S, Z
150	D	T86D157(1)004(7)(6)(4)(5)	6.0	8	0.60	0.30	A, B, C, S, Z
220	D	T86D227(1)004(7)(3)(4)(5)	8.8	8	0.60	0.40	A, B, S, Z
330	D	T86D337(1)004(7)(3)(4)(5)	13.2	15	0.60	0.30	A, B, S, Z
330	E	T86E337(1)004(7)(3)(4)(5)	13.2	8	0.50	0.30	A, B, S, Z
470	E	T86E477(1)004(7)(3)(4)(5)	18.8	16	0.50	0.25	A, B, S, Z
6.3 V_{DC} AT +85 °C; 4 V_{DC} AT +125 °C							
15	C	T86C156(1)6R3(2)(6)(4)(5)	0.9	6	1.80	0.60	A, B, C, S, Z
22	C	T86C226(1)6R3(2)(6)(4)(5)	1.1	6	1.80	0.60	A, B, C, S, Z
33	C	T86C336(1)6R3(2)(6)(4)(5)	1.6	6	1.40	0.60	A, B, C, S, Z
47	C	T86C476(1)6R3(2)(6)(4)(5)	2.3	6	1.30	0.60	A, B, C, S, Z
47	D	T86D476(1)6R3(7)(6)(4)(5)	2.3	6	0.90	0.45	A, B, C, S, Z
68	C	T86C686(1)6R3(2)(3)(4)S	3.3	6	0.80	n/a	A, B, S, Z
68	D	T86D686(1)6R3(7)(6)(4)(5)	3.3	6	0.70	0.35	A, B, C, S, Z
100	D	T86D107(1)6R3(7)(6)(4)(5)	6.0	8	0.70	0.35	A, B, C, S, Z
100	E	T86E107(1)6R3(7)(6)(4)(5)	6.0	8	0.70	0.30	A, B, C, S, Z
150	D	T86D157(1)6R3(7)(3)(4)(5)	9.0	8	0.60	0.30	A, B, S, Z
220	D	T86D227(1)6R3(7)(3)(4)(5)	13.2	8	0.60	0.30	A, B, S, Z
220	E	T86E227(1)6R3(7)(3)(4)(5)	13.2	8	0.50	0.30	A, B, S, Z
330	E	T86E337(1)6R3(7)(3)(4)(5)	19.8	8	0.50	0.30	A, B, S, Z

Note

- Part number definitions:
 - Capacitance tolerance codes: K, M
 - Terminations and packaging codes: C, E, K, H, L, M, Z, R, N
 - Reliability level: A, B, S, Z
 - Surge current: A, B, S
 - ESR: L, S
 - Reliability level: A, B, C, S, Z
 - Terminations and packaging codes: C, E, K, H, L, M, Z, R, N, V, T, S



STANDARD RATINGS							
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	STANDARD (S) MAX. ESR AT +25 °C 100 kHz (Ω)	LOW (L) MAX. ESR AT +25 °C 100 kHz (Ω)	AVAILABLE RELIABILITY LEVEL
10 V _{DC} AT +85 °C; 7 V _{DC} AT +125 °C							
10	C	T86C106(1)010(2)(6)(4)S	1.0	6	1.80	n/a	A, B, C, S, Z
15	C	T86C156(1)010(2)(6)(4)(5)	1.5	6	1.80	0.60	A, B, C, S, Z
22	C	T86C226(1)010(2)(6)(4)(5)	2.2	6	1.40	0.50	A, B, C, S, Z
33	C	T86C336(1)010(2)(6)(4)(5)	3.3	6	1.30	0.40	A, B, C, S, Z
33	D	T86D336(1)010(7)(6)(4)(5)	3.3	6	0.90	0.40	A, B, C, S, Z
47	C	T86C476(1)010(2)(3)(4)S	4.7	6	1.00	n/a	A, B, S, Z
47	D	T86D476(1)010(7)(6)(4)(5)	4.7	6	0.70	0.40	A, B, C, S, Z
68	D	T86D686(1)010(7)(6)(4)(5)	6.8	6	0.70	0.35	A, B, C, S, Z
68	E	T86E686(1)010(7)(6)(4)(5)	6.8	6	0.70	0.35	A, B, C, S, Z
100	D	T86D107(1)010(7)(3)(4)(5)	10.0	8	0.60	0.30	A, B, S, Z
150	D	T86D157(1)010(7)(3)(4)(5)	15.0	8	0.60	0.30	A, B, S, Z
150	E	T86E157(1)010(7)(3)(4)(5)	15.0	8	0.50	0.40	A, B, S, Z
220	E	T86E227(1)010(7)(3)(4)(5)	22.0	8	0.50	0.30	A, B, S, Z
16 V _{DC} AT +85 °C; 10 V _{DC} AT +125 °C							
6.8	C	T86C685(1)016(2)(6)(4)(5)	1.1	6	2.00	0.60	A, B, C, S, Z
10	C	T86C106(1)016(2)(6)(4)(5)	1.6	6	1.80	0.70	A, B, C, S, Z
15	C	T86C156(1)016(2)(6)(4)S	2.4	6	1.40	n/a	A, B, C, S, Z
22	C	T86C226(1)016(2)(6)(4)(5)	3.5	6	1.30	0.70	A, B, C, S, Z
22	D	T86D226(1)016(7)(6)(4)(5)	3.5	6	0.90	0.45	A, B, C, S, Z
33	C	T86C336(1)016(2)(3)(4)(5)	5.3	6	1.00	0.50	A, B, C, S, Z
33	D	T86D336(1)016(7)(6)(4)(5)	5.3	6	0.70	0.35	A, B, C, S, Z
47	D	T86D476(1)016(7)(6)(4)(5)	7.5	6	0.70	0.35	A, B, C, S, Z
47	E	T86E476(1)016(7)(6)(4)(5)	7.5	6	0.70	0.35	A, B, C, S, Z
68	D	T86D686(1)016(7)(3)(4)(5)	10.9	6	0.60	0.30	A, B, S, Z
100	E	T86E107(1)016(7)(3)(4)(5)	16.0	8	0.60	0.30	A, B, S, Z
150	E	T86E157(1)016(7)(3)(4)S	24.0	10	0.40	n/a	A, B, S, Z
20 V _{DC} AT +85 °C; 13 V _{DC} AT +125 °C							
4.7	C	T86C475(1)020(2)(6)(4)(5)	0.9	6	2.00	1.00	A, B, C, S, Z
6.8	C	T86C685(1)020(2)(6)(4)(5)	1.4	6	1.90	0.6	A, B, C, S, Z
10	C	T86C106(1)020(2)(6)(4)(5)	2.0	6	1.60	0.8	A, B, C, S, Z
15	C	T86C156(1)020(2)(6)(4)S	3.0	6	1.40	n/a	A, B, C, S, Z
15	D	T86D156(1)020(7)(6)(4)(5)	3.0	6	0.90	0.45	A, B, C, S, Z
22	D	T86D226(1)020(7)(6)(4)(5)	4.4	6	0.70	0.35	A, B, C, S, Z
33	D	T86D336(1)020(7)(6)(4)(5)	6.6	6	0.70	0.40	A, B, C, S, Z
33	E	T86E336(1)020(7)(6)(4)(5)	6.6	6	0.70	0.40	A, B, C, S, Z
47	E	T86E476(1)020(7)(3)(4)(5)	9.4	6	0.60	0.30	A, B, S, Z
68	E	T86E686(1)020(7)(3)(4)(5)	13.6	6	0.60	0.30	A, B, S, Z

Note

- Part number definitions:
 - Capacitance tolerance codes: K, M
 - Terminations and packaging codes: C, E, K, H, L, M, Z, R, N
 - Reliability level: A, B, S, Z
 - Surge current: A, B, S
 - ESR: L, S
 - Reliability level: A, B, C, S, Z
 - Terminations and packaging codes: C, E, K, H, L, M, Z, R, N, V, T, S



STANDARD RATINGS							
CAPACITANCE (μ F)	CASE CODE	PART NUMBER	MAX. DCL AT +25 °C (μ A)	MAX. DF AT +25 °C 120 Hz (%)	STANDARD (S) MAX. ESR AT +25 °C 100 kHz (Ω)	LOW (L) MAX. ESR AT +25 °C 100 kHz (Ω)	AVAILABLE RELIABILITY LEVEL
25 V _{DC} AT +85 °C; 17 V _{DC} AT +125 °C							
2.2	C	T86C225(1)025(2)(6)(4)S	0.6	6	2.80	n/a	A, B, C, S, Z
3.3	C	T86C335(1)025(2)(6)(4)(5)	0.8	6	2.30	2.10	A, B, C, S, Z
4.7	C	T86C475(1)025(2)(6)(4)(5)	1.2	6	1.90	1.00	A, B, C, S, Z
6.8	C	T86C685(1)025(2)(6)(4)(5)	1.7	6	1.60	0.60	A, B, C, S, Z
10	C	T86C106(1)025(2)(6)(4)(5)	2.5	6	1.40	0.60	A, B, C, S, Z
10	D	T86D106(1)025(7)(6)(4)(5)	2.5	6	1.00	0.50	A, B, C, S, Z
15	D	T86D156(1)025(7)(6)(4)(5)	3.8	6	0.80	0.40	A, B, C, S, Z
22	D	T86D226(1)025(7)(6)(4)(5)	5.5	6	0.70	0.35	A, B, C, S, Z
22	E	T86E226(1)025(7)(6)(4)(5)	5.5	6	0.70	0.35	A, B, C, S, Z
33	E	T86E336(1)025(7)(3)(4)(5)	8.3	6	0.60	0.30	A, B, C, S, Z
35 V _{DC} AT +85 °C; 23 V _{DC} AT +125 °C							
1.5	C	T86C155(1)035(2)(6)(4)(5)	0.5	6	3.80	2.60	A, B, C, S, Z
2.2	C	T86C225(1)035(2)(6)(4)S	0.8	6	2.90	n/a	A, B, C, S, Z
3.3	C	T86C335(1)035(2)(6)(4)S	1.2	6	2.00	n/a	A, B, C, S, Z
4.7	C	T86C475(1)035(2)(6)(4)S	1.6	6	1.80	n/a	A, B, C, S, Z
4.7	D	T86D475(1)035(7)(6)(4)(5)	1.6	6	1.20	0.60	A, B, C, S, Z
6.8	D	T86D685(1)035(7)(6)(4)(5)	2.4	6	1.00	0.50	A, B, C, S, Z
10	D	T86D106(1)035(7)(6)(4)(5)	3.5	6	0.80	0.50	A, B, C, S, Z
10	E	T86E106(1)035(7)(6)(4)(5)	3.5	6	0.80	0.50	A, B, C, S, Z
15	D	T86D156(1)035(7)(3)(4)(5)	5.3	6	0.70	0.50	A, B, S, Z
15	E	T86E156(1)035(7)(3)(4)(5)	5.3	6	0.70	0.50	A, B, S, Z
22	E	T86E226(1)035(7)(3)(4)(5)	7.7	6	0.60	0.40	A, B, S, Z
50 V _{DC} AT +85 °C; 33 V _{DC} AT +125 °C							
0.47	C	T86C474(1)050(2)(6)(4)S	0.5	4	6.70	n/a	A, B, C, S, Z
0.68	C	T86C684(1)050(2)(6)(4)S	0.5	4	5.90	n/a	A, B, C, S, Z
1.0	C	T86C105(1)050(2)(6)(4)(5)	0.5	4	4.40	2.70	A, B, C, S, Z
1.5	C	T86C155(1)050(2)(6)(4)(5)	0.8	6	5.00	3.20	A, B, C, S, Z
2.2	C	T86C225(1)050(2)(6)(4)S	1.1	6	2.80	n/a	A, B, C, S, Z
2.2	D	T86D225(1)050(7)(6)(4)(5)	1.1	6	2.10	0.90	A, B, C, S, Z
3.3	C	T86C335(1)050(2)(6)(4)(5)	1.7	6	2.40	1.60	A, B, C, S, Z
3.3	D	T86D335(1)050(7)(6)(4)S	1.7	6	2.00	n/a	A, B, C, S, Z
4.7	D	T86D475(1)050(7)(6)(4)S	2.4	6	1.10	n/a	A, B, C, S, Z
6.8	D	T86D685(1)050(7)(6)(4)S	3.4	6	0.90	n/a	A, B, C, S, Z
6.8	E	T86E685(1)050(7)(6)(4)S	3.4	6	0.90	n/a	A, B, C, S, Z

Note

- Part number definitions:
 - Capacitance tolerance codes: K, M
 - Terminations and packaging codes: C, E, K, H, L, M, Z, R, N
 - Reliability level: A, B, S, Z
 - Surge current: A, B, S
 - ESR: L, S
 - Reliability level: A, B, C, S, Z
 - Terminations and packaging codes: C, E, K, H, L, M, Z, R, N, V, T, S



RECOMMENDED VOLTAGE DERATING GUIDELINES (for temperatures below +85 °C)


STANDARD CONDITIONS. FOR EXAMPLE: OUTPUT FILTERS

Capacitor Voltage Rating	Operating Voltage
4.0	2.5
6.3	3.6
10	6.0
16	10
20	12
25	15
35	24
50	28

SEVERE CONDITIONS. FOR EXAMPLE: INPUT FILTERS

Capacitor Voltage Rating	Operating Voltage
4.0	2.5
6.3	3.3
10	5.0
16	8.0
20	10
25	12
35	15
50	24

TYPICAL CURVES AT +25 °C, IMPEDANCE AND ESR VS. FREQUENCY



**POWER DISSIPATION**

CASE CODE	MAXIMUM PERMISSIBLE POWER DISSIPATION AT +25 °C (W) IN FREE AIR
C	0.110
D	0.150
E	0.165

STANDARD PACKAGING QUANTITY

CASE CODE	UNITS PER REEL		
	7" REEL	½ 7" REEL	7" PARTIAL REEL
C	500	250	100
D	500	250	100
E	400	200	100

PRODUCT INFORMATION

Guide for Molded Tantalum Capacitors	www.vishay.com/doc?40074
Pad Dimensions	
Package Dimensions	
Moisture Sensitivity	www.vishay.com/doc?40135
SELECTOR GUIDES	
Solid Tantalum Selector Guide	www.vishay.com/doc?49053
Solid Tantalum Chip Capacitors	www.vishay.com/doc?40091
FAQ	
Frequently Asked Questions	www.vishay.com/doc?40110



Guide for Molded Tantalum Capacitors

INTRODUCTION

Tantalum electrolytic capacitors are the preferred choice in applications where volumetric efficiency, stable electrical parameters, high reliability, and long service life are primary considerations. The stability and resistance to elevated temperatures of the tantalum / tantalum oxide / manganese dioxide system make solid tantalum capacitors an appropriate choice for today's surface mount assembly technology.

Vishay Sprague has been a pioneer and leader in this field, producing a large variety of tantalum capacitor types for consumer, industrial, automotive, military, and aerospace electronic applications.

Tantalum is not found in its pure state. Rather, it is commonly found in a number of oxide minerals, often in combination with Columbium ore. This combination is known as "tantalite" when its contents are more than one-half tantalum. Important sources of tantalite include Australia, Brazil, Canada, China, and several African countries. Synthetic tantalite concentrates produced from tin slags in Thailand, Malaysia, and Brazil are also a significant raw material for tantalum production.

Electronic applications, and particularly capacitors, consume the largest share of world tantalum production. Other important applications for tantalum include cutting tools (tantalum carbide), high temperature super alloys, chemical processing equipment, medical implants, and military ordnance.

Vishay Sprague is a major user of tantalum materials in the form of powder and wire for capacitor elements and rod and sheet for high temperature vacuum processing.

THE BASICS OF TANTALUM CAPACITORS

Most metals form crystalline oxides which are non-protecting, such as rust on iron or black oxide on copper. A few metals form dense, stable, tightly adhering, electrically insulating oxides. These are the so-called "valve" metals and include titanium, zirconium, niobium, tantalum, hafnium, and aluminum. Only a few of these permit the accurate control of oxide thickness by electrochemical means. Of these, the most valuable for the electronics industry are aluminum and tantalum.

Capacitors are basic to all kinds of electrical equipment, from radios and television sets to missile controls and automobile ignitions. Their function is to store an electrical charge for later use.

Capacitors consist of two conducting surfaces, usually metal plates, whose function is to conduct electricity. They are separated by an insulating material or dielectric. The dielectric used in all tantalum electrolytic capacitors is tantalum pentoxide.

Tantalum pentoxide compound possesses high-dielectric strength and a high-dielectric constant. As capacitors are being manufactured, a film of tantalum pentoxide is applied to their electrodes by means of an electrolytic process. The film is applied in various thicknesses and at various voltages and although transparent to begin with, it takes on different colors as light refracts through it. This coloring occurs on the tantalum electrodes of all types of tantalum capacitors.

Rating for rating, tantalum capacitors tend to have as much as three times better capacitance / volume efficiency than aluminum electrolytic capacitors. An approximation of the capacitance / volume efficiency of other types of capacitors may be inferred from the following table, which shows the dielectric constant ranges of the various materials used in each type. Note that tantalum pentoxide has a dielectric constant of 26, some three times greater than that of aluminum oxide. This, in addition to the fact that extremely thin films can be deposited during the electrolytic process mentioned earlier, makes the tantalum capacitor extremely efficient with respect to the number of microfarads available per unit volume. The capacitance of any capacitor is determined by the surface area of the two conducting plates, the distance between the plates, and the dielectric constant of the insulating material between the plates.

COMPARISON OF CAPACITOR DIELECTRIC CONSTANTS

DIELECTRIC	ϵ DIELECTRIC CONSTANT
Air or vacuum	1.0
Paper	2.0 to 6.0
Plastic	2.1 to 6.0
Mineral oil	2.2 to 2.3
Silicone oil	2.7 to 2.8
Quartz	3.8 to 4.4
Glass	4.8 to 8.0
Porcelain	5.1 to 5.9
Mica	5.4 to 8.7
Aluminum oxide	8.4
Tantalum pentoxide	26
Ceramic	12 to 400K

In the tantalum electrolytic capacitor, the distance between the plates is very small since it is only the thickness of the tantalum pentoxide film. As the dielectric constant of the tantalum pentoxide is high, the capacitance of a tantalum capacitor is high if the area of the plates is large:

$$C = \frac{\epsilon A}{t}$$

where

C = capacitance

ϵ = dielectric constant

A = surface area of the dielectric

t = thickness of the dielectric

Tantalum capacitors contain either liquid or solid electrolytes. In solid electrolyte capacitors, a dry material (manganese dioxide) forms the cathode plate. A tantalum lead is embedded in or welded to the pellet, which is in turn connected to a termination or lead wire. The drawings show the construction details of the surface mount types of tantalum capacitors shown in this catalog.



SOLID ELECTROLYTE TANTALUM CAPACITORS

Solid electrolyte capacitors contain manganese dioxide, which is formed on the tantalum pentoxide dielectric layer by impregnating the pellet with a solution of manganous nitrate. The pellet is then heated in an oven, and the manganous nitrate is converted to manganese dioxide.

The pellet is next coated with graphite, followed by a layer of metallic silver, which provides a conductive surface between the pellet and the Leadframe.

Molded Chip tantalum capacitor encases the element in plastic resins, such as epoxy materials. After assembly, the capacitors are tested and inspected to assure long life and reliability. It offers excellent reliability and high stability for consumer and commercial electronics with the added feature of low cost

Surface mount designs of “Solid Tantalum” capacitors use lead frames or lead frameless designs as shown in the accompanying drawings.

TANTALUM CAPACITORS FOR ALL DESIGN CONSIDERATIONS


Solid electrolyte designs are the least expensive for a given rating and are used in many applications where their very small size for a given unit of capacitance is of importance. They will typically withstand up to about 10 % of the rated DC working voltage in a reverse direction. Also important are their good low temperature performance characteristics and freedom from corrosive electrolytes.

Vishay Sprague patented the original solid electrolyte capacitors and was the first to market them in 1956. Vishay Sprague has the broadest line of tantalum capacitors and has continued its position of leadership in this field. Data sheets covering the various types and styles of Vishay Sprague capacitors for consumer and entertainment electronics, industry, and military applications are available where detailed performance characteristics must be specified.

MOLDED CHIP CAPACITOR, ALL TYPES EXCEPT 893D / TF3 / T86



MOLDED CHIP CAPACITOR WITH BUILT-IN FUSE, TYPES 893D / TF3 / T86




COMMERCIAL PRODUCTS

SOLID TANTALUM CAPACITORS - MOLDED CASE						
SERIES	293D	793DE-793DX-CTC3-CTC4	593D	TR3	TP3	TL3
PRODUCT IMAGE						
TYPE	Surface mount TANTAMOUNT®, molded case					
FEATURES	Standard industrial grade	CECC approved	Low ESR	Low ESR	High performance, automotive grade	Very low DCL
TEMPERATURE RANGE	-55 °C to +125 °C					
CAPACITANCE RANGE	0.1 µF to 1000 µF	0.1 µF to 100 µF	1 µF to 470 µF	0.47 µF to 1000 µF	0.1 µF to 470 µF	0.1 µF to 470 µF
VOLTAGE RANGE	4 V to 75 V	4 V to 50 V	4 V to 50 V	4 V to 75 V	4 V to 50 V	4 V to 50 V
CAPACITANCE TOLERANCE	± 10 %, ± 20 %					
LEAKAGE CURRENT	0.01 CV or 0.5 µA, whichever is greater					0.005 CV or 0.25 µA, whichever is greater
DISSIPATION FACTOR	4 % to 30 %	4 % to 6 %	4 % to 15 %	4 % to 30 %	4 % to 15 %	4 % to 15 %
CASE CODES	A, B, C, D, E, V	A, B, C, D	A, B, C, D, E	A, B, C, D, E, V, W	A, B, C, D, E	A, B, C, D, E
TERMINATION	100 % matte tin standard, tin / lead available					

SOLID TANTALUM CAPACITORS - MOLDED CASE					
SERIES	TH3	TH4	TH5	893D	TF3
PRODUCT IMAGE					
TYPE	Surface mount TANTAMOUNT®, molded case				
FEATURES	High temperature +150 °C, automotive grade	High temperature +175 °C, automotive grade	Very high temperature +200 °C	Built-in fuse	Built-in fuse, low ESR
TEMPERATURE RANGE	-55 °C to +150 °C	-55 °C to +175 °C	-55 °C to +200 °C	-55 °C to +125 °C	
CAPACITANCE RANGE	0.33 µF to 220 µF	10 µF to 47 µF	4.7 µF to 100 µF	0.47 µF to 680 µF	0.47 µF to 470 µF
VOLTAGE RANGE	6.3 V to 50 V	6.3 V to 35 V	5 V to 24 V	4 V to 50 V	4 V to 50 V
CAPACITANCE TOLERANCE	± 10 %, ± 20 %				
LEAKAGE CURRENT	0.01 CV or 0.5 µA, whichever is greater				
DISSIPATION FACTOR	4 % to 8 %	4.5 % to 6 %	6 % to 10 %	6 % to 15 %	6 % to 15 %
CASE CODES	A, B, C, D, E	B, C, D	E	C, D, E	C, D, E
TERMINATION	100 % matte tin standard, tin / lead and gold plated available	100 % matte tin	Gold plated	100 % matte tin standard	

HIGH RELIABILITY PRODUCTS

SOLID TANTALUM CAPACITORS - MOLDED CASE				
SERIES	T83	T86	CWR11	95158
PRODUCT IMAGE				
TYPE	TANTAMOUNT®, molded case, Hi-Rel. COTS		TANTAMOUNT®, molded case, DLA approved	
FEATURES	High reliability, standard and low ESR	High reliability, built-in fuse, standard and low ESR	MIL-PRF-55365/8 qualified	Low ESR
TEMPERATURE RANGE	-55 °C to +125 °C			
CAPACITANCE RANGE	0.1 µF to 470 µF	0.47 µF to 330 µF	0.1 µF to 100 µF	4.7 µF to 220 µF
VOLTAGE RANGE	4 V to 63 V	4 V to 50 V		
CAPACITANCE TOLERANCE	± 10 %, ± 20 %		± 5 %, ± 10 %, ± 20 %	± 10 %, ± 20 %
LEAKAGE CURRENT	0.01 CV or 0.5 µA, whichever is greater			
DISSIPATION FACTOR	4 % to 15 %	6 % to 16 %	4 % to 6 %	4 % to 12 %
CASE CODES	A, B, C, D, E	C, D, E	A, B, C, D	C, D, E
TERMINATION	100 % matte tin; tin / lead; tin / lead solder fused	100 % matte tin; tin / lead solder fused	Tin / lead; tin / lead solder fused	Tin / lead solder plated; gold plated

PLASTIC TAPE AND REEL PACKAGING in inches [millimeters]




Notes

- Metric dimensions will govern. Dimensions in inches are rounded and for reference only.
- (1) A₀, B₀, K₀, are determined by the maximum dimensions to the ends of the terminals extending from the component body and / or the body dimensions of the component. The clearance between the ends of the terminals or body of the component to the sides and depth of the cavity (A₀, B₀, K₀) must be within 0.002" (0.05 mm) minimum and 0.020" (0.50 mm) maximum. The clearance allowed must also prevent rotation of the component within the cavity of not more than 20°.
- (2) Tape with components shall pass around radius "R" without damage. The minimum trailer length may require additional length to provide "R" minimum for 12 mm embossed tape for reels with hub diameters approaching N minimum.
- (3) This dimension is the flat area from the edge of the sprocket hole to either outward deformation of the carrier tape between the embossed cavities or to the edge of the cavity whichever is less.
- (4) This dimension is the flat area from the edge of the carrier tape opposite the sprocket holes to either the outward deformation of the carrier tape between the embossed cavity or to the edge of the cavity whichever is less.
- (5) The embossed hole location shall be measured from the sprocket hole controlling the location of the embossement. Dimensions of embossement location shall be applied independent of each other.
- (6) B₁ dimension is a reference dimension tape feeder clearance only.

CASE CODE	TAPE SIZE	B ₁ (MAX.)	D ₁ (MIN.)	F	K ₀ (MAX.)	P ₁	W
293D - 593D - 893D - TR3 - TH3 - TF3 - TP3 - 793DE / 793DX / CTC3 / CTC4							
A	8 mm	0.165 [4.2]	0.039 [1.0]	0.138 ± 0.002 [3.5 ± 0.05]	0.094 [2.4]	0.157 ± 0.004 [4.0 ± 1.0]	0.315 ± 0.012 [8.0 ± 0.30]
B							
C							
D							
E	12 mm	0.32 [8.2]	0.059 [1.5]	0.217 ± 0.00 [5.5 ± 0.05]	0.177 [4.5]	0.315 ± 0.004 [8.0 ± 1.0]	0.472 ± 0.012 [12.0 ± 0.30]
V							
W							

RECOMMENDED REFLOW PROFILES

Capacitors should withstand reflow profile as per J-STD-020 standard




PROFILE FEATURE	SnPb EUTECTIC ASSEMBLY	LEAD (Pb)-FREE ASSEMBLY
Preheat / soak		
Temperature min. ($T_{s \text{ min.}}$)	100 °C	150 °C
Temperature max. ($T_{s \text{ max.}}$)	150 °C	200 °C
Time (t_s) from ($T_{s \text{ min.}}$ to $T_{s \text{ max.}}$)	60 s to 120 s	60 s to 120 s
Ramp-up		
Ramp-up rate (T_L to T_p)	3 °C/s max.	3 °C/s max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60 s to 150 s	60 s to 150 s
Peak package body temperature (T_p)	Depends on case size - see table below	
Time (t_p) within 5 °C of the specified classification temperature (T_C)	20 s	30 s
Time 25 °C to peak temperature	6 min max.	8 min max.
Ramp-down		
Ramp-down rate (T_p to T_1)	6 °C/s max.	6 °C/s max.

PEAK PACKAGE BODY TEMPERATURE (T_p)

CASE CODE	PEAK PACKAGE BODY TEMPERATURE (T _p)	
	SnPb EUTECTIC PROCESS	LEAD (Pb)-FREE PROCESS
A, B, C, V	235 °C	260 °C
D, E, W	220 °C	250 °C

PAD DIMENSIONS in inches [millimeters]



CASE CODE	A (MIN.)	B (NOM.)	C (NOM.)	D (NOM.)
293D - 593D - 893D - TR3 - TL3 - TH3 - TH4 - TH5 - TF3 - TP3 - 793DE / 793DX / CTC3 / CTC4 - T83 - T86 - CWR11 - 95158				
A	0.071 [1.80]	0.067 [1.70]	0.053 [1.35]	0.187 [4.75]
B	0.118 [3.00]	0.071 [1.80]	0.065 [1.65]	0.207 [5.25]
C	0.118 [3.00]	0.094 [2.40]	0.118 [3.00]	0.307 [7.80]
D	0.157 [4.00]	0.098 [2.50]	0.150 [3.80]	0.346 [8.80]
E	0.157 [4.00]	0.098 [2.50]	0.150 [3.80]	0.346 [8.80]
V	0.157 [4.00]	0.098 [2.50]	0.150 [3.80]	0.346 [8.80]
W	0.185 [4.70]	0.098 [2.50]	0.150 [3.80]	0.346 [8.80]



GUIDE TO APPLICATION

1. **AC Ripple Current:** the maximum allowable ripple current shall be determined from the formula:

$$I_{RMS} = \sqrt{\frac{P}{R_{ESR}}}$$

where,

P = power dissipation in W at +25 °C as given in the tables in the product datasheets (Power Dissipation).

R_{ESR} = the capacitor equivalent series resistance at the specified frequency

2. **AC Ripple Voltage:** the maximum allowable ripple voltage shall be determined from the formula:

$$V_{RMS} = I_{RMS} \times Z$$

or, from the formula:

$$V_{RMS} = Z \sqrt{\frac{P}{R_{ESR}}}$$

where,

P = power dissipation in W at +25 °C as given in the tables in the product datasheets (Power Dissipation).

R_{ESR} = the capacitor equivalent series resistance at the specified frequency

Z = the capacitor impedance at the specified frequency

- 2.1 The sum of the peak AC voltage plus the applied DC voltage shall not exceed the DC voltage rating of the capacitor.
- 2.2 The sum of the negative peak AC voltage plus the applied DC voltage shall not allow a voltage reversal exceeding 10 % of the DC working voltage at +25 °C.
3. **Reverse Voltage:** solid tantalum capacitors are not intended for use with reverse voltage applied. However, they have been shown to be capable of withstanding momentary reverse voltage peaks of up to 10 % of the DC rating at 25 °C and 5 % of the DC rating at +85 °C.
4. **Temperature Derating:** if these capacitors are to be operated at temperatures above +25 °C, the permissible RMS ripple current shall be calculated using the derating factors as shown:

TEMPERATURE	DERATING FACTOR
+25 °C	1.0
+85 °C	0.9
+125 °C	0.4

5. **Power Dissipation:** power dissipation will be affected by the heat sinking capability of the mounting surface. Non-sinusoidal ripple current may produce heating effects which differ from those shown. It is important that the equivalent I_{RMS} value be established when calculating permissible operating levels. (Power dissipation calculated using +25 °C temperature rise).

6. **Printed Circuit Board Materials:** molded capacitors are compatible with commonly used printed circuit board materials (alumina substrates, FR4, FR5, G10, PTFE-fluorocarbon and porcelainized steel).

7. **Attachment:**

- 7.1 **Solder Paste:** the recommended thickness of the solder paste after application is 0.007" ± 0.001" [0.178 mm ± 0.025 mm]. Care should be exercised in selecting the solder paste. The metal purity should be as high as practical. The flux (in the paste) must be active enough to remove the oxides formed on the metallization prior to the exposure to soldering heat. In practice this can be aided by extending the solder preheat time at temperatures below the liquidous state of the solder.

- 7.2 **Soldering:** capacitors can be attached by conventional soldering techniques; vapor phase, convection reflow, infrared reflow, wave soldering, and hot plate methods. The soldering profile charts show recommended time / temperature conditions for soldering. Preheating is recommended. The recommended maximum ramp rate is 2 °C per s. Attachment with a soldering iron is not recommended due to the difficulty of controlling temperature and time at temperature. The soldering iron must never come in contact with the capacitor.

- 7.2.1 **Backward and Forward Compatibility:** capacitors with SnPb or 100 % tin termination finishes can be soldered using SnPb or lead (Pb)-free soldering processes.

8. **Cleaning (Flux Removal) After Soldering:** molded capacitors are compatible with all commonly used solvents such as TES, TMS, Prelete, Chloroethane, Terpene and aqueous cleaning media. However, CFC / ODS products are not used in the production of these devices and are not recommended. Solvents containing methylene chloride or other epoxy solvents should be avoided since these will attack the epoxy encapsulation material.

- 8.1 When using ultrasonic cleaning, the board may resonate if the output power is too high. This vibration can cause cracking or a decrease in the adherence of the termination. DO NOT EXCEED 9W/l at 40 kHz for 2 min.

9. **Recommended Mounting Pad Geometries:** proper mounting pad geometries are essential for successful solder connections. These dimensions are highly process sensitive and should be designed to minimize component rework due to unacceptable solder joints. The dimensional configurations shown are the recommended pad geometries for both wave and reflow soldering techniques. These dimensions are intended to be a starting point for circuit board designers and may be fine tuned if necessary based upon the peculiarities of the soldering process and / or circuit board design.




COTS Tantalum Capacitors

ELECTRICAL PERFORMANCE CHARACTERISTICS				
ITEM	PERFORMANCE CHARACTERISTICS			
Category temperature range	-55 °C to +85 °C (to +125 °C with voltage derating)			
Capacitance tolerance	± 20 %, ± 10 %, tested via bridge method, at 25 °C, 120 Hz			
Dissipation factor	Limit per Standard Ratings table. Tested via bridge method, at 25 °C, 120 Hz			
ESR	Limit per Standard Ratings table. Tested via bridge method, at 25 °C, 100 kHz			
Leakage current	After application of rated voltage applied to capacitors for 5 min using a steady source of power with 1 k Ω resistor in series with the capacitor under test, leakage current at 25 °C is not more than 0.01 CV or 0.5 μ A, whichever is greater. <i>Note that the leakage current varies with temperature and applied voltage. See graph below for the appropriate adjustment factor.</i>			
Capacitance change by temperature	+15 % max. (at +125 °C) +10 % max. (at +85 °C) -10 % max. (at -55 °C)			
Reverse voltage	Capacitors are capable of withstanding peak voltages in the reverse direction equal to: 10 % of the DC rating at +25 °C 5 % of the DC rating at +85 °C 1 % of the DC rating at +125 °C Vishay does not recommend intentional or repetitive application of reverse voltage.			
Ripple current	For maximum ripple current values (at 25 °C) refer to relevant datasheet. If capacitors are to be used at temperatures above +25 °C, the permissible RMS ripple current (or voltage) shall be calculated using the derating factors: 1.0 at +25 °C 0.9 at +85 °C 0.4 at +125 °C			
Maximum operating and surge voltages vs. temperature	+85 °C		+125 °C	
	RATED VOLTAGE (V)	SURGE VOLTAGE (V)	CATEGORY VOLTAGE (V)	SURGE VOLTAGE (V)
	4.0	5.2	2.7	3.4
	6.3	8.0	4.0	5.0
	10	13	7.0	8.0
	16	20	10	12
	20	26	13	16
	25	32	17	20
	35	46	23	28
	40	52	26	31
	50	65	33	40
	50 ⁽¹⁾	60	33	40
	63	75	42	50
	75	75	50	50

Notes

- All information presented in this document reflects typical performance characteristics
- ⁽¹⁾ Capacitance value 15 μ F and higher

**TYPICAL LEAKAGE CURRENT - TEMPERATURE FACTOR****Notes**

- At +25 °C, the leakage current shall not exceed the value listed in the Standard Ratings table.
- At +85 °C, the leakage current shall not exceed 10 times the value listed in the Standard Ratings table.
- At +125 °C, the leakage current shall not exceed 12 times the value listed in the Standard Ratings table.

ENVIRONMENTAL PERFORMANCE CHARACTERISTICS

ITEM	CONDITION	POST TEST PERFORMANCE	
Surge voltage	MIL-PRF-55365 1000 successive test cycles at 85 °C of surge voltage (as specified in the table above), in series with a 33 Ω resistor at the rate of 30 s ON, 30 s OFF	Capacitance change Dissipation factor Leakage current	Within ± 10 % of initial value Initial specified limit Initial specified limit
Life test at +85 °C	MIL-STD-202, method 108 1000 h application of rated voltage at 85 °C	Capacitance change Dissipation factor Leakage current	Within ± 10 % of initial value Initial specified limit Shall not exceed 125 % of initial limit
Life test at +125 °C	MIL-STD-202, method 108 1000 h application 2/3 of rated voltage at 125 °C	Capacitance change Dissipation factor Leakage current	Within ± 10 % of initial value Initial specified limit Shall not exceed 125 % of initial limit
Moisture resistance	MIL-STD-202, method 106 at rated voltage, 20 cycles	Capacitance change Dissipation factor Leakage current	Within ± 15 % of initial value Shall not exceed 150 % of initial limit Shall not exceed 200 % of initial limit
Stability at low and high temperatures	MIL-PRF-55365	Delta cap limit at -55 °C, 85 °C is ± 10 % of initial value Delta cap limit at 125 °C is ± 15 % of initial value Delta cap at step 3 and final step 25 °C is ± 10 % DCL at 85 °C: 10 x initial specified value DCL at 125 °C: 12 x initial specified value DCL at 25 °C: initial specified value at RV	
Thermal shock	MIL-STD-202, method 107 At -55 °C / +125 °C, for 5 cycles, 30 min at each temperature	Capacitance change Dissipation factor Leakage current	Within ± 10 % of initial value Initial specified limit Initial specified limit



MECHANICAL PERFORMANCE CHARACTERISTICS		
ITEM	CONDITION	POST TEST PERFORMANCE
Terminal strength / Shear force test	Apply a pressure load of 5 N for 10 s $\pm$ 1 s horizontally to the center of capacitor side body	Capacitance change Within $\pm$ 10 % of initial value Dissipation factor Initial specified limit Leakage current Initial specified limit There shall be no mechanical or visual damage to capacitors post-conditioning.
Vibration	MIL-STD-202, method 204, condition D, 10 Hz to 2000 Hz, 20 g peak, 8 h, at rated voltage	Electrical measurements are not applicable, since the same parts are used for shock (specified pulse) test. There shall be no mechanical or visual damage to capacitors post-conditioning.
Shock (specified pulse)	MIL-STD-202, method 213, condition I, 100 g peak	Capacitance change Within $\pm$ 10 % of initial value Dissipation factor Initial specified limit Leakage current Initial specified limit There shall be no mechanical or visual damage to capacitors post-conditioning.
Resistance to soldering heat	MIL-STD-202, method 210, condition J (leadbearing capacitors) and K (lead (Pb)-free capacitors), one heat cycle	Capacitance change Within $\pm$ 10 % of initial value Dissipation factor Initial specified limit Leakage current Initial specified limit
Solderability	MIL-STD-202, method 208, ANSI/J-STD-002, test B (leadbearing) and B1 (lead (Pb)-free). Preconditioning per category C (category E - optional). Does not apply to gold terminations. Lead (Pb)-free and leadbearing capacitors are backward and forward compatible	Solder coating of all capacitors shall meet specified requirements. There shall be no mechanical or visual damage to capacitors post-conditioning.
Resistance to solvents	MIL-STD-202, method 215	There shall be no mechanical or visual damage to capacitors post-conditioning. Body marking shall remain legible.
Flammability	Encapsulation materials meet UL 94 V-0 with an oxygen index of 32 %	



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.