





I 2 3 4

A



B

C



A

B

C

D



Copyright FCI.



D

REV E - 2006-03-28

I 2 3 4

rev	ecn no	dr	date
A	S40256	BSL	1994-10-24
B	S05-0064	KBM	2005-03-01
C	S10-0205	AK	2010-02-01
-	-	-	-
-	-	-	-
-	-	-	-
-	-	-	-

CONFIDENTIAL

www.fciconnect.com			surface -  ISO 1302		tolerance std ISO 406 ISO 1101		projection 	MM 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED						
Dr	ML CHWA	1994-10-24	ANGULAR		LINEAR	X.X	±-	size A3	Scale 10:1
Eng	BS LOW	1994-10-27				X.XX	±0.25		
Chr	KH LEE	2010-02-01	0°	±°		X.XXX	±-	ECN	S10-0205
Appr	JOEY NG	2010-02-01	Product family				MINITEK	Spec ref	-
		title	MINITEK II 2.0 MM				dwg no		Rev.
			HOLDING HEADER				94268		C
		catalog no	-				CUSTOMER		sheet 1 of 2





Copyright FCI.

PRODUCT NO SEE NOTE 7	POS	DIM X	DIM Y
94268-X04	2 X 2	2	4
X06	2 X 3	4	6
X08	2 X 4	6	8
X10	2 X 5	8	10
X12	2 X 6	10	12
X14	2 X 7	12	14
X16	2 X 8	14	16
X18	2 X 9	16	18
X20	2 X 10	18	20

NOTES:

1. MATERIAL:
BODY : G.F NYLON UL94V-0 BLACK
PIN : COPPER ALLOY
2. TOLERANCE UNLESS OTHERWISE NOTED ± 0.25
3. HEADER BODY TO BE REMOVED AFTER SOLDERING
4. PIN TO HOUSING RETENTION FORCE 200 gm MAX.
PER PIN AFTER SUBJECTION TO SOLDER TEMPERATURE
AT 260°C FOR 5 sec.
5. DIM 1.0 APPLIES TO MOLDED SIDE(S) ONLY. IF
SIDE(S) ARE SAW, DIM 0.5 MIN APPLIES.
6. RECESS APPLIES TO MOLDED SIDE(S) ONLY.
7. PRODUCT DESCRIPTION CODE :
XXXXX-XXXLF
LEAD FREE (SEE NOTE 8 & 10)
TOTAL POSITIONS
TERMINAL PLATING
BASE NUMBER

PLATING	DESCRIPTION
0	0.2 μ m Au OVER Ni
1	0.76 μ m Au OVER Ni
3	0.38 μ m Au OVER Ni
5	0.38 μ m PdNi W Au FLASH OVER Ni
6	0.76 μ m PdNi W Au FLASH OVER Ni

8. P/N:94268-XXXLF IS SAME AS P/N:94268-XXX. THE SUFFIX 'LF' IS ADDED JUST FOR EASY LEAD FREE IDENTIFICATION
9. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE FOR 10 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.57MM MINIMUM THICK CIRCUIT BOARD.
10. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
11. A SYMBOL WILL BE NEXT TO ANY DIMENSION, VIEW OR NOTE WHICH HAS BEEN MODIFIED WITH THE CURRENT DRAWING REVISION

CONFIDENTIAL

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection 	MM
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	ML CHWA	1994-10-24	ANGULAR	LINEAR	x.x	±-
Eng	BS LOW	1994-10-27			x.xx	±0.25
Chr	KH LEE	2010-02-01	0°	±-°	x.xxx	±-
Appr	JOEY NG	2010-02-01	Product family			MINITEK
						Spec ref -
			MINITEK 11 2.0 MM			dwg no 94268
			HOLDING HEADER			Rev. C
			catalog no -			CUSTOMER
						sheet 2 of 2

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

FCI:

[94268-014](#) [94268-114](#) [94268-120](#)