

SOT23 PNP SILICON PLANAR MEDIUM POWER TRANSISTORS

FMMT549
FMMT549A


ISSUE 3 - OCTOBER 1995

FEATURES

- * Low equivalent on-resistance; $R_{CE(sat)} 250m\Omega$ at 1A
- * 1 Amp continuous current

COMPLEMENTARY TYPES – FMMT549 – FMMT449
FMMT549A – N/A

PARTMARKING DETAIL – FMMT549 – 549
FMMT549A – 59A



ABSOLUTE MAXIMUM RATINGS.

PARAMETER	SYMBOL	VALUE	UNIT
Collector-Base Voltage	V_{CBO}	-35	V
Collector-Emitter Voltage	V_{CEO}	-30	V
Emitter-Base Voltage	V_{EBO}	-5	V
Peak Pulse Current	I_{CM}	-2	A
Continuous Collector Current	I_C	-1	A
Base Current	I_B	-200	mA
Power Dissipation: at $T_{amb}=25^\circ C$	P_{tot}	500	mW
Operating and Storage Temperature Range	$T_j; T_{stg}$	-55 to +150	$^\circ C$

ELECTRICAL CHARACTERISTICS (at $T_{amb} = 25^\circ C$ unless otherwise stated).

PARAMETER	SYMBOL	MIN.	TYP.	MAX.	UNIT	CONDITIONS.
Breakdown Voltages	$V_{(BR)CBO}$	-35			V	$I_C = -100\mu A$
	$V_{(BR)CEO}$	-30			V	$I_C = -10mA^*$
	$V_{(BR)EBO}$	-5			V	$I_E = -100\mu A$
Cut-Off Currents	I_{CBO}			-0.1 -10	μA μA	$V_{CB} = -30V$ $V_{CB} = -30V, T_{amb} = 100^\circ C$
	I_{EBO}			-0.1	μA	$V_{EB} = -4V$
	$I_{CE(sat)}$		-0.25 -0.50	-0.50 -0.75	V V	$I_C = -1A, I_B = -100mA^*$ $I_C = -2A, I_B = -200mA^*$
Saturation Voltages				-0.30	V	$I_C = -100mA, I_B = -1mA^*$
	FMMT549A					
	$V_{BE(sat)}$		-0.9	-1.25	V	$I_C = -1A, I_B = -100mA^*$
Base Emitter Turn-on Voltage	$V_{BE(on)}$		-0.85	-1	V	$I_C = -1A, V_{CE} = -2V^*$
Static Forward Current Transfer Ratio	h_{FE}	70 80 40	200 130 80			$I_C = -50mA, V_{CE} = -2V^*$ $I_C = -1A, V_{CE} = -2V^*$ $I_C = -2A, V_{CE} = -2V^*$
	FMMT549		100	160	300	$I_C = -500mA, V_{CE} = -2V^*$
	FMMT549A		150	200	500	$I_C = -500mA, V_{CE} = -2V^*$
	Transition Frequency	f_T	100		MHz	$I_C = -100mA, V_{CE} = -5V$ $f = 100MHz$
	Output Capacitance	C_{obo}		25	pF	$V_{CB} = -10V, f = 1MHz$
Switching Times	t_{on}		50		ns	$I_C = -500mA, V_{CC} = -10V$
	t_{off}		300		ns	$I_{B1} = I_{B2} = -50mA$

*Measured under pulsed conditions. Pulse width=300 μs . Duty cycle $\leq 2\%$

FMMT549 **FMMT549A**

TYPICAL CHARACTERISTICS

