

DO NOT SCALE
FROM THIS PRINT

TERMINAL SPECIFICATIONS

TERMINAL SPEC	PIN #1	PIN #2	PIN #3
-05	T-1S6-21-X-2	N/A	N/A
-06	T-1S6-18-X-2	N/A	N/A
-07	T-1S6-07-X-2	T-1S6-15-X-2	T-1S6-10-X-2
-08	T-1S6-08-X-2	T-1S6-09-X-2	T-1S6-11-X-2
-09	T-1S6-09-X-2	T-1S6-11-X-2	T-1S6-20-X-2
-10	T-1S6-10-X-2	T-1S6-12-X-2	T-1S6-13-X-2
-11	T-1S6-11-X-2	T-1S6-20-X-2	T-1S6-19-X-2
-12	T-1S6-12-X-2	T-1S6-13-X-2	T-1S6-14-X-2
-13	T-1S6-13-X-2	T-1S6-14-X-2	N/A
-21	T-1S6-14-X-2	N/A	N/A
-22	T-1S6-15-X-2	T-1S6-10-X-2	T-1S6-12-X-2
-23	T-1S6-16-X-2	N/A	N/A
-24	T-1S6-17-X-2	N/A	N/A
-27	T-1S6-19-X-2	N/A	N/A
-28	T-1S6-20-X-2	T-1S6-19-X-2	N/A

FOR -RX OPTION: TAIL = L-C-B-.15 REF
FOR -NX OPTION: TAIL = L-C-B-.13 REF
(CALCULATIONS APPLY TO FIRST ROW PIN LENGTHS ONLY)

LEAD STYLE	C MAXIMUM STRAIGHT	C MAXIMUM W/RA	C MAXIMUM W/RE
-05	.235 [5.97]	N/A	N/A
-06	.200 [5.08]	N/A	N/A
-07	.330 [8.38]	.130 [3.30]	N/A
-08	.430 [10.92]	.230 [5.84]	.130 [3.30]
-09	.630 [16.00]	.430 [10.92]	.330 [8.38]
-10	.730 [18.54]	.530 [13.46]	.430 [10.92]
-11	.830 [21.08]	.630 [16.00]	.530 [13.46]
-12	.930 [23.62]	.730 [18.54]	.630 [16.00]
-13	1.130 [28.70]	.930 [23.62]	.830 [21.08]
-21	1.330 [33.78]	1.130 [28.70]	1.030 [26.16]
-22	.530 [13.46]	.330 [8.38]	.230 [5.84]
-23	.345 [8.76]	.145 [3.68]	N/A
-24	.380 [9.65]	.180 [4.57]	
-27	1.230 [31.24]	1.030 [26.16]	.930 [23.62]
-28	1.030 [26.16]	.830 [21.08]	.730 [18.54]

1. TERMINAL PUSHOUT FORCE: 3 LBS. MIN.
2. HEIGHT VARIATION BETWEEN ANY TWO ROWS SHALL BE .005[0.13] MAX (R.A. TAIL N/A)
3. ASSEMBLE GOLD PLATE END AS SHOWN.
4. NOTE DELETED.
5. (Ⓢ) REPRESENTS CRITICAL DIMENSION.
6. TOW & SWAY SPEC OF 2" APPLIES TO ALL POSITIONS, POST & TAIL, IN ALL DIRECTIONS.
7. -STL PLATING AVAILABLE IN LEAD STYLES -07, -08, -10, -16, -17, & -21.
STRAIGHT THROUGH HOLE ONLY.
8. ORIENTATE PINS TO REDUCE THE NUMBER OF BANDOLIER MARKS IN THE POST AREA.
(SEE TABLE 6)
9. NOTE DELETED.
10. MAXIMUM CUT FLASH: .020[0.51]
11. TABLE 5 IS A REFERENCE FOR INDIVIDUAL PIN LENGTHS AS LISTED ON THE T-156
COMPONENT PART AND NOT THE TERMINAL SPEC IN TABLE 1 OR IN THE PART CALLOUT.
12. MUST USE T-30193-13 (2 1/2" BLADES) TO CUT -T AND -Q PARTS.

[illegible]

BODY SPECIFICATION		TABLE 3	
ROW/OPTION	USE BODY	-XX	"B"
-S/-S-NA/-S-NE	TSW-50-S	-RA	.060 [1.52]
-S-RA/-S-RE	TSW-50-S-RA	-RE	.160 [4.06]
-D/-D-NA/-D-NE	RTSW-50-D *		
-D-RA	TSW-50-D-RA		
-T/-T-NA/-T-NE	TSW-50-T		
-T-RA	TSW-50-T-RA		
-O	TSW-50-T		

* RTSW FOR HAND FILL. TSW FOR MACHINE FILL.
TSW AND RTSW ARE INTERCHANGEABLE.

LENGTH	L	
-07	.430	[10.92]
-08	.530	[13.46]
-09	.730	[18.54]
-10	.830	[21.08]
-11	.930	[23.62]
-12	1.030	[26.16]
-13	1.230	[31.24]
-14	1.430	[36.32]
-15	.630	[16.00]
-16	.445	[11.30]
-17	.480	[12.19]
-18	.300	[7.62]
-19	1.330	[33.78]
-20	1.130	[28.70]
-21	.335	[8.51]

SEE NOTE 11

* REF FOR PIN LENGTH, SHT 1

ONE PLACE DECIMALS $\pm .1$ [3]	THREE PLACE DECIMALS $\pm .005$ [.13]
TWO PLACE DECIMALS $\pm .01$ [.3]	FOUR PLACE DECIMALS $\pm .0020$ [.051]

cs	ASSEMBLY, .025 [.64] SQ. PO TERMINAL STRIP
----	--

SHEET 1 OF 3

TERMINAL SPACE SPEC. _____
(SEE ASSEMBLY INSTR.)

-1= .100 [2.54] (FILL EVERY POS.)
-2= .200 [5.08] (FILL E/O POS.
STARTING W/ 1st & ENDING
W/ LAST POS. IN BODY)

BODY LENGTH SPEC. —
EXPRESSED IN # OF POS.

-1: 01 THRU -50 (-S,-D,-T)
"A"= NO. OF POS. x .100 [2.54]
-2: 02 THRU -25 (-S,-D,-T)
"A"= (NO OF POS. x .200)-.100

TERMINAL SPECIFICATION
SEE TABLE 1

— OPTION #2

-POLARIZATION SPEC.
XXX INDICATES POS. TO BE OMITTED
(SEE FIG. 2)

OPTION #1

-BLANK= STRAIGHT
 -RA= RIGHT ANGLE (SEE TABLE 3 & FIG. 3) (-05 N/A)
 -RE= REVERSE POINT ANGLE (SEE TABLE 3 & FIG. 3) (-05 N/A)
 -S= SINGLE ROW ONLY (-05, -07, -23, -24 N/A)
 -NA= RA OPTION WITH STRAIGHT OPTION BODY
 -NE= RE OPTION WITH STRAIGHT OPTION BODY
 -L= LOOKING LEAD (SEE FIG. 1)
 -LL= WITH -RE OPTION OR SINGLE ROW
 1 OR 2 POSITION)
 (TAILS FROM .090 [2.29] TO .400 [10.16] ONLY)
 -N/A IN SINGLE ROW, 1 & 2 POSITIONS)
 -LA= RA OPTION WITH -L OPTION (2 & 3)
 (WITH SINGLE ROW OR 2 POSITION)
 (TAILS FROM .090 [2.29] TO .310 [7.87] ONLY)
 POST = .530 [13.46] MAX.

— POST HEIGHT
XXXX = "C"

PLATING SPECIFICATIONS

- G: 10µ GOLD CONTACT, 3µ GOLD TAIL
- T: MATTE TIN CONTACT AND TAIL
- S: 30µ SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- L: 10µ SELECTIVE GOLD IN CONTACT AREA, MATTE TIN ON TAIL
- H: HEAVY GOLD ON CONTACT, 3µ GOLD ON TAIL
- H: 30µ HEAVY GOLD CONTACT, 3µ GOLD ON TAIL
- F: 3µ FLASH SELECTIVE GOLD, MATTE TIN TAIL
- STL: 30µ GOLD SELECTIVE ON CONTACT TIN/LEAD (90/10/-5%) TAIL
- TM: MATTE TIN CONTACT AND TAIL
- SM: 30µ SELECTIVE GOLD CONTACT MATTE TIN TAIL
- LM: 10µ LIGHT SELECTIVE GOLD MATTE TIN TAIL
- EM: 3µ GOLD FLASH SELECTIVE ON CONTACT MATTE TIN TAIL

— ROW SPECIFICATION (SEE TABLE #2)

- S: SINGLE
- D: DOUBLE
- T: TRIPLE
- Q: TRIPLE ROW (FILL OUTER ROWS ONLY)

2"
(TYP)

STRAIGHT
(SCALE=.75x)

SINGLE -RA/-RE
DOUBLE -RA
(SCALE=.75x)

MATERIAL:
BODIES:
GLASS FILLED POLYESTER
COLOR: BLACK
TERMINALS:
PHOSPHOR BRONZE

EXISPROD\ASSEMBLY\100
MTSW-ASM

samtec

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY: PURVIS 2-17-87

MTSW-XXX-XX-X-X-XXXX-XX-XXX
SHEET 1 OF 3

PROPRIETARY NOTE
THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.