

Data Sheet

Total Output Power: 1050 Watts
+3.3 or 5.0 Vdc Stand-by Output
Wide Range Input Voltage: 90 - 264 Vac

SPECIAL FEATURES

- Active power factor correction
- EN61000-3-2 harmonic compliance
- Inrush control
- 1U X 2U form factor
- 19.0 W/in³
- +12 Vdc output
- Available in +3.3V and +5.0V standby output versions
- No minimum load required
- Hot plug operation
- N + 1 redundant
- Internal OR'ing fets
- Active current sharing (10 - 100% load)
- • Built-in cooling fan (40 mm x 28 mm)
- I²C communication interface bus
- PMBus compliant
- EEPROM for FRU data
- Amber/green bi-color LED status
- Internal fan speed control
- Fan fail tach output signal
- Full digital control
- Two years warranty

SAFETY

- UL/cUL 60950 (UL Recognized)
- NEMKO+ CB report EN60950
- EN60950
- CE mark
- China CCC

DS1050

Distributed Power Bulk Front-End



Electrical Specifications

Input

Input range:	180 - 264 (1050 W) 90 - 264 (1050 W)
Frequency:	47 - 63 Hz, single phase AC
Inrush current:	40 Apk maximum inrush current
Efficiency:	> 92% typical at high line 50% load (Climate Saver Gold)
Conducted EMI:	FCC Subpart J EN55022 Class B
Radiated EMI:	FCC Subpart J EN55022 Class B
Power factor:	0.99 typical
Leakage current:	1.40 mA @ 240 VAC
Hold up time:	12 ms minimum

Output

Main DC voltage:	+12 V @ 87 A
Stand-By:	+3.3 Vsb @ 4 A (5 V @ 2.5 A available)*
Adjustment range:	± 5% on +12V only using I ² C
Regulation:	+12 Vdc; +5%/-5% +3.3 Vsb; +5%/-5%
Over current:	+12 Vdc; latches off if overcurrent lasts over 1 second, otherwise it is auto recovery (See Table 1 next page) +3.3 Vsb, 6 A max (hiccup mode)
Over voltage:	+12 Vdc; 13.2 - 14.4 Vdc +3.3 Vsb; 3.76 - 4.30 Vdc
Under voltage:	+12 Vdc; 9 - 10.8 V (latch off)
Turn-on delay:	2 second max, 5 - 50 mS, monotonic rise
Main output rise time	5 - 50 mS, monotonic rise

*20 W standby available with derated efficiency

Logic Control

PS_SEATED (A4):	TTL logic LOW if power supply is seated into system connector. This is a short pin. A logic HIGH if the PSU is removed
PWR GOOD (C3):	Active TTL high when output is within regulation limits.
AC OK (B1):	A low logic level if the input voltage is within allowable limits. A TTL logic HIGH level, and a 5mS early warning signal before 12.0 V DC output loss of regulation.
PS_INHIBIT/PS_KILL (B4):	This signal is connected to a short pin on the PSU When left open power supply operation will be inhibited. When the power supply is inserted into the system, this pin will be pull low by the system and turn the power supply on only after all other power supply pins have seated.
PS ON (A1):	The output will be enabled when this signal is pulled low, below 0.8 V outputs disabled when pin is driven high or left open.

Environmental Specifications

Operating temperature:	-10° to 50 °C ; 50% power derating at 70 °C
Storage temperature:	-40°C to +85°C
Altitude, operating:	10,000 ft
Electromagnetic susceptibility/Input transients:	-EN61000-3-2, -3-3 -EN61000-4-2, 4.3, 4-4, -4-5, 4-11 -EN55024:1998
RoHS & lead-free compliant:	No tantalum caps.
Humidity:	20 to 90% RH, non-condensing
Shock and vibration specifications:	Standard operating/non-operating random shock/vibration
MTBF (Demonstrated)	500K Hrs at full load, 40 °C

Ordering Information

Model Number	Nominal Output Voltage Set Point	Set Point Tolerance	Total Regulation	Minimum Current	Maximum Current	Output Ripple P/P	Over Current	Stand-by**	Air Flow
DS1050-3	12.0 Vdc	±0.2%	±5%	0 A	87 A	120 mV	102.7 A - 128.4 A	3.3 V @ 4 A	STD
DS1050-3-001	12.0 Vdc	±0.2%	±5%	0 A	87 A	120 mV	102.7 A - 128.4 A	3.3 V @ 4 A	REV
DS1050-3-002	12.0 Vdc	±0.2%	±5%	0 A	87 A	120 mV	102.7 A - 128.4 A	5.0 V @ 2.5 A	STD
DS1050-3-003	12.0 Vdc	±0.2%	±5%	0 A	87 A	120 mV	102.7 A - 128.4 A	5.0 V @ 2.5 A	REV

*Over current latches off if overcurrent lasts over 1 seconds, otherwise it is auto recovery.

** 3.3V standby can operate at 6A, but overall unit efficiency will fall slightly below Gold Standard.

STANDARD AIRFLOW DIRECTION

279.4 ± 1.0

200.9

7.02 ± 0.80

EMI GASKET
P/N 40366107530

HOT SURFACE LABEL

31.5

HANDLE
P/N 1836611161X

(3x) EMI GASKET
P/N 40366107530

(3x) 200.9

LABEL MODEL

PROGRAMMING WINDOW

8.0

3.2

275.5 ± 0.7

LATCH BUTTON
P/N 1836611209X
COLOR: HF GREEN

C14 GINLET

7.6

19.9

EMI GASKET
P/N 40366107530

200.9

10.2 ± 0.5

27.1

12.8 ± 0.1

7.2 ± 0.5

39.9 ± 0.5

15.3 ± 0.5

(3x) EMI GASKET
P/N 40366107530

(3x) 200.9

71.8 ± 0.5

FULL R

(2X) 1.5 X 45° CHAMFER
RECOMMENDED KEY
HEIGHTS 2.5MM MAX.

6.0 ± 0.5

6.0 ± 0.5

DC Output Connector Pinout Assignment

Male connector as viewed from the rear of the supply:

D1	D2	D3	D4	D5	D6	PB1	PB2	PB3	PB4	PB5	PB6
C1	C2	C3	C4	C5	C6						
B1	B2	B3	B4	B5	B6						
A1	A2	A3	A4	A5	A6						

P1 - Power Supply Side

1	FCI Power Blade 51721 series 51721-10002406AA
2	Molex Power Connector SD-87667 series 87667-7002

Mating Connector (System Side)

1	FCI Power Blade 51741-10002406CC Strait Pins
2	FCI Power Blade 51761-10002406AALF Right Angle

Pin Assignments

Pin	Signal Name
PB 1	Main output return
PB 2	Main output return
PB 3	Main output return
PB 4	+ Main output
PB 5	+ Main output
PB 6	+ Main output
A1	PS_ON
A2	Main output remote sense return
A3	Spare
A4	PS_SEATED (Power Supply Seated)
A5	STAND-BY
A6	STAND-BY RETURN
B1	AC_OK (AC Input Present)
B2	Main output remote sense
B3	Main output current share
B4	PS_INHIBIT/PS_Kill
B5	STAND-BY
B6	STAND-BY RETURN

Pin Assignments

Pin	Signal Name
C1	SDA (I ² C Data Signal)
C2	SCL (I ² C Clock Signal)*
C3	POWER GOOD
C4	Spare
C5	STAND-BY
C6	STAND-BY RETURN
D1	A0 (I ² C Address BIT 0 Signal)
D2	A1 (I ² C Address BIT 1 Signal)
D3	S_INT (Alarm)
D4	STAND-BY RMT SENSE
D5	STAND-BY
D6	STAND-BY RETURN

*Supports I²C standard mode (100 kHz) only

WORLDWIDE OFFICES

Americas

2900 S.Diablo Way
Tempe, AZ 85282
USA
+1 888 412 7832

Europe (UK)

Waterfront Business Park
Merry Hill, Dudley
West Midlands, DY5 1LX
United Kingdom
+44 (0) 1384 842 211

Asia (HK)

14/F, Lu Plaza
2 Wing Yip Street
Kwun Tong, Kowloon
Hong Kong
+852 2176 3333

ARTESYN
EMBEDDED TECHNOLOGIES

www.artesyn.com

While every precaution has been taken to ensure accuracy and completeness in this literature, Artesyn Embedded Technologies assumes no responsibility, and disclaims all liability for damages resulting from use of this information or for any errors or omissions. Artesyn Embedded Technologies, Artesyn and the Artesyn Embedded Technologies logo are trademarks and service marks of Artesyn Embedded Technologies, Inc. All other names and logos referred to are trade names, trademarks, or registered trademarks of their respective owners.
© 2014 Artesyn Embedded Technologies, Inc.

For more information: www.artesyn.com/power
For support: productsupport.ep@artesyn.com

DS1050-DS Rev. 06.16.14