



NOTES:

1. SUGGESTED MOUNTING HOLE = $\phi.120$
2. MAXIMUM INSTALLATION TEMP.: 500°F



LEAD FINISH	SOLDER
EYELET FINISH	SOLDER
CAPACITANCE	1500pF MIN.
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C 350 VDC MAX. 125°C 200 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	N/A
10	5
100	40
1 GHz/10GHz	70



MARKING:

PART: NONE
BAG: SCI 1251-001
DATE CODE
LOT #
QTY./BAG (200 MAX.)

		08	07	06	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	 SPECTRUM CONTROL INC.	FAIRVIEW PENNSYLVANIA	
						Fractions $\pm 1/64$		Dwn. KAUFFMAN	Description
						Dec. .xx $\pm$			
						Dec. .xxx $\pm .010$		Date 11-8-04	EYELET FILTER
						Angles $\pm 0^{\circ} 30'$		Engr STRUCHEN	
		CN 15735-CPD	CN 201258	CN 184991	CHANGE NOTICE	CODE IDENT. NO. DLSP2	Scale NONE	1251-001	