

AC Line Rated Ceramic Disc Capacitors

Class X1, 760 V_{AC}, Class Y1, 500 V_{AC}



FEATURES

- Complying with IEC 60384-14, 3rd edition
- High reliability
- Vertical (inline) kinked or straight leads
- Singlelayer AC Disc capacitors
- Material categorization:
For definitions of compliance please see
www.vishay.com/doc?99912



RoHS
COMPLIANT
HALOGEN
FREE
Available

APPLICATIONS

- X1, Y1 according to IEC 60384-14.3
- Across-the-line
- Line by-pass
- Antenna coupling

DESIGN

The capacitors consist of a ceramic disc both sides of which are silver-plated. Connection leads are made of tinned copper having a diameter of 0.6 mm.

The capacitors may be supplied with vertical (inline) kinked leads having a lead spacing of 10.0 mm and 12.5 mm. Encapsulation is made of flammable resistant epoxy resin in accordance with "UL 94 V-0".

QUICK REFERENCE DATA				
DESCRIPTION	VALUE			
Ceramic Class	1		2	
Ceramic Dielectric	U2J	U2J	Y5S, Y5U	Y5S, Y5U
Voltage (V _{AC})	500	760	500	760
Min. Capacitance (pF)	10		33	
Max. Capacitance (pF)	22		4700	
Mounting	Radial			

OPERATING TEMPERATURE RANGE

- 40 °C to + 125 °C

TEMPERATURE CHARACTERISTICS

See Ordering Information table

CLIMATIC CATEGORY

40/125/21 according to EN 60068-1

COATING

According to UL 94 V-0

Epoxy resin, isolating, flame retardant

APPROVALS

IEC 60384-14.3

UL 60384-14

DIN EN 60384-14

CSA E60384-1:03, CSA E60384-14:09

PACKAGING

Bulk, tape and reel, taped ammpack

CAPACITANCE RANGE

10 pF to 4700 pF

RATED VOLTAGE U_R

IEC 60384-14.3:

(X1): 760 V_{AC}, 50 Hz

(Y1): 500 V_{AC}, 50 Hz

TEST VOLTAGE

Component test (100 %):

4000 V_{AC}, 50 Hz, 2 s

Random sampling test (destructive test):

4000 V_{AC}, 50 Hz, 60 s

Voltage proof of coating (destructive test):

4000 V_{AC}, 50 Hz, 60 s

INSULATION RESISTANCE

10 000 MΩ minimum


TOLERANCE OF CAPACITANCE

± 20 % (code M); ± 10 % (code K)

DISSIPATION FACTOR

2.5 % maximum

DIMENSIONS



Capacitors with 10.0 mm and 12.5 mm lead spacing

ORDERING INFORMATION

C (pF)	TOL. (%)	TEMP. COEFFICIENT	BODY DIAMETER D _{MAX.} (mm)	BODY THICKNESS T _{MAX.} (mm)	LEAD SPACING F (mm)	CLEAR TEXT CODE	
						15 TH DIGIT: T = REEL; U = AMMO; 3 = BULK ⁽¹⁾	
						RoHS COMPLIANT	RoHS AND HALOGEN-FREE
10	± 10	U2J (N750)	8.0	5.0	10.0	VY1100K31U2JQ6*V0	VY1100K31U2JG6*V0
15						VY1150K31U2JQ6*V0	VY1150K31U2JG6*V0
22						VY1220K31U2JQ6*V0	VY1220K31U2JG6*V0
33		Y5S (2C3)				VY1330K31Y5SQ6*V0	VY1330K31Y5SG6*V0
47						VY1470K31Y5SQ6*V0	VY1470K31Y5SG6*V0
68						VY1680K31Y5SQ6*V0	VY1680K31Y5SG6*V0
100						VY1101K31Y5SQ6*V0	VY1101K31Y5SG6*V0
150						VY1151K31Y5SQ6*V0	VY1151K31Y5SG6*V0
220						VY1221K31Y5SQ6*V0	VY1221K31Y5SG6*V0
330	± 20	Y5U (2E3)	VY1331K31Y5SQ6*V0	VY1331K31Y5SG6*V0			
470			VY1471M31Y5UQ6*V0	VY1471M31Y5UG6*V0			
680			VY1681M31Y5UQ6*V0	VY1681M31Y5UG6*V0			
1000			VY1102M35Y5UQ6*V0	VY1102M35Y5UG6*V0			
1500			VY1152M41Y5UQ6*V0	VY1152M41Y5UG6*V0			
2200			VY1222M47Y5UQ6*V0	VY1222M47Y5UG6*V0			
3300			VY1332M59Y5UQ6*V0	VY1332M59Y5UG6*V0			
3900			VY1392M61Y5UQ6*V0	VY1392M61Y5UG6*V0			
4700			VY1472M63Y5UQ6*V0	VY1472M63Y5UG6*V0			
10	± 10	U2J (N750)	8.0	5.0	12.5	VY1100K31U2JQ6*VX	VY1100K31U2JG6*VX
15						VY1150K31U2JQ6*VX	VY1150K31U2JG6*VX
22						VY1220K31U2JQ6*VX	VY1220K31U2JG6*VX
33		Y5S (2C3)				VY1330K31Y5SQ6*VX	VY1330K31Y5SG6*VX
47						VY1470K31Y5SQ6*VX	VY1470K31Y5SG6*VX
68						VY1680K31Y5SQ6*VX	VY1680K31Y5SG6*VX
100						VY1101K31Y5SQ6*VX	VY1101K31Y5SG6*VX
150						VY1151K31Y5SQ6*VX	VY1151K31Y5SG6*VX
220						VY1221K31Y5SQ6*VX	VY1221K31Y5SG6*VX
330	± 20	Y5U (2E3)	VY1331K31Y5SQ6*VX	VY1331K31Y5SG6*VX			
470			VY1471M31Y5UQ6*VX	VY1471M31Y5UG6*VX			
680			VY1681M31Y5UQ6*VX	VY1681M31Y5UG6*VX			
1000			VY1102M35Y5UQ6*VX	VY1102M35Y5UG6*VX			
1500			VY1152M41Y5UQ6*VX	VY1152M41Y5UG6*VX			
2200			VY1222M47Y5UQ6*VX	VY1222M47Y5UG6*VX			
3300			VY1332M59Y5UQ6*VX	VY1332M59Y5UG6*VX			
3900			VY1392M61Y5UQ6*VX	VY1392M61Y5UG6*VX			
4700			VY1472M63Y5UQ6*VX	VY1472M63Y5UG6*VX			


Notes

- Straight leads are available on request
 - Coating extension DR valid for straight leads only
 - On request available: ± 10 % tolerance
- ⁽¹⁾ 15th digit of the clear text code number to be completed with the packaging code

PACKAGING					
CAPACITANCE VALUE	SIZE CODE	BODY DIAMETER $D_{MAX.}$ (mm)	PACKAGING QUANTITIES		
			BULK	REEL	AMMO
10 pF to 2200 pF	31 to 47	12.0	1000	500	750
3300 pF to 4700 pF	51 to 63	16.0	500	500	750

Note

- The capacitors are supplied in bulk packaging (cardboard boxes), in tape on reel in ammopack


STRAIGHT LEADS


Lead spacing 10.0 mm and 12.5 mm, sprocket hole pitch 25.04 mm for lead spacing


DIMENSIONS OF TAPE		
SYMBOL	PARAMETER	DIMENSIONS (mm)
		FIG. 2
D ⁽¹⁾	Body diameter	16.0 max.
d	Lead diameter	0.6 ± 0.05
P	Pitch of component	25.4 ± 1
P ₀ ⁽²⁾	Pitch of sprocket hole	12.7 ± 0.3
P ₁ ⁽³⁾	Distance, hole center to lead	7.7 or 6.4 ± 1.0
P ₂ ⁽³⁾	Distance, hole to center of component	12.7 ± 1.5
F	Lead spacing	10.0 or 12.5 + 0.6/- 0.4
Δh	Average deviation across tape	± 1.0 max.
ΔP	Average deviation in direction of reeling	± 1.0 max.
W	Carrier tape width	18.0 + 1/- 0.5
W ₀	Hold-down tape width	5.0 min.
W ₁	Position of sprocket hole	9.0 + 0.75/- 0.5
W ₂	Distance of hold-down tape	3.0 max.
H ₁	Maximum component height	40.0
H ₀	Height to seating plane (for kinked leads)	16.0 ± 0.5
H ₀	Height to seating plane (for straight leads)	20.0 ± 0.5
L	Length of cut leads	11.0 max.
l	Length of lead protrusion	1.0 max.
D ₀	Diameter of sprocket hole	4.0 ± 0.2
t	Total tape thickness	0.9 max.

Notes

- (1) See Ordering Information table
(2) Cumulative pitch error: ± 1 mm/20 pitches
(3) Obliquity maximum 3°

REEL AND TAPE DATA in millimeters


Reel with capacitors on tape



Ammopack with capacitors on tape

APPROVALS

IEC 60384-14.3 - Safety tests

This approval together with CB test certificate substitutes all national approvals.

CB Certificate

Y1-capacitor: CB test certificate:	US-19600-UL	10 pF to 4.7 nF	500 V _{AC}
X1-capacitor: CB test certificate:	US-19600-UL	10 pF to 4.7 nF	760 V _{AC}



VDE

Y1-capacitor: VDE marks approval:	40012673	10 pF to 4.7 nF	500 V _{AC}
X1-capacitor: VDE marks approval:	40012673	10 pF to 4.7 nF	760 V _{AC}



DIN EN 60384-14 VDE 0565-1-1:2006-04 - Safety tests

Underwriters Laboratories Inc./Canadian Standards Association

Y1-capacitor: CSA test certificate:	E183844	10 pF to 4.7 nF	500 V _{AC}
X1-capacitor: CSA test certificate:	E183844	10 pF to 4.7 nF	760 V _{AC}



UL 60384-14, CSA E60384-1:03, CSA E60384-14:09


Fixed capacitors for electromagnetic interference suppression and connection to the supply mains.

CQC


Y1-capacitor: CQC test certificate:	C0042538	10 pF to 4.7 nF	500 V _{AC}
X1-capacitor: CQC test certificate:	C0042538	10 pF to 4.7 nF	760 V _{AC}



MARKING

Sample
(2 sides)


4 digit date code (year/week)




PN: VY1471M31Y5UQ6XT0 Lot1: 14Z551S12 DC1: 0601
QTY: 225 Lot2: DC2:
PO: Batch: 200601CN
SO: Region: 9520 SL: 0010
Ser.No: 0601H69340






1/1

PERFORMANCE

TEST	TEST CONDITION	TEST LIMITS
Visual and mechanical inspection	Optical inspection, dimensions measured with caliper	No visible damage, marking legible
Capacitance (C)	25 °C ± 3 °C, relative humidity (RH) ≤ 75 %, 1.0 V _{RMS} ± 0.2 V _{RMS} at 1 kHz for Y5U and Y5S, and 1 MHz for U2J	Capacitance within specified tolerance
Dissipation factor (DF)		DF ≤ 0.3 % for U2J and DF ≤ 2.5 % for Y5S and Y5U
Insulation resistance (IR)	Measured within 60 s ± 5 s after charging at 500 V _{DC}	10 000 MΩ min.
Dielectric strength	4000 V _{AC} at 50 Hz/60 Hz for 1 min, 50 mA max.	No failure
Temperature characteristic	RH ≤ 75 %, 1.0 V _{RMS} ± 0.2 V _{RMS} at 1 kHz for Y5U and Y5S, and 1 MHz for U2J	U2J: -750 ppm ± 120 ppm Y5S: ± 22 % Y5U: +22 %/-56 %
Impulse voltage	3 pulses of 8 kV	No failure

PERFORMANCE		
TEST	TEST CONDITION	TEST LIMITS
Life test	1000 h at 125 °C $\pm$ 2 °C, 850 V _{AC} /50 Hz; once every hour 1000 V _{AC} for 0.1 s	External appearance: No visible damage $\Delta C \leq \pm 15 \%$ DF $\leq 0.5 \%$ for U2J and $\leq 5 \%$ for Y5S and Y5U IR $\geq 3000 \text{ M}\Omega$ Dielectric strength: No failure
Humidity test	500 h at 500 V _{AC} , 50 Hz and 500 h unloaded 40 °C, RH = 90 % to 95%	External appearance: No visible damage $\Delta C \leq \pm 10 \%$ for U2J and $\leq \pm 15 \%$ for Y5S and Y5U DF $\leq 0.5 \%$ for U2J and $\leq 5 \%$ for Y5S and Y5U IR $\geq 3000 \text{ M}\Omega$ Dielectric strength: No failure
Robustness of termination	Pull test: 0.5 kg tensile weight in radial direction for 10 s $\pm$ 1 s Bending strength: Capacitor body rotated by 90° in both directions	No damage to capacitor body and lead wire
Soldering effect	Immersion of lead wires into 260 °C $\pm$ 5 °C solder for 10 s $\pm$ 2 s; min. distance from body: 1.5 mm Hand soldering at 400 °C $\pm$ 10 °C for 3 s to 4 s; min. distance from body: 1.5 mm	External appearance: No visible damage $\Delta C \leq \pm 5 \%$ for U2J and $\leq \pm 10 \%$ for Y5S and Y5U Dielectric strength: No failure
Vibration test	 Solder the capacitor onto test jig (glass epoxy body) and use resin (adhesive) to stick the body to the test jig. The capacitor must be soldered firmly to the supporting lead wire. Vibration change from 10 Hz to 2000 Hz and back to 10 Hz; Total amplitude: 1.5 mm; Acceleration: 100 m/s²; Sweep rate: 1 oct/min, each axis 2 h (6 h in total)	External appearance: No visible damage Capacitance within specified tolerance DF $\leq 0.3 \%$ for U2J and $\leq 2.5 \%$ for Y5S and Y5U IR $\geq 10\,000 \text{ G}\Omega$

LEAKAGE CURRENT VS. VOLTAGE (Typical)


IMPEDANCE VS. FREQUENCY (Typical)

Note

- The capacitors meet the essential requirements of "EIA 198". Unless stated otherwise all electrical values apply at an ambient temperature of 25 °C ± 3 °C, at normal atmospheric conditions.

RELATED DOCUMENTS

General Information	www.vishay.com/doc?28536
CB Test Certificate	www.vishay.com/doc?22249
VDE Marks Approval	www.vishay.com/doc?22251
UL Test Certificate	www.vishay.com/doc?22250
CQC Test Certificate	www.vishay.com/doc?22248



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and/or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

Material Category Policy

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as RoHS-Compliant fulfill the definitions and restrictions defined under Directive 2011/65/EU of The European Parliament and of the Council of June 8, 2011 on the restriction of the use of certain hazardous substances in electrical and electronic equipment (EEE) - recast, unless otherwise specified as non-compliant.

Please note that some Vishay documentation may still make reference to RoHS Directive 2002/95/EC. We confirm that all the products identified as being compliant to Directive 2002/95/EC conform to Directive 2011/65/EU.

Vishay Intertechnology, Inc. hereby certifies that all its products that are identified as Halogen-Free follow Halogen-Free requirements as per JEDEC JS709A standards. Please note that some Vishay documentation may still make reference to the IEC 61249-2-21 definition. We confirm that all the products identified as being compliant to IEC 61249-2-21 conform to JEDEC JS709A standards.