

NCP4687

500 mA, High PSRR, LDO Linear Voltage Regulator

The NCP4687 is a CMOS 500 mA LDO linear voltage regulator with high output voltage accuracy which features a high ripple rejection, low supply current with low dropout and chip enable with built-in low $R_{DS(on)}$ NMOS transistor for fast output capacitor discharging as option. The device is composed of the voltage reference unit, error amplifier, resistor divider for output voltage sensing or precise output voltage setting. The current limit and thermal shutdown makes the device very suitable for industrial applications and portable communication equipments.

Features

- Operating Input Voltage Range: 2.5 V to 5.25 V
- Output Voltage Range: 0.7 to 3.6 V (available in 0.1 V steps)
- $\pm 0.8\%$ Output Voltage Accuracy @ $V_{out} > 1.8$ V
- Output noise : 40 μV_{rms}
- Line Regulation: 0.02%/V
- Current Limit Circuit
- High PSRR: 75 dB at 1 kHz, 70 dB at 10 kHz
- Thermal Shutdown
- Available in SOT-23-5, SOT-89-5 and uDFN 1.2 x 1.2 mm Packages
- Pb-Free Packages are Available

Typical Applications

- Home Appliances, Industrial Equipment
- DVB-T and DVB-S Receivers
- Car Audio Equipment, Navigation Systems
- Notebook Adaptors, LCD TVs, Cordless Phones and Private LAN Systems




Figure 1. Typical Application Schematic




ON Semiconductor™

<http://onsemi.com>

MARKING DIAGRAMS




**SOT89-5
CASE 528AB**



**XDFN6
CASE 711AH**



**SOT-23-5
CASE 1212**



XX, XXX = Specific Device Code
MM = Date Code

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 15 of this data sheet.

NCP4687




Figure 2. Simplified Schematic Block Diagram

PIN FUNCTION DESCRIPTION

Pin No. SOT-23-5	Pin No. SOT-89-5	Pin No. DFN1212	Pin Name	Description
1	4	6	VIN	Input pin
2	2	3	GND	Ground pin
3	3	4	CE	Chip enable pin ("H" active)
4	1	2	SENSE	Output Voltage Sensing
5	5	1	VOUT	Output pin
		5	NC	Non Connected
		*EP	EP	Exposed Pad (leave floating or connect to GND)

ABSOLUTE MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Input Voltage	V_{IN}	0 – 6	V
Output Voltage	V_{OUT}	–0.3 to V_{IN} – 0.3	V
Chip Enable Input	V_{CE}	–0.3 – 6	V
Power Dissipation SOT–23–5	P_D	420	mW
Power Dissipation uDFN 1.2 x 1.2 mm		600	
Power Dissipation SOT–89–5		900	
Junction Temperature	T_J	–40 to 150	°C
Storage Temperature	T_{STG}	–55 to 125	°C
ESD Capability, Human Body Model (Note 1)	ESD_{HBM}	2000	V
ESD Capability, Machine Model (Note 1)	ESD_{MM}	200	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

1. This device series incorporates ESD protection and is tested by the following methods:

ESD Human Body Model tested per AEC–Q100–002 (EIA/JESD22–A114)

ESD Machine Model tested per AEC–Q100–003 (EIA/JESD22–A115)

Latchup Current Maximum Rating tested per JEDEC standard: JESD78

THERMAL CHARACTERISTICS

Rating	Symbol	Value	Unit
Thermal Characteristics, SOT–23–5 Thermal Resistance, Junction–to–Air	$R_{\theta JA}$	238	°C/W
Thermal Characteristics, uDFN 1.2x1.2 Thermal Resistance, Junction–to–Air	$R_{\theta JA}$	167	°C/W
Thermal Characteristics, SOT–89–5 Thermal Resistance, Junction–to–Air	$R_{\theta JA}$	111	°C/W

NCP4687

ELECTRICAL CHARACTERISTICS $-40^{\circ}\text{C} \leq T_A \leq 85^{\circ}\text{C}$; $C_{IN} = C_{OUT} = 1.0 \mu\text{F}$, unless otherwise noted. Typical values are at $T_A = +25^{\circ}\text{C}$.

Parameter	Test Conditions		Symbol	Min	Typ	Max	Unit
Operating Input Voltage	V _{OUT} ≤ 1.5 V		V _{IN}	2.5		5.25	V
	V _{OUT} > 1.5 V			V _{OUT} + 1		5.25	
Output Voltage	Ta = 25°C, V _{OUT} > 1.8 V		V _{OUT}	x0.992		x1.008	V
	−40°C < Ta < 85°C, V _{OUT} > 1.8 V			x0.985		x1.015	V
	Ta = 25°C, V _{OUT} ≤ 1.8 V			−18		+18	mV
	−40°C < Ta < 85°C, V _{OUT} ≤ 1.8 V			−55		+55	mV
Output Voltage Temp. Coefficient	−40°C < Ta < 85°C, V _{OUT} > 1.8 V				±30		ppm/°C
	−40°C < Ta < 85°C, V _{OUT} ≤ 1.8 V				±100		
Load Regulation	1 mA < I _{OUT} ≤ 500 mA		Load _{Reg}		1	20	mV
Line Regulation	Set V _{OUT} + 0.5 V < V _{IN} < 5.25 V		Line _{Reg}		0.02	0.1	%/V
Dropout Voltage	I _{OUT} = 500 mA	0.7 V ≤ V _{OUT} < 0.8 V	V _{DO}		0.58	0.88	V
		0.8 V ≤ V _{OUT} < 0.9 V			0.52	0.80	
		0.9 V ≤ V _{OUT} < 1.0 V			0.45	0.70	
		1.0 V ≤ V _{OUT} < 1.2 V			0.42	0.64	
		1.2 V ≤ V _{OUT} < 1.4 V			0.35	0.53	
		1.4 V ≤ V _{OUT} < 1.8 V			0.31	0.48	
		1.8 V ≤ V _{OUT} < 2.1 V			0.27	0.41	
		2.1 V ≤ V _{OUT} < 2.5 V			0.25	0.38	
		2.5 V ≤ V _{OUT} < 3.0 V			0.23	0.34	
		3.0 V ≤ V _{OUT} < 3.6 V			0.22	0.32	
Output Current			I _{OUT}	500			mA
Short Current Limit	V _{OUT} = 0 V		I _{SC}		50		mA
Quiescent Current	I _{OUT} = 0 mA	V _{OUT} > 1.5 V	I _q		80	115	μA
		V _{OUT} ≤ 1.5 V			75		
Standby Current	V _{IN} = V _{IN max} , V _{CE} = 0 V		I _{STB}		0.1	1.0	μA
CE Pin Pull–Down Current			I _{PD}		0.3	0.6	μA
CE Pin Threshold Voltage	CE Input Voltage “H”		V _{CEH}	1.0		V _{IN}	V
	CE Input Voltage “L”		V _{CEL}			0.4	
Power Supply Rejection Ratio	V _{OUT} ≤ 2.0 V @ V _{IN} = 3.0 V, V _{OUT} > 2.0 V @ V _{IN} = = Set V _{OUT} + 1.0 V, ΔV _{IN_PK-PK} = 0.2 V, I _{OUT} = 30 mA	f = 1 kHz	PSRR		75		dB
		f = 10 kHz			70		
Output Noise Voltage	I _{OUT} = 30 mA , f = 10 Hz to 100 kHz, V _{OUT} > 1.8 V		V _{NOISE}		20 x V _{OUT}		μV _{rms}
	I _{OUT} = 30 mA, f = 10 Hz to 100 kHz, V _{OUT} ≤ 1.8 V				40 x V _{OUT}		
Thermal Shutdown / Hysteresis					165/65		°C
Auto–discharge N–MOS Resistance	V _{IN} = 4.0 V, V _{CE} = 0.0 V (Note 2)		R _{DS(on)}		60		Ω

2.

TYPICAL CHARACTERISTICS




Figure 3. Output Voltage vs. Output Current
0.7 V Version




Figure 4. Output Voltage vs. Output Current
2.5 V Version




Figure 5. Output Voltage vs. Output Current
3.6 V Version




Figure 6. Output Voltage vs. Input Voltage 0.7 V
Version




Figure 7. Output Voltage vs. Input Voltage 2.5 V
Version




Figure 8. Output Voltage vs. Input Voltage 3.6 V
Version

TYPICAL CHARACTERISTICS




Figure 9. Output Voltage vs. Temperature, 0.7 V Version




Figure 10. Output Voltage vs. Temperature, 2.5 V Version




Figure 11. Output Voltage vs. Temperature, 3.6 V Version




Figure 12. Dropout Voltage vs. Output Current, 0.7 V Version




Figure 13. Dropout Voltage vs. Output Current, 2.5 V Version




Figure 14. Dropout Voltage vs. Output Current, 3.6 V Version

TYPICAL CHARACTERISTICS




Figure 15. Quiescent Current vs. Input Voltage, 0.7 V Version




Figure 16. Quiescent Current vs. Input Voltage, 2.5 V Version




Figure 17. Quiescent Current vs. Input Voltage, 3.6 V Version




Figure 18. PSRR vs. Frequency, 0.7 V Version




Figure 19. PSRR vs. Frequency, 2.5 V Version




Figure 20. PSRR vs. Frequency, 3.6 V Version

TYPICAL CHARACTERISTICS




Figure 21. Output Noise vs. Frequency, 0.7 V Version




Figure 22. Output Noise vs. Frequency, 2.5 V Version




Figure 23. Output Noise vs. Frequency, 3.6 V Version




Figure 24. Line Transients, 0.7 V Version

TYPICAL CHARACTERISTICS




Figure 25. Line Transients, 2.5 V Version




Figure 26. Line Transients, 3.6 V Version




Figure 27. Load Transients, 0.7 V Version, Load Step 1 mA to 400 mA

TYPICAL CHARACTERISTICS




Figure 28. Load Transients, 2.5 V Version, Load Step 1 mA to 400 mA




Figure 29. Load Transients, 3.6 V Version, Load Step 1 mA to 400 mA




Figure 30. Load Transients, 0.7 V Version, Load Step 50 mA to 100 mA

TYPICAL CHARACTERISTICS




Figure 31. Load Transients, 2.5 V Version, Load Step 50 mA to 100 mA




Figure 32. Load Transients, 3.6 V Version, Load Step 50 mA to 100 mA




Figure 33. Turn On with CE Behavior, 0.7 V Version

TYPICAL CHARACTERISTICS




Figure 34. Turn On with CE Behavior, 2.5 V Version




Figure 35. Turn On with CE Behavior, 3.6 V Version




Figure 36. Turn Off with CE Behavior, 0.7 V Version

TYPICAL CHARACTERISTICS




Figure 37. Turn Off with CE Behavior, 2.5 V Version




Figure 38. Turn Off with CE Behavior, 3.6 V Version

APPLICATION INFORMATION

A typical application circuit for NCP4687 series is shown in the Figure 39.




Figure 39. Typical Application Schematic

Input Decoupling Capacitor (C1)

A 1.0 μF ceramic input decoupling capacitor should be connected as close as possible to the input and ground pin of the NCP4687 device. Higher values and lower ESR improves line transient response.

Output Decoupling Capacitor (C2)

A 1.0 μF ceramic output decoupling capacitor is sufficient to achieve stable operation of the device. If tantalum capacitor is used, and its ESR is high, the loop oscillation may result. The capacitor should be connected as close as possible to the output and ground pin. Larger values and lower ESR improves dynamic parameters.

Enable Operation

The enable pin CE may be used for turning the regulator on and off. The IC is switched on when a high level voltage is applied to the CE pin. The enable pin has an internal pull

down current source which assure off state of LDO in case the CE pin will stay floating. If the enable function is not needed connect CE pin to VIN.

The D version of the NCP4687 device includes a transistor between VOUT and GND that is used for faster discharging of the output capacitor. This function is activated when the IC goes into disable mode.

Thermal Consideration

As a power across the IC increase, it might become necessary to provide some thermal relief. The maximum power dissipation supported by the device is dependent upon board design and layout. Mounting pad configuration on the PCB, the board material, and also the ambient temperature affect the rate of temperature increase for the part. When the device has good thermal conductivity through the PCB the junction temperature will be relatively low in high power dissipation applications.

The IC includes internal thermal shutdown circuit that stops operation of regulator, if junction temperature is higher than 165°C. After that, when junction temperature decreases below 100°C, the operation of voltage regulator would restart. While high power dissipation condition is, the regulator starts and stops repeatedly and protects itself against overheating.

Sense Pin

The SENSE pin improves significantly the load regulation. The connection resistance between the LDO and the load given by PCB parameters has reduced impact to load regulation. If possible, use wide PCB traces as short as possible.

NCP4687

ORDERING INFORMATION


Device	Marking	Nominal Output Voltage	Feature	Package	Shipping [†]
NCP4687DH12T1G	A12D	1.2 V	Auto discharge	SOT-89 (Pb-Free)	1000 / Tape & Reel
NCP4687DH15T1G	A15D	1.5 V	Auto discharge	SOT-89 (Pb-Free)	1000 / Tape & Reel
NCP4687DH18T1G	A18D	1.8 V	Auto discharge	SOT-89 (Pb-Free)	1000 / Tape & Reel
NCP4687DH25T1G	A25D	2.5 V	Auto discharge	SOT-89 (Pb-Free)	1000 / Tape & Reel
NCP4687DH33T1G	A33D	3.3 V	Auto discharge	SOT-89 (Pb-Free)	1000 / Tape & Reel
NCP4687DMX18TCG	9P	1.8 V	Auto discharge	XDFN6 (Pb-Free)	5000 / Tape & Reel
NCP4687DMX25TCG	9X	2.5 V	Auto discharge	XDFN6 (Pb-Free)	5000 / Tape & Reel
NCP4687DMX33TCG	0G	3.3 V	Auto discharge	XDFN6 (Pb-Free)	5000 / Tape & Reel
NCP4687DSN18T1G	J18	1.8 V	Auto discharge	SOT-23 (Pb-Free)	3000 / Tape & Reel
NCP4687DSN25T1G	J25	2.5 V	Auto discharge	SOT-23 (Pb-Free)	3000 / Tape & Reel
NCP4687DSN28T1G	J28	2.8 V	Auto discharge	SOT-23 (Pb-Free)	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

NCP4687

PACKAGE DIMENSIONS

SOT-23 5-LEAD CASE 1212-01 ISSUE A




NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSIONS: MILLIMETERS.
3. DATUM C IS THE SEATING PLANE.

MILLIMETERS		
DIM	MIN	MAX
A	---	1.45
A1	0.00	0.10
A2	1.00	1.30
b	0.30	0.50
c	0.10	0.25
D	2.70	3.10
E	2.50	3.10
E1	1.50	1.80
e	0.95 BSC	
L	0.20	---
L1	0.45	0.75

RECOMMENDED SOLDERING FOOTPRINT*




DIMENSIONS: MILLIMETERS

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

PACKAGE DIMENSIONS

XDFN6 1.20x1.20, 0.40P
CASE 711AH
ISSUE O




NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.25mm FROM TERMINAL TIPS.
4. COPLANARITY APPLIES TO ALL OF THE TERMINALS.

DIM	MILLIMETERS	
	MIN	MAX
A	---	0.40
A1	0.00	0.05
b	0.13	0.23
D	1.20 BSC	
D2	0.89	0.99
E	1.20 BSC	
E2	0.25	0.35
e	0.40 BSC	
L	0.15	0.25
L1	0.05 BSC	

**RECOMMENDED
MOUNTING FOOTPRINT***




DIMENSIONS: MILLIMETERS

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.


NCP4687

PACKAGE DIMENSIONS


SOT-89, 5 LEAD CASE 528AB-01 ISSUE O



TOP VIEW



SIDE VIEW




BOTTOM VIEW

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. LEAD THICKNESS INCLUDES LEAD FINISH.
4. DIMENSIONS D AND E DO NOT INCLUDE MOLD FLASH, PROTRUSIONS, OR GATE BURRS.
5. DIMENSIONS L, L2, L3, L4, L5, AND H ARE MEASURED AT DATUM PLANE C.

DIM	MILLIMETERS	
	MIN	MAX
A	1.40	1.60
b	0.32	0.52
b1	0.37	0.57
c	0.30	0.50
D	4.40	4.60
D2	1.40	1.80
E	2.40	2.60
e	1.40	1.60
H	4.25	4.45
L	1.10	1.50
L2	0.80	1.20
L3	0.95	1.35
L4	0.65	1.05
L5	0.20	0.60

RECOMMENDED MOUNTING FOOTPRINT*



DIMENSIONS: MILLIMETERS

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative