


2SC4981

(TP7S8)

7A NPN

OUTLINE DIMENSIONS



RATINGS

• Absolute Maximum Ratings


Item	Symbol	Conditions	Ratings	Unit
Storage Temperature	Tstg		-55 ~ 150	
Junction Temperature	Tj		150	
Collector to Base Voltage	V _{CBO}		100	V
Collector to Emitter Voltage	V _{CEO}		80	V
Emitter to Base Voltage	V _{EBO}		7	V
Collector Current DC	I _C		7	A
Collector Current Peak	I _{CP}		14	A
Base Current DC	I _B		1.5	A
Base Current Peak	I _{BP}		2	A
Total Transistor Dissipation	P _T	Tc = 25	25	W
Dielectric Strength	Vdis	Terminal to case, AC 1 minute	2	kV
Mounting Torque	TOR	(Recommended torque : 0.3N·m)	0.5	N·m

• Electrical Characteristics (Tc=25)


Item	Symbol	Conditions	Ratings	Unit
Collector to Emitter Sustaining Voltage	V _{CEO} (sus)	I _C = 0.1A	Min 80	V
Collector Cutoff Current	I _{CBO}	At rated Voltage	Max 0.1	mA
	I _{CEO}		Max 0.1	
Emitter Cutoff Current	I _{EBO}	At rated Voltage	Max 0.1	mA
DC Current Gain	h _{FE}	V _{CE} = 2V, I _C = 3.5A	Min 70	
Collector to Emitter Saturation Voltage	V _{CE} (sat)	I _C = 3.5A	Max 0.3	V
Base to Emitter Saturation Voltage	V _{BE} (sat)	I _B = 0.2A	Max 1.2	V
Thermal Resistance	θ jc	Junction to case	Max 5	/W
Transition Frequency	f _T	V _{CE} = 10V, I _C = 0.7A	TYP 50	MHz
Turn on Time	ton	I _C = 3.5A I _{B1} = 0.35A, I _{B2} = 0.35A R _L = 8Ω, V _{BB2} = 4V	Max 0.3	μ s
Storage Time	ts		Max 1.5	
Fall Time	tf		Max 0.2	

2SC4981

$h_{FE} - I_C$




2SC4981 Saturation Voltage




2SC4981

Switching Time - I_C




2SC4981


Switching Time - T_c



2SC4981 Transient Thermal Impedance



2SC4981 Forward Bias SOA



2SC4981 Collector Current Derating

