






LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
CM	0		C	EC 0G3B 0215 05	24SEP05	BSV	RCJ



1. 0.00076[.000030] MIN GOLD AT POINT OF MEASUREMENT IN THE LOCALIZED GOLD PLATE AREA AND ON INSIDE OF WIRE BARREL; 0.00127[.000050] MIN NICKEL UNDERPLATE ON ENTIRE CONTACT.
2. WIRE RANGE: 0.05–0.15mm² [30–26] AWG. INSULATION RANGE: 0.81–1.45[.032–.057] DIA.
3. DIMENSIONS IN BRACKETS ARE IN INCHES.

GOLD 		0.30 [.012] PH BRZ		770416-6	
FINISH		MATERIAL		PART NO.	
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K. SALMON 20JAN93		 Tyco Electronics Corporation Harrisburg, PA 17105-3608	
		CHK R. SWING 20JAN93			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD M. TRULL 01APR93		SOCKET, LOOSE PIECE, UNIVERSAL MATE-N-LOK(TM) II	
		PRODUCT SPEC			
		APPLICATION SPEC			
		—			
MATERIAL		FINISH		SIZE CAGE CODE DRAWING NO RESTRICTED TO	
SEE TABLE		SEE TABLE		A2 00779 C-770416 —	
		WEIGHT —			
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 of 1 REV C	

