

Max. 320 m³/h

DC diagonal fan

□ 127 x 38 mm



Series DV 5200

Nominal data

Type	m ³ /h	cfm	VDC	VDC	dB(A)	Bel(A)	■ / ■	Watts	rpm ⁻¹	°C	Hours	Hours	Curve
DV 5212 N	270	159	12	9...15	56	6.4	■	21.0	5 000	-20...+65	70 000 / 40 000	117 500	①
DV 5214 N	270	159	24	16...30	56	6.4	■	20.4	5 000	-20...+65	70 000 / 40 000	117 500	①
DV 5218 N	270	159	48	36...60	56	6.4	■	18.5	5 000	-20...+65	70 000 / 40 000	117 500	①

Standard model comes with speed signal and PWM control input. Other versions by request.


DV 5214/2 HP	320	188	24	16...30	62	7.2	■	38.5	6 000	-20...+65	62 500 / 35 000	105 000	②
--------------	-----	-----	----	---------	----	-----	---	------	-------	-----------	-----------------	---------	---

Subject to change


Speed control range from 1000 rpm⁻¹ up to maximum nominal speed.

Standstill at 0% PWM, maximum speed if control cable is interrupted.

* Power consumption at free air flow. These values can be significantly higher in the operating point.



Air performance measured according to: ISO 5801.
Installation category A, without contact protection.
Noise: Total sound power level L_{WA} ISO 103002
measured on a hemisphere with a radius of 2 m.
Sound pressure level L_{PA} measured at 1 m distance from
fan axis.
The values given are applicable only under the specified
measuring conditions and may differ depending on the
installation conditions.
In the event of deviation from the standard configuration,
the parameters must be checked after installation!
For detailed information see
<http://www.ebmpapst.com/general conditions>



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ebm-papst](#):

[DV5212/2N-40184](#) [DV5218/2NP-40182](#) [DV5214/2N-40185](#) [DV5214N](#) [DV5218N](#) [DV5212N](#) [DV5218/2N](#)
[DV5212/2N](#) [DV5214/2N](#) [DV5288N](#) [DV5214/2NU-805](#) [DV5218/12NA-192](#) [DV5214/2NP-181](#) [DV5218/2N-40154](#)
[DV5214N/2U-807](#) [DV5214/2HP](#)