

1XE313

CATALOG LISTING

M

ISSUE
3

REPLACES

RELEASE NO. PR-20379

CHECK

CHECK


CHECK

2 NOV 92

DDM/CAD

DRAWN

TSM




NOTES

- ① MOUNTING HOLES WILL ACCEPT .087 MAX DIA PINS OR SCREWS ON .188 ± .002 CENTERS
- ② ACTUATION IN LINE WITH ARROW "A" IS RECOMMENDED
- ③ WEIGHT OF SWITCH ONLY IS .16 OZ MAX. WEIGHT OF SWITCH WITH WIRE LEADS IS .55 OZ MAX

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION



CHARACTERISTICS

OPERATING FORCE — — — — 5-17 OZ
RELEASE FORCE — — — — 4 OZ MIN
RELEASE TRAVEL — — — — .004 MIN
DIFFERENTIAL TRAVEL — — — .005 MAX
OVERTRAVEL — — — — .004 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
S P N O

28 VOLTS DC RATING
INDUCTIVE — SEA LEVEL — 4 AMP
50,000 FT — 2.5 AMP
RESISTIVE — SEA LEVEL — 7 AMP
50,000 FT — 7 AMP
LAMP — SEA LEVEL — 1 AMP
MOTOR — SEA LEVEL — 2.5 AMP
115 V 400 CYCLES — SEA LEVEL
RESISTIVE — 7 AMP
INDUCTIVE — 4 AMP
LAMP — 1 AMP
MOTOR — 1.5 AMP

SCALE 2 : 1

DO NOT
SCALE PRINT

UNLESS OTHERWISE SPECIFIED TOLERANCES ARE

ONE PLACE (.0) ± .030
TWO PLACE (.00) ± .015
THREE PLACE (.000) ± .005
ANGLES ±

WEIGHT ③

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1XE313](#)