

NCP4688

150 mA, Low Noise, LDO Linear Voltage Regulator

The NCP4688 is a CMOS 150 mA LDO linear voltage regulator with high output voltage accuracy which features a low noise output voltage and high ripple rejection. The low level of output noise 10 μ Vrms typically is kept at any output voltage. The very common SOT23-5 package and small μ DFN 1x1 package are suitable for industrial applications, portable communication equipments and RF modules.

Features

- Operating Input Voltage Range: 2 V to 5.25 V
- Output Voltage Range: 1.2 to 4.8 V (available in 0.1 V steps)
- $\pm 1\%$ Output Voltage Accuracy
- Output Noise: 10 μ Vrms
- Line Regulation: 0.02%/V
- Current Limit Circuit
- High PSRR: 80 dB at 1 kHz, 75 dB at 10 kHz
- Available in SOT-23-5 and μ DFN 1.0 x 1.0 mm Package
- These are Pb-Free Devices

Typical Applications

- Home Appliances, Industrial Equipment
- Cable Boxes, Satellite Receivers, Entertainment Systems
- Car Audio Equipment, Navigation Systems
- Notebook Adaptors, LCD TVs, Cordless Phones and Private LAN Systems
- RF Modules




Figure 1. Typical Application Schematic




ON Semiconductor™

<http://onsemi.com>


MARKING DIAGRAMS



SOT-23-5
CASE 1212



UDFN-4
CASE 517BR



(Top Views)

XX, XXX = Specific Device Code

M, MM = Date Code

▪ = Pb-Free Package

(*Note: Microdot may be in either location)

ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 12 of this data sheet.

NCP4688




Figure 2. Simplified Schematic Block Diagram

Table 1. PIN FUNCTION DESCRIPTION

Pin No. SOT-23-5	Pin No. DFN 1x1	Pin Name	Description
1	4	VIN	Input pin
2	2	GND	Ground pin
3	3	CE	Chip enable pin ("H" active)
4		NC	Non connected
5	1	VOUT	Output pin
	*EP	EP	Exposed Pad (leave floating or connect to GND)

Table 2. ABSOLUTE MAXIMUM RATINGS

Rating	Symbol	Value	Unit
Input Voltage	V_{IN}	0 – 6 V	V
Output Voltage	V_{OUT}	-0.3 to $V_{IN} + 0.3$	V
Chip Enable Input	V_{CE}	0 – 6 V	V
Power Dissipation SOT-23-5	P_D	420	mW
Power Dissipation μ DFN 1.0 x 1.0 mm		400	
Junction Temperature	T_J	-40 to 150	°C
Storage Temperature	T_{STG}	-55 to 125	°C
ESD Capability, Human Body Model (Note 1)	ESD_{HBM}	2000	V
ESD Capability, Machine Model (Note 1)	ESD_{MM}	200	V

Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.

- This device series incorporates ESD protection and is tested by the following methods:
 ESD Human Body Model tested per AEC-Q100-002 (EIA/JESD22-A114)
 ESD Machine Model tested per AEC-Q100-003 (EIA/JESD22-A115)
 Latchup Current Maximum Rating tested per JEDEC standard: JESD78

Table 3. THERMAL CHARACTERISTICS

Rating	Symbol	Value	Unit
Thermal Characteristics, SOT-23-5 Thermal Resistance, Junction-to-Air	$R_{\theta JA}$	238	$^{\circ}\text{C/W}$
Thermal Characteristics, $\mu\text{DFN } 1 \times 1$ Thermal Resistance, Junction-to-Air	$R_{\theta JA}$	250	$^{\circ}\text{C/W}$

Table 4. ELECTRICAL CHARACTERISTICS

($-40^{\circ}\text{C} \leq T_A \leq 85^{\circ}\text{C}$; $C_{IN} = C_{OUT} = 1.0 \mu\text{F}$, unless otherwise noted. Typical values are at $T_A = +25^{\circ}\text{C}$.)

Parameter	Test Conditions		Symbol	Min	Typ	Max	Unit
Operating Input Voltage	1.2 V < Vout < 4.8 V		VIN	2.0		5.25	V
Output Voltage	Ta = 25°C, Vout > 2.0 V		VOUT	x0.99		x1.01	V
	−40°C < Ta < 85°C, Vout > 2.0 V			x0.985		x1.015	V
	Ta = 25°C, Vout ≤ 2.0 V			−20		+20	mV
	−40°C < Ta < 85°C, Vout ≤ 2.0 V			−30		+30	mV
Output Voltage Temp. Coefficient	−40°C < Ta < 85°C				±100		ppm/°C
Line Regulation	Set Vout + 0.3 < VIN < 5.25 V	Vout > 4.1 V	LineReg		0.02	0.10	%/V
	Set Vout + 0.5 < VIN < 5.0 V	1.7 V ≤ VOUT < 4.1 V					
	2.2 < VIN < 5.0 V	Vout < 1.7 V					
Load Regulation	1 mA < IOUT ≤ 150 mA		LoadReg	−14	0	14	mV
Dropout Voltage	IOUT = 150 mA	1.2 V ≤ VOUT < 1.3 V	VDO		0.39	0.80	V
		1.3 V ≤ VOUT < 1.4 V			0.37	0.70	
		1.4 V ≤ VOUT ≤ 1.5 V			0.34	0.60	
		1.5 V ≤ VOUT < 1.7 V			0.32	0.50	
		1.7 V ≤ VOUT < 2.0 V			0.29	0.41	
		2.0 V ≤ VOUT < 2.5 V			0.25	0.36	
		2.5 V ≤ VOUT < 2.8 V			0.22	0.31	
		2.8 V ≤ VOUT ≤ 4.8 V			0.20	0.28	
Output Current			IOUT	150			mA
Short Current Limit	VOUT = 0 V		ISC		40		mA
Quiescent Current	Iout = 0 mA	Vout > 4.1 V	IQ		80	100	μA
		Vout ≤ 4.1 V			75		
Standby Current	VIN = VIN max , VCE = 0 V		ISTB		0.1	1.0	μA
CE Pin Pull–Down Current			IPD		0.3	0.6	μA
CE Pin Threshold Voltage	CE Input Voltage “H”		VCEH	1.0		VIN	V
	CE Input Voltage “L”		VCEL			0.4	
Power Supply Rejection Ratio	VOUT > 4.1 V @ VIN = 5.25 V, f = 1 kHz VOUT ≤ 4.1 V @ VIN = Set VOUT + 1.0 V, ΔVIN_PK–PK = 0.2 V, IOUT = 30 mA	f = 10 kHz	PSRR		80		dB
		f = 100 kHz			75		
					65		
Output Noise Voltage	IOUT = 30 mA, f = 10 Hz to 100 kHz		VNOISE		10		μVrms
Autodischarge NMOS Resistance	VIN = 4.0 V, VCE = 0.0 V		RDSON		60		ohm

TYPICAL CHARACTERISTICS




Figure 3. Output Voltage vs. Output Current
NCP4688xx12




Figure 4. Output Voltage vs. Output Current
NCP4688xx25




Figure 5. Output Voltage vs. Output Current
NCP4688xx40




Figure 6. Output Voltage vs. Input Voltage
NCP4688xx12




Figure 7. Output Voltage vs. Input Voltage
NCP4688xx25






Figure 8. Output Voltage vs. Input Voltage
NCP4688xx40


TYPICAL CHARACTERISTICS




**Figure 9. Supply Current vs. Input Voltage
NCP4688xx12**




**Figure 10. Supply Current vs. Input Voltage
NCP4688xx25**




**Figure 11. Supply Current vs. Input Voltage
NCP4688xx40**



**Figure 12. Supply Current vs. Temperature
NCP4688xx12**




**Figure 13. Supply Current vs. Temperature
NCP4688xx25**




**Figure 14. Supply Current vs. Temperature
NCP4688xx40**


TYPICAL CHARACTERISTICS




**Figure 15. Output Voltage vs. Temperature
NCP4688xx12**




**Figure 16. Output Voltage vs. Temperature
NCP4688xx25**




**Figure 17. Output Voltage vs. Temperature
NCP4688xx40**



**Figure 18. Dropout Voltage vs. Output Current
NCP4688xx12**



**Figure 19. Dropout Voltage vs. Output Current
NCP4688xx25**



**Figure 20. Dropout Voltage vs. Output Current
NCP4688xx40**

TYPICAL CHARACTERISTICS




Figure 21. PSRR vs. Frequency NCP4688xx12




Figure 22. PSRR vs. Frequency NCP4688xx25




Figure 23. PSRR vs. Frequency NCP4688xx40




Figure 24. Output Noise Density vs. Frequency NCP4688xx12




Figure 25. Output Noise Density vs. Frequency NCP4688xx25




Figure 26. Output Noise Density vs. Frequency NCP4688xx40

TYPICAL CHARACTERISTICS




Figure 27. Line Transient Response
NCP4688xx12




Figure 28. Line Transient Response
NCP4688xx25




Figure 29. Line Transient Response
NCP4688xx40




Figure 30. Load Transient Response Load
Step 1 mA to 150 mA NCP4688xx12




Figure 31. Load Transient Response Load
Step 50 mA to 100 mA NCP4688xx12




Figure 32. Load Transient Response Load
Step 1 mA to 150 mA NCP4688xx25

TYPICAL CHARACTERISTICS




Figure 33. Load Transient Response Load Step 50 mA to 100 mA NCP4688xx25




Figure 34. Load Transient Response Load Step 1 mA to 150 mA NCP4688xx40




Figure 35. Load Transient Response Load Step 50 mA to 100 mA NCP4688xx40




Figure 36. Turn Off with CE Behavior NCP4688Dx12




Figure 37. Turn Off with CE Behavior NCP4688Dx25




Figure 38. Turn Off with CE Behavior NCP4688Dx40

TYPICAL CHARACTERISTICS




Figure 39. Turn ON with CE Behavior
NCP4688xx12




Figure 40. Turn ON with CE Behavior
NCP4688xx25

APPLICATION INFORMATION

A typical application circuit for NCP4688 series is shown in the Figure 41.




Figure 41. Typical Application Schematic

Input Decoupling Capacitor (C1)

A 1.0 μF ceramic input decoupling capacitor should be connected as close as possible to the input and ground pin of the NCP4688 device. Higher values and lower ESR improves line transient response.

Output Decoupling Capacitor (C2)

A 1.0 μF ceramic output decoupling capacitor is sufficient to achieve stable operation of the device. If tantalum capacitor is used, and its ESR is high, the loop oscillation may result. For information about ESR see Figures 42, 43 and 44. The capacitor should be connected as close as possible to the output and ground pin. Larger values and lower ESR improves dynamic parameters.

Enable Operation

The enable pin CE may be used for turning the regulator on and off. The IC is switched on when a high level voltage is applied to the CE pin. The enable pin has an internal pull down current source which assure off state of LDO in case the CE pin will stay floating. If the enable function is not needed connect CE pin to V_{IN} .

The D version of the NCP4688 device includes a transistor between V_{OUT} and GND that is used for faster discharging of the output capacitor. This function is activated when the IC goes into disable mode.

Thermal Consideration

As a power across the IC increase, it might become necessary to provide some thermal relief. The maximum power dissipation supported by the device is dependent upon board design and layout. Mounting pad configuration on the PCB, the board material, and also the ambient temperature affect the rate of temperature increase for the part. When the device has good thermal conductivity through the PCB the junction temperature will be relatively low in high power dissipation applications.

ESR vs. Output Current

When using the NCP4688 devices, consider the following points:

The relation between Output Current I_{out} and ESR of the output capacitor are shown below in Figures 42, 43 and 44. The conditions when the device performs stable operation are marked as the hatched area in the charts.




Figure 42. ESR vs. Load Current NCP4688xx12




Figure 43. ESR vs. Load Current NCP4688xx25

NCP4688




Figure 44. ESR vs. Load Current NCP4688xx40




ORDERING INFORMATION

Device	Marking	Nominal Output Voltage	Feature	Package	Shipping [†]
NCP4688DMU12TCG	3A	1.2 V	Auto discharge	DFN1010 (Pb-Free)	10000 / Tape & Reel
NCP4688DMU15TCG	3E	1.5 V	Auto discharge	DFN1010 (Pb-Free)	10000 / Tape & Reel
NCP4688DMU18TCG	3H	1.8 V	Auto discharge	DFN1010 (Pb-Free)	10000 / Tape & Reel
NCP4688DMU25TCG	3R	2.5 V	Auto discharge	DFN1010 (Pb-Free)	10000 / Tape & Reel
NCP4688DMU28TCG	3U	2.8 V	Auto discharge	DFN1010 (Pb-Free)	10000 / Tape & Reel
NCP4688DMU30TCG	3X	3.0 V	Auto discharge	DFN1010 (Pb-Free)	10000 / Tape & Reel
NCP4688DMU33TCG	4A	3.3 V	Auto discharge	DFN1010 (Pb-Free)	10000 / Tape & Reel
NCP4688DSN12T1G	L12	1.2 V	Auto discharge	SOT-23 (Pb-Free)	3000 / Tape & Reel
NCP4688DSN15T1G	L15	1.5 V	Auto discharge	SOT-23 (Pb-Free)	3000 / Tape & Reel
NCP4688DSN18T1G	L18	1.8 V	Auto discharge	SOT-23 (Pb-Free)	3000 / Tape & Reel
NCP4688DSN25T1G	L25	2.5 V	Auto discharge	SOT-23 (Pb-Free)	3000 / Tape & Reel
NCP4688DSN28T1G	L28	2.8 V	Auto discharge	SOT-23 (Pb-Free)	3000 / Tape & Reel
NCP4688DSN33T1G	L33	3.3 V	Auto discharge	SOT-23 (Pb-Free)	3000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

PACKAGE DIMENSIONS


UDFN4 1.0x1.0, 0.65P
CASE 517BR-01
ISSUE O




NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSION: MILLIMETERS.
3. DIMENSION b APPLIES TO PLATED TERMINAL AND IS MEASURED BETWEEN 0.15 AND 0.20 mm FROM TERMINAL.
4. COPLANARITY APPLIES TO THE EXPOSED PAD AS WELL AS THE TERMINALS.

MILLIMETERS		
DIM	MIN	MAX
A	---	0.60
A1	0.00	0.05
A3	0.10	REF
b	0.20	0.30
D	1.00	BSC
D2	0.43	0.53
E	1.00	BSC
e	0.65	BSC
L	0.20	0.30
L2	0.27	0.37
L3	0.02	0.12



RECOMMENDED
MOUNTING FOOTPRINT*





*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

NCP4688

PACKAGE DIMENSIONS

SOT-23 5-LEAD CASE 1212-01 ISSUE A




NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
2. CONTROLLING DIMENSIONS: MILLIMETERS.
3. DATUM C IS THE SEATING PLANE.

MILLIMETERS		
DIM	MIN	MAX
A	---	1.45
A1	0.00	0.10
A2	1.00	1.30
b	0.30	0.50
c	0.10	0.25
D	2.70	3.10
E	2.50	3.10
E1	1.50	1.80
e	0.95 BSC	
L	0.20	---
L1	0.45	0.75

RECOMMENDED SOLDERING FOOTPRINT*



DIMENSIONS: MILLIMETERS

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 5163, Denver, Colorado 80217 USA
Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada
Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: <http://www.onsemi.com/orderlit>

For additional information, please contact your local Sales Representative