



THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.




LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
J	—			RELEASED FJB0-1203-04	02NOV04



POWER CONT. SECTION



SIGNAL CONT. SECTION



PANEL CUT-OUT DIMENSIONS

P/N	PACKING TYPE	EMBOSS
	TRAY	
6376818-1		

1	1	1	1	SHELL	—	COPPER ALLOY	Tin PLATING	4
1				HOUSING WITH KEY 4	12.2	THERMOPLASTIC	—	3
	1			HOUSING WITH KEY 3	11.1	THERMOPLASTIC	—	3
		1		HOUSING WITH KEY 2	10.0	THERMOPLASTIC	—	3
			1	HOUSING WITH KEY 1	8.9	THERMOPLASTIC	—	3
4	4	4	4	POWER CONTACT	—	COPPER ALLOY	CONTACT AREA: Au PL. OVER Ni PL.	2
34	34	34	34	SIGNAL CONTACT	—	COPPER ALLOY	SOLDER TAIL: Tin PL. OVER Ni PL.	1
QTY				NAME	DIM A	MATERIAL	FINISH	ITEM NO.

PARTS LIST

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 特 MM	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差
	0-PLC ± 1-PLC ± ± 0.5 2-PLC ± ± 3° 3-PLC ± 4-PLC ± ANGLES ±
MATERIAL 材料 SEE TABLE	FINISH 仕上 SEE TABLE

DWN A.KUBO CHK S.KAJINUMA APVD Y.YAMAMOTO PRODUCT SPEC 製品規格 108-78219 APPLICATION SPEC 取付適用規格	01NOV04 02NOV04 02NOV04	tyco Electronics Tyco Electronics AMP K.K. Kawasaki, Japan	NAME 名称 HEADER 1MM GIGA I/O CONN. LEAD-FREE	SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C-6376818	RESTRICTED TO —
WEIGHT 6.3 g	CUSTOMER DRAWING	SCALE 尺度 2:1	SHEET 1 OF 4	REV 0			


THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

© COPYRIGHT BY TYCO ELECTRONICS CORPORATION.


ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS				
J	—	P	LTR	DESCRIPTION	DATE	DWN
				変更		APVD
				SEE SHEET 1	—	—



- 1 PWB: 1.0t
METAL MASK: 0.12t
(リフロー後、スルーホール部は手半田でのフィレット形成を推奨)


- 2 スタンドオフ エリア (パターン 禁止領域)
3 コンタクトタイン部の平坦度 (COPLANARITY) は 0.1 MAX



4. パッキング仕様 : SHEET 3,4を参照のこと。


- 1 PWB: 1.0t
METAL MASK: 0.12t
(MANUAL TOUCH UP IS RECOMMENDED TO CREATE SOLDER FILET AT THROUGH HOLE AREA AFTER REFLOW MOUNTING)

- 2 STAND-OFF AREA (PROHIBITED PATTERN AREA)
3 COPLANARITY AT CONTACT TINES : 0.1 MAX



4. PACKING TYPE : REFERENCE TO SHEET 3,4

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 寸
MMMATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC ± —
1 PLC ± —
2 PLC ± —
3 PLC ± —
4 PLC ± —
ANGLES ± —
FINISH 仕上

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

tyco
Electronics

 Tyco Electronics AMP K.K.
Kawasaki, Japan
NAME
名称
 HEADER
1MM GIGA I/O CONN.
LEAD-FREE

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

A3

00779

C-6376818

SCALE
尺度 4:1

SHEET 2 OF 4

REV 0

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION



COPYRIGHT

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

変更




DESCRIPTION

DATE


DWN

APVD

SEE SHEET 1



SECT "A"-"A"



SECT "B"-"B"


PACKING TYPE : TRAY ASSY
AS SHOWN : -1

TRAY ASSY LAYOUT

36 PCS/TRAY

QTY

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
単位: 耗
MMMATERIAL
材料TOLERANCES UNLESS
OTHERWISE SPECIFIED:
一般公差

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	仕上

FINISH
仕上

DWN

CHK

APVD

PRODUCT SPEC
製品規格APPLICATION SPEC
取付適用規格

WEIGHT

CUSTOMER DRAWING

tyco
ElectronicsTyco Electronics AMP K.K.
Kawasaki, JapanNAME
名称HEADER
1MM GIGA I/O CONN.
LEAD-FREE

SIZE

CAGE CODE

DRAWING NO
番号

RESTRICTED TO

A3

00779

C-6376818

SCALE
尺度 NONSHEET
3 OF 4REV
0

