







LOC	DIST	REVISIONS					
GP	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			L	REVISED PER ECO-13-012013	09AUG2013	CJV	CWR



- ① CONTACTS DESIGNED FOR 26 & 28 AWG STRANDED OR 26, 28 & 30 AWG SOLID WIRE.
- ② AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.
- ③ STANDOFFS: POS 10 (2) STANDOFFS AS SHOWN.
14-16 (3) STANDOFFS, (1) CENTERED BETWEEN (2) SHOWN
20-26 (4) (2)
30 (5) (3)
34 (6) (4)
40-44 (7) (5)
50 (8) (6)
60 (9) (7)
64 (10) (8)
- ④ .000100-.000200 BRIGHT TIN-LEAD, ALL OVER .000050 NICKEL.
- ⑤ HEIGHT AFTER TERMINATION IS .253 ±.010.
6. FOR USE IN .062 - .093" THICK PCB.
- ⑦ .000005 MIN GOLD ON RIBBON CABLE TERMINATION AREA,
.000100-.000200 MATTE TIN ON SOLDER TAILS, ALL OVER
.000050 MIN NICKEL.
- ⑧ MOLDED PARTS, 94V-0 RATED THERMOPLASTIC, COLOR: BLACK
CONTACTS: PHOS BRONZE.



		24	2.680	48	49	50	2-111382-0
		16	1.880	32	33	34	1-111382-9
		12	1.480	24	25	26	1-111382-8
		9	1.180	18	19	20	1-111382-7
		7	0.980	14	15	16	1-111382-6
		4	.680	8	9	10	1-111382-4
OBSOLETE		21	2.380	42	43	44	1-111382-3
OBSOLETE		31	3.380	62	63	64	1-111382-2
OBSOLETE		29	3.180	58	59	60	1-111382-1
OBSOLETE		24	2.680	48	49	50	1-111382-0
OBSOLETE		19	2.180	38	39	40	111382-9
OBSOLETE		16	1.880	32	33	34	111382-8
OBSOLETE		14	1.680	28	29	30	111382-7
OBSOLETE		12	1.480	24	25	26	111382-6
OBSOLETE		11	1.380	22	23	24	111382-5
		9	1.180	18	19	20	111382-4
OBSOLETE		7	.980	14	15	16	111382-3
OBSOLETE		6	.880	12	13	14	111382-2
OBSOLETE		4	.680	8	9	10	111382-1
	CONTACT FINISH	D	C	B	A	NO OF POSN	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 11-29-04 L. VARELA - DOCKS CHK 11-29-04 C. ROHDE		 TE Connectivity	
DIMENSIONS: INCHES		TOLERANCES, UNLESS OTHERWISE SPECIFIED: APD 11-29-04 M. WALMSLEY		NAME	
		PRODUCT SPEC 108-40013		KIT, DIP PLUG, PREASSEMBLED, .100 X .100 CENTERLINE, AMP-LATCH	
MATERIAL 		APPLICATION SPEC 114-40005		SIZE CAGE CODE DRAWING NO	
FINISH 		WEIGHT —		A1 00779 C 111382	
CONTACTS: SEE TABLE		CUSTOMER DRAWING		SCALE 10:1 SHEET 1 OF 1 REV —	