



Pb-free
HEAT



DN504

Through-hole IRED/Right Angle Type

Features

Package	φ 3.6 Right Angle type, Water clear epoxy
Product features	<ul style="list-style-type: none">• High Total Power : 12mW TYP. ($I_F=50mA$)• High Speed : Cut-off Frequency 20 TYP. MHz ($I_F=50mA$)• Lead-free soldering compatible• RoHS compliant
Peak Wavelength	850nm
Half Intensity Angle	80 deg.
Die materials	GaAlAs
Rank grouping parameter	Sorted by radiant intensity per rank taping
Soldering methods	TTW (Through The Wave) soldering and manual soldering ※Please refer to Soldering Conditions about soldering.
ESD	2kV (HBM)
Packing	Bulk : 200pcs(MIN.)

Recommended Applications

Electric Household Appliances, OA/FA, PC/Peripheral Equipment, Other General Applications

Absolute Maximum Ratings

(Ta=25°C)

Item	Symbol	Absolute Maximum Ratings	Unit
Power Dissipation	Pd	150	mW
Forward Current	I _F	100	mA
Pulse Forward Current ※1	I _{FRM}	1,000	mA
Derating (Ta=25°C or higher)	ΔI _F	1.33	mA/°C
	ΔI _{FRM}	13.3	mA/°C
Reverse Voltage	V _R	5	V
Operating Temperature	T _{opr}	-30~+85	°C
Storage Temperature	T _{stg}	-30~+100	°C

※1 IFRM Measurement condition : Pulse Width ≤ 100 μs, Duty ≤ 1/100

Electro-Optical Characteristics

(Ta=25°C)

Item	Conditions	Symbol	Characteristics		Unit
Forward Voltage	I _F =50mA	V _F	TYP.	1.6	V
			MAX.	2.0	
Reverse Current	V _R =5V	I _R	MAX.	100	μA
Radiant Intensity	I _F =50mA	I _E	MIN.	4	mW/sr
			TYP.	8	
Total Output Power	I _F =50mA	P _o	TYP.	12	mW
Peak Wavelength	I _F =50mA	λ _p	TYP.	850	nm
Spectral Half-width	I _F =50mA	Δλ	TYP.	40	nm
Half Intensity Angle	I _F =50mA	2θ _{1/2}	TYP.	80	deg.
Cut-off Frequency	I _F =50mA _{DC} ±5mA, -3db from 0.1MHz	fc	MIN.	-	MHz
			TYP.	30	
Response Time	I _F =50mA	tr/ta	TYP.	10	ns

Radiant Intensity Rank


(Ta=25°C)

Rank	I _E (mW/sr)		Condition
	MIN.	MAX.	
A	4.0	8.0	I _F = 50mA
B	5.6	11.2	
C	8.0	16.0	
D	11.2	22.4	
E	16.0	-	

※Please contact our sales staff concerning rank designation.


Technical Data

Spectral Distribution
Relative Intensity vs. Wavelength
Condition : $T_a = 25^\circ\text{C}$, $I_F = 50\text{mA}$




Spatial Distribution Example


Condition : $T_a = 25^\circ\text{C}$



Forward Voltage vs. Forward Current
Condition : $T_a = 25^\circ\text{C}$




Duty Ratio vs. Pulse Forward Current
Condition : $T_a = 25^\circ\text{C}$, $t_w \leq 100\mu\text{s}$




Technical Data


Ambient Temperature vs. Forward Current




Ambient Temperature vs. Pulse Forward Current
Condition : $t_w \leq 100 \mu s$, Duty $\leq 1/100$



Ambient Temperature vs. Forward Voltage
Condition : $I_F = 50mA$




Ambient Temperature vs. Peak Wavelength
Condition : $I_F = 50mA$



Technical Data


Forward Current vs. Relative Total Power

Condition : -- Pulse, $t_w \leq 100 \mu s$,
Duty $\leq 1/100$, $T_a = 25^\circ C$
--DC




Ambient Temperature vs. Relative Total Power

Condition : $I_F = 50mA$




Frequency

Condition : $T_a = 25^\circ C$, $I_F = 50mA_{DC} \pm 5mA$




Pulse Forward Voltage vs. Pulse Forward Current

Condition : $T_a = 25^\circ C$, $t_w \leq 100 \mu s$, Duty $\leq 1/100$



Package Dimensions

(Unit: mm)





DN504

Through-hole IRED/Right Angle Type

TTW (Through The Wave) soldering Conditions

Pre-heating	100 °C	(MAX.) Resin surface temperature
Solder Bath Temp.	265 °C	(MAX.)
Dipping Time	5 s	(MAX.)
Position	At least 3.0 mm away from the root of lead	

- 1) The dip soldering process shall be twice maximum.
- 2) The product shall be cooled to normal temperature before the second dipping process.
 ※The detail is described to LED and Photodetector handling precautions of home page:
 "Mounting through-hole Type Devices" and "Soldering", and use it after the confirmation, please.

Manual Soldering Conditions

Iron tip temp.	400 °C	(MAX.) (30 W Max.)
Soldering time and frequency	3 s	(MAX.)
	1 time	(MAX.)
Position	At least 3.0 mm away from the root of lead	

※The detail is described to LED and Photodetector handling precautions of home page:
 "Mounting through-hole Type Devices" and "Soldering", and use it after the confirmation, please.

Reliability Testing Result

Reliability Testing Result	Applicable Standard	Testing Conditions	Duration	Failure
Room Temp. Operating Life	EIAJ ED-4701/100(101)	Ta = 25°C, If = Maximum Rated Current	1,000 h	0/25
Resistance to Soldering Heat	EIAJ ED-4701/300(302)	265±5°C, 3mm from package base	10s	0/25
Temperature Cycling	EIAJ ED-4701/100(105)	Minimum Rated Storage Temperature(30min) ~Normal Temperature(15min) ~Maximum Rated Storage Temperature(30min) ~Normal Temperature(15min)	5 cycles	0/25
Wet High Temp. Storage Life	EIAJ ED-4701/100(103)	Ta = 60±2°C, RH = 90±5%	1,000 h	0/25
High Temp. Storage Life	EIAJ ED-4701/200(201)	Ta = Maximum Rated Storage Temperature	1,000 h	0/25
Low Temp. Storage Life	EIAJ ED-4701/200(202)	Ta = Minimum Rated Storage Temperature	1,000 h	0/25
Lead Tension	EIAJ ED-4701/400(401)	10N, 1time (□0.4 and Flat Package : 5N)	10s	0/10
Vibration, Variable Frequency	EIAJ ED-4701/400(403)	98.1m/s ² (10G), 100 ~ 2KHz sweep for 20min., XYZ each direction	2 h	0/10

Failure Criteria

Items	Symbols	Conditions	Failure criteria
Luminous Intensity	Iv	If Value of each product Luminous Intensity	Testing Min. Value < Spec. Min. Value x 0.5
Forward Voltage	V _F	If Value of each product Forward Voltage	Testing Max. Value ≥ Spec. Max. Value x 1.2
Reverse Current	I _R	V _R = Maximum Rated Reverse Voltage V	Testing Max. Value ≥ Spec. Max. Value x 2.5

Special Notice to Customers Using the Products and Technical Information Shown in This Data Sheet

- 1) The technical information shown in the data sheets are limited to the typical characteristics and circuit examples of the referenced products. It does not constitute the warranting of industrial property nor the granting of any license.
- 2) For the purpose of product improvement, the specifications, characteristics and technical data described in the data sheets are subject to change without prior notice. Therefore it is recommended that the most updated specifications be used in your design.
- 3) When using the products described in the data sheets, please adhere to the maximum ratings for operating voltage, heat dissipation characteristics, and other precautions for use. We are not responsible for any damage which may occur if these specifications are exceeded.
- 4) The products that have been described to this catalog are manufactured so that they will be used for the electrical instrument of the benchmark (OA equipment, telecommunications equipment, AV machine, home appliance and measuring instrument).
The application of aircrafts, space borne application, transportation equipment, medical equipment and nuclear power control equipment, etc. needs a high reliability and safety, and the breakdown and the wrong operation might influence the life or the human body. Please consult us beforehand if you plan to use our product for the usages of aircrafts, space borne application, transportation equipment, medical equipment and nuclear power control equipment, etc. except OA equipment, telecommunications equipment, AV machine, home appliance and measuring instrument.
- 5) In order to export the products or technologies described in this data sheet which are under the "Foreign Exchange and Foreign Trade Control Law," it is necessary to first obtain an export permit from the Japanese government.
- 6) No part of this data sheet may be reprinted or reproduced without prior written permission from Stanley Electric Co., Ltd.
- 7) The most updated edition of this data sheet can be obtained from the address below:
<http://www.stanley-components.com>