



ELECTRONICS, INC.
44 FARRAND STREET
BLOOMFIELD, NJ 07003
(973) 748-5089
<http://www.nteinc.com>

NTE1419 Integrated Circuit Head Amp Circuit for VCR

Features:

- Video Signal Pre-Amplifier Circuit
- Filter Amplifier Circuit
- Mixer Amplifier Circuit
- Head Switch Over Circuit
- Supply Voltage, either 9V or 12V

Absolute Maximum Ratings: ($T_A = +25^\circ\text{C}$, unless otherwise specified)

Supply Voltage, V_{CC}	14.4V
Power Dissipation, P_D	530mW
Operating Temperature Range, T_{opg}	-20° to $+70^\circ\text{C}$
Storage Temperature Range, T_{stg}	-40° to $+150^\circ\text{C}$

Electrical Characteristics: ($T_A = +25^\circ\text{C}$, $V_{CC} = 12\text{V}$ unless otherwise specified)

Parameter	Symbol	Test Conditions	Min	Typ	Max	Unit
Supply Current	I_1		26	–	44	mA
Voltage Gain (Head Amp)	$G_{V(1)}$	$f = 4\text{MHz}$, $v_i = 1\text{mV}_{p-p}$	50.5	–	62.5	mA
	$G_{V(1)}$		50.5	–	62.5	mA
Voltage Gain (Mix Amp)	$G_{V(3)}$		10	–	14	dB
Second Harmonic Distortion (Head Amp)	$D_{2(1)}$		–	–	–40	dB
	$D_{2(2)}$		–	–	–40	dB
Input Noise Voltage	$V_{ni(1)}$	$f = 1\text{MHz}$, B.P.F	–	–	2	μV_{rms}
	$V_{ni(2)}$		–	–	–2	μV_{rms}
Sensitivity	S		300	–	–	μA

Pin Connection Diagram

