

Low Profile Holder Type Crystal Units



FEATURES

- Low cost
- Industry standard
- Wide frequency range
- Excellent aging
- Material categorization: for definitions of compliance please see www.vishay.com/doc?99912


RoHS
COMPLIANT

This part is a miniature AT cut strip crystal unit with a low profile package. It is with resistance weld.


STANDARD ELECTRICAL SPECIFICATIONS

PARAMETER	SYMBOL	CONDITION	UNIT	MIN.	TYP.	MAX.
Frequency range	F _O		MHz	3.579545	-	66.000
Frequency tolerance	ΔF/F _O	At 25 °C	ppm	-	± 10, ± 15, ± 20, ± 25, ± 30	-
Temperature stability	T _C	Ref. to 25 °C	ppm	-	± 20, ± 25, ± 30, ± 35, ± 50, ± 100	-
Operating temperature range	T _{OPR}		°C	-10	-	+70
Storage temperature range	T _{STG}		°C	-55	-	+125
Shunt capacitance	C ₀		pF	-	-	7
Load capacitance	C _L	Customer specified	pF	10	-	Series
Insulation resistance	I _R	100 V _{DC}	MΩ	500	-	-
Drive level	D _L		μW	-	100	500
Aging (first year)	Fa	At 25 °C, per year	ppm	-5	-	+5

EQUIVALENT SERIES RESISTANCE (ESR) AND MODE OF VIBRATION (MODE)

FREQUENCY RANGE (MHz)	MAX. ESR (Ω)	MODE	FREQUENCY RANGE (MHz)	MAX. ESR (Ω)	MODE
3.579 to 3.999	200	Fundamental / AT	10.000 to 13.999	80	Fundamental / AT
4.000 to 4.999	150	Fundamental / AT	14.000 to 39.999	50	Fundamental / AT
5.000 to 5.999	120	Fundamental / AT	40.000 to 66.000	80	3 rd overtone
6.000 to 9.999	100	Fundamental / AT	-	-	-

DIMENSIONS in inches [millimeters]



**PART NUMBER CONFIGURATIONS** (to be used on all New Designs)

X	T	9	S	2	0	A	J	R	G	X	8	M	1	9	2	E
Crystal		Package / Size		Load Cap.		Pack Code	Freq. Tolerance	Operating Temp.	Temp. Stability	Options		Frequency				Lead (PB)-free
		9S		20 = std. SE = series		A = bulk	G = ± 30 ppm E = ± 25 ppm H = ± 20 ppm I = ± 15 ppm J = ± 10 ppm	S = -10 °C to +70 °C R = -40 °C to +85 °C	C = ± 100 ppm D = ± 50 ppm F = ± 35 ppm G = ± 30 ppm E = ± 25 ppm H = ± 20 ppm	X = no options Contact factory for available options		Use "M" as decimal place holder Frequency must be five digits - complete with "0" at the end				E = lead (Pb)-free

Previous / legacy part number information: still valid for existing designs;
all New Designs should use the new part configuration above

PREVIOUS / LEGACY GLOBAL PART NUMBERING

X	T	9	S	2	0	A	N	A	4	0	M
MODEL NUMBER				LOAD CAPACITANCE		PACKAGE CODE	OPTIONS		FREQUENCY		
XT9S = XT49S				18 = 18 pF 20 = 20 pF NL = series to be specified by customer		Tape and reel H = RF7 (XT9M) Bulk A = B04 (all models)	NA = no additional options RR = extended temperature of -40 °C to +85 °C Contact factory for all other options		4M = 4 MHz 40M = 40 MHz 100M = 100 MHz 12M288 = 12.288 MHz M is used as decimal place holder in frequency		
XT49S	R	-20		SP		12M		e2			
MODEL	OTR	LOAD		OPTIONS		FREQUENCY/MHz		JEDEC® LEAD (Pb)-FREE STANDARD			
	blank = standard R = -40 °C to +85 °C	blank = series -16 = 16 pF -20 = 20 pF standard -30 = 30 pF -32 = 32 pF		blank = standard SP = spacer SL = sleeve							



Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Vishay products are not designed for use in life-saving or life-sustaining applications or any application in which the failure of the Vishay product could result in personal injury or death unless specifically qualified in writing by Vishay. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.